



Bourns Introduces New 11 mm Rotary Metal Shaft Potentiometer

Model PRS11R Series

Riverside, California – April 12, 2021 – In line with our commitment to provide products with innovative designs, superior quality and exceptional value, Bourns Sensors and Controls announces the release of the [Model PRS11R](#) Rotary Metal Shaft Potentiometer series.

The Model PRS11R is designed for use in professional audio and lighting applications, low/medium risk medical* and laboratory equipment, industrial automation controls and other applications where a reliable potentiometer is required. This model features a very small form factor and offers an optional momentary switch.

Samples and product quantities are now available. For detailed product information, please visit: www.bourns.com/products/potentiometers/commercial-panel-controls.

Should you have any questions or need any additional information, please contact [Bourns Customer Service/ Inside Sales](#).

Features

- THT mounting type
- 15,000 rotational cycle rating
- -20 °C to +70 °C operating temperature range
- Flatted shaft option
- Horizontal or vertical orientation option
- Optional push momentary switch
- RoHS compliant**

Applications

- Professional audio equipment
- Professional lighting consoles
- Consumer white goods
- Low/medium risk medical and diagnostic equipment*
- Test and measurement equipment
- Communications equipment
- Laboratory equipment
- Industrial automation controls

* Bourns[®] products have not been designed for and are not intended for use in "lifesaving," "life-critical" or "life-sustaining" applications nor any other applications where failure or malfunction of the Bourns[®] product may result in personal injury or death. See Legal Disclaimer Notice: www.bourns.com/docs/legal/disclaimer.pdf.

** RoHS Directive 2015/863, Mar 31, 2015 and Annex.