






Bourns® Model BID Series IGBT Product Guide

TO-252 SMD IGBT ($T_C = 25\text{ }^\circ\text{C}$, Unless Otherwise Specified)

Model Number	Photo	Package	Type	V_{CES} (V)	I_C @ $T=100\text{ }^\circ\text{C}$ (A)	Typ. $V_{CE(sat)}$ @ $I_C, V_{ge}=15\text{ V}$ (V)	I_F @ $T_C=100\text{ }^\circ\text{C}$ (A)	Operating Junction Temperature
BIDD05N60T		TO-252	Medium Speed	600	5	1.5	N/A	-55 °C to +150 °C

TO-247 DIP IGBT ($T_C = 25\text{ }^\circ\text{C}$, Unless Otherwise Specified)

Model Number	Photo	Package	Type	V_{CES} (V)	I_C @ $T=100\text{ }^\circ\text{C}$ (A)	Typ. $V_{CE(sat)}$ @ $I_C, V_{ge}=15\text{ V}$ (V)	I_F @ $T_C=100\text{ }^\circ\text{C}$ (A)	Operating Junction Temperature
BIDW20N60T		TO-247	Medium Speed	600	20	1.7	20	-55 °C to +150 °C
BIDW30N60T		TO-247	Medium Speed	600	30	1.65	30	-55 °C to +150 °C
BIDW50N65T		TO-247	Medium Speed	650	50	1.65	50	-55 °C to +150 °C
BIDNW30N60H3		TO-247N	High Speed	600	30	1.65	12	-55 °C to +150 °C

www.bourns.com

Americas: Tel +1-951 781-5500
Email americus@bourns.com

EMEA: Tel +36 88 885 877
Email eurocus@bourns.com



Asia-Pacific: Tel +886-2 256 241 17
Email asiacus@bourns.com

COPYRIGHT © 2022 • BOURNS, INC. • 08/22 • e/ESD2239
"Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries.