



SinglFuse™ SMD Fuses


Cross Reference Guide




SF-0603SPA-R Series



SF-2410FPA-W Series



SF-0603HI-F Series



SF-1206HIA-M Series



SF-2923HC-C Series



SF-2410HI-T Series



SF-3812TM-T Series


Competitor Series		Bourns Series			
		General Purpose		AEC-Q200 Compliant & Automotive Grade	
Littelfuse	407	SF-1206SP-M	-	-	-
Littelfuse	422	SF-2410FP-W	-	-	-
Littelfuse	422A	-	-	SF-2410FPA-W	-
Littelfuse	429	SF-1206FP	SF-1206S	-	-
Littelfuse	430	SF-1206SP	-	-	-
Littelfuse	433	SF-1206FP	SF-1206S	-	-
Littelfuse	434	SF-0603FP	SF-0603FP-F	-	-
Littelfuse	435	SF-0402FP	SF-0402FP-F	-	-
Littelfuse	437	SF-1206S-M	-	-	-
Littelfuse	437A	-	-	SF-1206SA-M	SF-1206SA-W
Littelfuse	438	SF-0603S-M	-	-	-
Littelfuse	438A	-	-	SF-0603SA-M	-
Littelfuse	438GT	SF-0603S-M	-	-	-
Littelfuse	440	SF-1206HI-M	SF-1206F	-	-
Littelfuse	440A	-	-	SF-1206HIA-M	SF-1206SA-W
Littelfuse	441	SF-0603SP-M	SF-0603HI-M	-	-
Littelfuse	441A	-	-	SF-0603HIA-M	SF-0603SPA-R
Littelfuse	443	SF-3812TL-T	-	-	-
Littelfuse	443LC	SF-3812TM-T	SF-3812TL-T	-	-
Littelfuse	448	SF-2410FP-W	-	-	-
Littelfuse	451	SF-2410FP-T	SF-2410FP-W SF-2410F-W	-	-
Littelfuse	452	SF-2410HI-T	SF-2410F-T	-	-
Littelfuse	453	SF-2410FP-T	SF-2410FP-W SF-2410F-W	-	-
Littelfuse	454	SF-2410HI-T	SF-2410F-T	-	-
Littelfuse	456	SF-3812FG-T	SF-3812F-T	-	-
Littelfuse	456SD	SF-3812F-T	-	-	-
Littelfuse	458	SF-1206S-W	-	-	-
Littelfuse	459	SF-2410FP-T*	SF-2410FP-W*	-	-
Littelfuse	460	SF-2410HI-T*	-	-	-
Littelfuse	461	SF-3812TM-T	-	-	-
Littelfuse	462	SF-3812TM-T	SF-3812TL-T	-	-
Littelfuse	463	SF-3812F-T	-	-	-
Littelfuse	464	SF-3812TL-T	SF-3812SP-T	-	-
Littelfuse	465	SF-3812TL-T	SF-3812SP-T	-	-
Littelfuse	466	SF-1206S	SF-1206S-M	-	-
Littelfuse	467	SF-0603FP-F	SF-0603FP	-	-
Littelfuse	468	SF-1206SP	SF-1206HI-M	-	-
Littelfuse	470	SF-1206S-W	-	-	-
Littelfuse	476	SF-2410FP-T	SF-2410FP-W SF-2410F-W	-	-
Littelfuse	485	SF-3812TM-T*	-	-	-
Littelfuse	493	SF-1206FP	-	-	-
Littelfuse	494	SF-0603FP-F	SF-0603FP	-	-
Littelfuse	501	SF-1206HV-M	-	-	-
Littelfuse	501A	-	-	SF-1206SA-R	SF-1206SA-W

* Recommend for new designs

SinglFuse™ SMD Fuses - Cross Reference Guide



SF-0603SPA-R Series



SF-2410FPA-W Series



SF-0603HI-F Series



SF-1206HIA-M Series



SF-2923HC-C Series



SF-2410HI-T Series



SF-3812TM-T Series

ADDITIONAL INFORMATION

[SinglFuse™ SMD Fuses](#)

[SinglFuse™ SMD Fuse Parametric Search Product Selection Tool](#)

[SinglFuse™ SMD Fuse Technical Library](#)

[SinglFuse™ SMD Fuses - Product Training Module](#)

Competitor Series		Bourns Series			
		General Purpose		AEC-Q200 Compliant & Automotive Grade	
Bel Fuse	0678D	SF-3812TM-T	SF-3812TL-T	-	-
Bel Fuse	0678H	SF-3812F-T	-	-	-
Bel Fuse	0678L	SF-3812F-T	-	-	-
Bel Fuse	0679H	SF-2410FP-W	SF-2410FP-T	SF-2410FPA-W	-
Bel Fuse	0679L	SF-2410F-W	SF-2410F-T	SF-2410FA-W	-
Bel Fuse	0679L	SF-2410FP-W	SF-2410FP-T	SF-2410FPA-W	-
Bel Fuse	0679L	SF-2410F-W	SF-2410F-T	SF-2410FA-W	-
Bel Fuse	0680H	SF-2410F-T	-	-	-
Bel Fuse	0680H	SF-2410HI-T	-	-	-
Bel Fuse	0680L	SF-2410F-T	-	-	-
Bel Fuse	0680L	SF-2410HI-T	-	-	-
Bel Fuse	0685F/C1F	SF-1206FP	SF-1206S-M	SF-1206SA-M	SF-1206SA-W
Bel Fuse	0685H/C1H	SF-1206HV-M	SF-1206HH-M	SF-1206SA-R	-
Bel Fuse	0685P	SF-1206S	SF-1206HI-M	SF-1206HIA-M	SF-1206SA-R
Bel Fuse	0685T/C1T	SF-1206SP	SF-1206SP-M	SF-1206HIA-M	SF-1206SA-W
Bel Fuse	0686F/C2F	SF-0603FP	SF-0603S-M	SF-0603SA-M	SF-0603SPA-R
Bel Fuse	0ABA	SF-0402F	SF-0402FP-F	-	-
Bel Fuse	0ABB	SF-0603HI-M	-	SF-0603SPA-R	SF-0603HIA-M
Bel Fuse	0ACA	SF-2410F-W	SF-2410F-T	-	-
Bel Fuse	C1Q	SF-1206FP	SF-1206S-M	-	-
Bel Fuse	C2Q	SF-0603FP	SF-0603S-M	-	-
Eaton	0603FA	SF-0603F	SF-0603S-M	SF-0603SA-M	SF-0603SPA-R
Eaton	0603HV	SF-0603HI-M	-	-	-
Eaton	1025FA	SF-3812TL-T	-	-	-
Eaton	1025HC	SF-3812F-T	-	-	-
Eaton	1025TD	SF-3812TL-T	-	-	-
Eaton	2410FA	SF-2410FP-W	SF-2410FP-T	-	-
Eaton	2410TD	SF-2410F-W	SF-2410F-T	-	-
Eaton	2410TD	SF-2410HI-T	SF-2410F-T	-	-
Eaton	3216FF	SF-1206S	SF-1206S-M	SF-1206SA-M	SF-1206SA-R
Eaton	3216TD	SF-1206SP	SF-1206SP-M	-	-
Eaton	3216TD	SF-1206SP	SF-1206SP-M	-	-
Eaton	CB61F	SF-2410FP-W	SF-2410FP-T	-	-
Eaton	CB61F	SF-2410F-W	SF-2410FP-T	-	-
Eaton	CC06FA	-	-	SF-0603SA-M	SF-0603SPA-R
Eaton	CC06H	SF-0603F	SF-0603HI-M	-	-
Eaton	CC12H	SF-1206F	SF-1206HI-M	SF-1206HIA-M	SF-1206SA-R
Eaton	CC12H	SF-1206F	SF-1206HH-M	SF-1206HIA-M	SF-1206SA-R
Eaton	CC12H	SF-1206F	SF-1206HH-M	SF-1206HIA-M	SF-1206SA-R
Schurter	MKF	SF-2410FP-T	SF-2410FP-W	-	-
Schurter	MKT	SF-2410HI-T	SF-2410F-T	-	-
Schurter	UAI 1206	-	-	SF-1206HIA-M	-
Schurter	UMF 250	SF-3812TL-T	-	-	-
Schurter	UMF 250	SF-3812F-T	-	-	-
Schurter	UMT 250	SF-3812TL-T	-	-	-
Schurter	USF 0402	SF-0402FP-F	SF-0402FP	-	-
Schurter	USF 0603	SF-0603HI-F	SF-0603F	-	-
Schurter	USI 1206	SF-1206FP	SF-1206S-M	-	-
Schurter	UST 1206	SF-1206HV-M	SF-1206S-W	-	-

www.bourns.com

BOURNS®

Americas: Tel +1-951 781-5500
Email americus@bourns.com

EMEA: Tel +36 88 885 877
Email eurocus@bourns.com

Asia-Pacific: Tel +886-2 256 241 17
Email asiacus@bourns.com

COPYRIGHT © 2023 • BOURNS, INC. • 05/23 • e/SF2301

"Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries. "SinglFuse" is a trademark of Bourns, Inc.