



# SinglFuse™ SMD Fuses


## Cross Reference Guide




SF-0603SPA-R Series



SF-2410FPA-W Series



SF-0603HI-F Series



SF-1206HIA-M Series



SF-2923HC-C Series



SF-2410HI-T Series



SF-3812TM-T Series

Competitor Series		Bourns Series			
		General Purpose		AEC-Q200 Compliant & Automotive Grade**	
Littelfuse	407	<a href="#">SF-1206SP-M</a>	-	-	-
Littelfuse	422	<a href="#">SF-2410FP-W</a>	-	-	-
Littelfuse	422A	-	-	<a href="#">SF-2410FPA-W</a>	-
Littelfuse	429	<a href="#">SF-1206FP</a>	<a href="#">SF-1206S</a>	-	-
Littelfuse	430	<a href="#">SF-1206SP</a>	-	-	-
Littelfuse	433	<a href="#">SF-1206FP</a>	<a href="#">SF-1206S</a>	-	-
Littelfuse	434	<a href="#">SF-0603FP</a>	<a href="#">SF-0603FP-F</a>	-	-
Littelfuse	435	<a href="#">SF-0402FP</a>	<a href="#">SF-0402FP-F</a> <a href="#">SF-0402FR</a>	-	-
Littelfuse	437	<a href="#">SF-1206S-M</a>	-	-	-
Littelfuse	437A	-	-	<a href="#">SF-1206SA-M</a>	<a href="#">SF-1206SA-W</a>
Littelfuse	438	<a href="#">SF-0603S-M</a>	-	-	-
Littelfuse	438A	-	-	<a href="#">SF-0603SA-M</a>	-
Littelfuse	438GT	<a href="#">SF-0603S-M</a>	-	-	-
Littelfuse	440	<a href="#">SF-1206HI-M</a>	<a href="#">SF-1206F</a>	-	-
Littelfuse	440A	-	-	<a href="#">SF-1206HIA-M</a>	<a href="#">SF-1206SA-W</a>
Littelfuse	441	<a href="#">SF-0603SP-R</a>	<a href="#">SF-0603HI-M</a>	-	-
Littelfuse	441A	-	-	<a href="#">SF-0603HIA-M</a>	<a href="#">SF-0603SPA-R</a>
Littelfuse	443	<a href="#">SF-3812TL-T</a>	-	-	-
Littelfuse	443LC	<a href="#">SF-3812TM-T</a>	<a href="#">SF-3812TL-T</a>	-	-
Littelfuse	448	<a href="#">SF-2410FP-W</a>	-	-	-
Littelfuse	451	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FP-W</a> <a href="#">SF-2410F-W</a>	-	-
Littelfuse	452	<a href="#">SF-2410HI-T</a>	<a href="#">SF-2410F-T</a>	-	-
Littelfuse	453	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FP-W</a> <a href="#">SF-2410F-W</a>	-	-
Littelfuse	454	<a href="#">SF-2410HI-T</a>	<a href="#">SF-2410F-T</a>	-	-
Littelfuse	456	<a href="#">SF-3812FG-T</a>	<a href="#">SF-3812F-T</a>	-	-
Littelfuse	456SD	<a href="#">SF-3812F-T</a>	-	-	-
Littelfuse	458	<a href="#">SF-1206S-W</a>	-	-	-
Littelfuse	459	<a href="#">SF-2410FP-T *</a>	<a href="#">SF-2410FP-W *</a>	-	-
Littelfuse	460	<a href="#">SF-2410HI-T *</a>	-	-	-
Littelfuse	461	<a href="#">SF-3812TM-T</a>	-	-	-
Littelfuse	462	<a href="#">SF-3812TM-T</a>	<a href="#">SF-3812TL-T</a>	-	-
Littelfuse	463	<a href="#">SF-3812F-T</a>	-	-	-
Littelfuse	464	<a href="#">SF-3812TL-T</a>	<a href="#">SF-3812SP-T</a>	-	-
Littelfuse	465	<a href="#">SF-3812TL-T</a>	<a href="#">SF-3812SP-T</a>	-	-
Littelfuse	466	<a href="#">SF-1206S</a>	<a href="#">SF-1206S-M</a>	-	-
Littelfuse	467	<a href="#">SF-0603FP-F</a>	<a href="#">SF-0603FP</a>	-	-
Littelfuse	468	<a href="#">SF-1206SP</a>	<a href="#">SF-1206HI-M</a>	-	-
Littelfuse	470	<a href="#">SF-1206S-W</a>	-	-	-
Littelfuse	476	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FP-W</a> <a href="#">SF-2410F-W</a>	-	-
Littelfuse	485	<a href="#">SF-3812TM-T *</a>	-	-	-
Littelfuse	493	<a href="#">SF-1206FP</a>	-	-	-
Littelfuse	494	<a href="#">SF-0603FP-F</a>	<a href="#">SF-0603FP</a>	-	-
Littelfuse	501	<a href="#">SF-1206HH-R</a> <a href="#">SF1206S-R</a>	<a href="#">SF-1206HV-M</a>	-	-
Littelfuse	501A	-	-	<a href="#">SF-1206SA-R</a> <a href="#">SF-1206HHA-R</a>	<a href="#">SF-1206SA-W</a>


\* Recommended for new designs

\*\*Meets Bourns' internal AEC-Q200 equivalent test plan.


# SinglFuse™ SMD Fuses - Cross Reference Guide



SF-0603SPA-R Series



SF-2410FPA-W Series



SF-0603HI-F Series



SF-1206HIA-M Series



SF-2923HC-C Series



SF-2410HI-T Series



SF-3812TM-T Series

## ADDITIONAL INFORMATION

[SinglFuse™ SMD Fuses](#)

[SinglFuse™ SMD Fuse Parametric Search Product Selection Tool](#)

[SinglFuse™ SMD Fuse Technical Library](#)

[SinglFuse™ SMD Fuse Product Training Module](#)

Competitor Series		Bourns Series			
		General Purpose		AEC-Q200 Compliant & Automotive Grade**	
Bel Fuse	0678D	<a href="#">SF-3812TM-T</a>	<a href="#">SF-3812TL-T</a>	-	-
Bel Fuse	0678H	<a href="#">SF-3812F-T</a>	-	-	-
Bel Fuse	0678L	<a href="#">SF-3812F-T</a>	-	-	-
Bel Fuse	0679H	<a href="#">SF-2410FP-W</a>	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FPA-W</a>	-
Bel Fuse	0679L	<a href="#">SF-2410F-W</a>	<a href="#">SF-2410F-T</a>	<a href="#">SF-2410FA-W</a>	-
		<a href="#">SF-2410FP-W</a>	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FPA-W</a>	-
Bel Fuse	0680H	<a href="#">SF-2410F-W</a>	<a href="#">SF-2410F-T</a>	<a href="#">SF-2410FA-W</a>	-
		<a href="#">SF-2410HI-T</a>	-	-	-
Bel Fuse	0680L	<a href="#">SF-2410HI-T</a>	-	-	-
		<a href="#">SF-2410HI-T</a>	-	-	-
Bel Fuse	0685F/C1F	<a href="#">SF-1206FP</a>	<a href="#">SF-1206S-M</a>	<a href="#">SF-1206SA-M</a>	<a href="#">SF-1206SA-W</a>
Bel Fuse	0685H/C1H	<a href="#">SF-1206S-R</a>	<a href="#">SF-1206HV-M</a>	<a href="#">SF-1206SA-R</a>	-
		<a href="#">SF-1206HH-R</a>	-	<a href="#">SF-1206HHA-R</a>	-
Bel Fuse	0685P	<a href="#">SF-1206S</a>	<a href="#">SF-1206HI-M</a>	<a href="#">SF-1206HIA-M</a>	<a href="#">SF-1206SA-R</a>
Bel Fuse	0685T/C1T	<a href="#">SF-1206SP</a>	<a href="#">SF-1206SP-M</a>	<a href="#">SF-1206HIA-M</a>	<a href="#">SF-1206SA-W</a>
Bel Fuse	0686F/C2F	<a href="#">SF-0603FP</a>	<a href="#">SF-0603S-M</a>	<a href="#">SF-0603SA-M</a>	<a href="#">SF-0603SPA-R</a>
Bel Fuse	0ABA	<a href="#">SF-0402F</a>	<a href="#">SF-0402FP-F</a>	-	-
		<a href="#">SF-0402FR</a>	-	-	-
Bel Fuse	0ABB	<a href="#">SF-0603SP-R</a>	<a href="#">SF-0603HI-M</a>	<a href="#">SF-0603SPA-R</a>	<a href="#">SF-0603HIA-M</a>
Bel Fuse	0ACA	<a href="#">SF-2410F-W</a>	<a href="#">SF-2410F-T</a>	-	-
Bel Fuse	C1Q	<a href="#">SF-1206FP</a>	<a href="#">SF-1206S-M</a>	-	-
Bel Fuse	C2Q	<a href="#">SF-0603FP</a>	<a href="#">SF-0603S-M</a>	-	-
Eaton	0603FA	<a href="#">SF-0603F</a>	<a href="#">SF-0603S-M</a>	<a href="#">SF-0603SA-M</a>	<a href="#">SF-0603SPA-R</a>
Eaton	0603HV	<a href="#">SF-0603SP-R</a>	<a href="#">SF-0603HI-M</a>	-	-
Eaton	1025FA	<a href="#">SF-3812TL-T</a>	-	-	-
		<a href="#">SF-3812F-T</a>	-	-	-
Eaton	1025HC	<a href="#">SF-3812F-T</a>	-	-	-
Eaton	1025TD	<a href="#">SF-3812TL-T</a>	-	-	-
Eaton	2410FA	<a href="#">SF-2410FP-W</a>	<a href="#">SF-2410FP-T</a>	-	-
		<a href="#">SF-2410F-W</a>	-	-	-
Eaton	2410TD	<a href="#">SF-2410HI-T</a>	<a href="#">SF-2410F-T</a>	-	-
Eaton	3216FF	<a href="#">SF-1206S</a>	<a href="#">SF-1206S-M</a>	<a href="#">SF-1206SA-M</a>	<a href="#">SF-1206SA-R</a>
		<a href="#">SF-1206HH-M</a>	<a href="#">SF-1206SP-M</a>	-	<a href="#">SF-1206HHA-R</a>
Eaton	3216TD	<a href="#">SF-1206SP</a>	<a href="#">SF-1206SP-M</a>	-	-
Eaton	CB61F	<a href="#">SF-2410FP-W</a>	<a href="#">SF-2410FP-T</a>	-	-
		<a href="#">SF-2410F-W</a>	-	-	-
Eaton	CC06FA	-	-	<a href="#">SF-0603SA-M</a>	<a href="#">SF-0603SPA-R</a>
Eaton	CC06H	<a href="#">SF-0603F</a>	<a href="#">SF-0603SP-R</a>	-	-
Eaton	CC12H	<a href="#">SF-1206F</a>	<a href="#">SF-1206HI-M</a>	<a href="#">SF-1206HIA-M</a>	<a href="#">SF-1206SA-R</a>
		<a href="#">SF-1206HH-M</a>	<a href="#">SF-1206HH-M</a>	<a href="#">SF-1206HHA-R</a>	<a href="#">SF-1206HHA-R</a>
Schurter	MKF	<a href="#">SF-2410FP-T</a>	<a href="#">SF-2410FP-W</a>	-	-
		<a href="#">SF-2410HI-T</a>	<a href="#">SF-2410F-W</a>	-	-
Schurter	MKT	<a href="#">SF-2410HI-T</a>	<a href="#">SF-2410F-T</a>	-	-
Schurter	UAI 1206	-	-	<a href="#">SF-1206HIA-M</a>	-
Schurter	UMF 250	<a href="#">SF-3812TL-T</a>	-	-	-
		<a href="#">SF-3812F-T</a>	-	-	-
Schurter	UMT 250	<a href="#">SF-3812TL-T</a>	-	-	-
Schurter	USF 0402	<a href="#">SF-0402FP-F</a>	<a href="#">SF-0402FP</a>	-	-
		<a href="#">SF-0402FR</a>	<a href="#">SF-0402FR</a>	-	-
Schurter	USF 0603	<a href="#">SF-0603HI-F</a>	<a href="#">SF-0603F</a>	-	-
Schurter	USI 1206	<a href="#">SF-1206FP</a>	<a href="#">SF-1206S-M</a>	-	-
		<a href="#">SF-1206HV-M</a>	<a href="#">SF-1206S-W</a>	-	-
Schurter	UST 1206	<a href="#">SF-1206HH-R</a>	<a href="#">SF-1206S-W</a>	-	-
		<a href="#">SF-1206HH-R</a>	-	-	-

\* Recommended for new designs

\*\*Meets Bourns' internal AEC-Q200 equivalent test plan.

[www.bourns.com](http://www.bourns.com)

**BOURNS®**

Americas: Tel +1-951 781-5500  
Email [americus@bourns.com](mailto:americus@bourns.com)

EMEA: Tel +36 88 885 877  
Email [eurocus@bourns.com](mailto:eurocus@bourns.com)

Asia-Pacific: Tel +886-2 256 241 17  
Email [asiacus@bourns.com](mailto:asiacus@bourns.com)

COPYRIGHT © 2024 • BOURNS, INC. • 2/24 • e/SF2404

"Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries. "SinglFuse" is a trademark of Bourns, Inc.