


Features

- Nano-second response to transients
- Solid brass gold or tin plated pins
- Designed to Telcordia and RUS standards
-  Listing per UL497 (File E53117)

Applications

- Central Office
- Remote cabinet
- Building entrance terminal

F Series 5-Pin Solid-State Overvoltage Surge Protectors

Bourns® solid-state 5-pin protector modules are designed to protect personnel and equipment from damage caused by excessive voltages and currents induced on telephone lines by lightning and AC power system faults. The solid-state protectors incorporate a fast semiconductor switch with operating voltage nearly independent of transient rise time. The module's fast, repeatable operation is designed to provide excellent equipment protection and long protection life. A fail-short mechanism operates under high current power-cross conditions to permanently short the line to ground. The industry-standard 5-pin base makes the modules interchangeable with existing 5-pin modules. The pins are available with gold or tin plating. The protectors have a detent position which disconnects the equipment side but leaves the module connected to the line side. Test points on the line side are optional.

Characteristics @ 20 °C, ±5 °C

	240 V	300 V
DC Breakdown Voltage (1 mA).....	200 V min.....	265 V min.
AC Breakdown (60 Hz).....	265 V max.....	400 V max.
Impulse Breakdown		
100 V/ μ s	<350 V	<400 V
1000 V/ μ s	<350 V	<400 V
Insulation Resistance @ 50 Vdc	100 M Ω min.	
Insulation Resistance @ 200 Vdc	100 M Ω min.	
DC Holdover	<30 ms max. with 25 A (10/1000 μ s) surge @260 mA and \pm 52 Vdc @200 mA and \pm 135 Vdc @140 mA and \pm 150 Vdc	
Service life	10 A for 1 sec, 10 surges, 60 Hz, 480 V \pm 10 A (10 x1000 μ s) unlimited \pm 100 A (10 x1000 μ s) unlimited \pm 10,000 A (8 x 20 μ s) fail-short	
Capacitance.....	Line to Ground, <100 pF @ 50 Vdc, 1 Vac, 1 Khz Line to Ground, <200 pF @ 0 Vdc, 1 Vac, 1 Khz to 1 Mhz Tip to Ring – imbalance <15 pF	
Response Time.....	<20 nanoseconds	
Power Cross Operation @60 Hz, rms	Fail-Short 5 A for 15 minutes Fail-Short 10 A for 15 minutes Fail-Short 30 A for 15 minutes Fail-Short 60 A for 3 seconds Fail-Short 120 A for 0.6 seconds Fail-Short 350 A for 0.04 seconds	
Storage and Operating Temperature	-40 to +65 °C	



WARNING Cancer and Reproductive Harm - www.P65Warnings.ca.gov

*RoHS Directive 2015/863, Mar 31, 2015 and Annex.

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

F Series 5-Pin Solid-State Overvoltage Surge Protectors

BOURNS®

How to Order

Catalog Number	Part Number	Color	Plating	Test Points	Housing Size	Service
240 Volt Modules without Heat Coil						
S3ABF	F013613	Black	Tin	No	3-type	Standard
R3B1FS	F013404	Black	Gold	No	3-type	Standard
R3C1FS	F013628	Black	Gold	Yes	3-type	Standard
R3B2FS	F013405	Green	Gold	No	3-type	Denial
R3C2FS	F013580	Green	Gold	Yes	3-type	Denial
S3ARF	F013614	Red	Tin	No	3-type	Special
R3B3FS	F013406	Red	Gold	No	3-type	Special
R3C3FS	F013570	Red	Gold	Yes	3-type	Special
R3B4FS	F013407	Yellow	Gold	No	3-type	PBX Battery
R3C4FS	F013571	Yellow	Gold	Yes	3-type	PBX Battery

300 Volt Modules without Heat Coil

S3AB	F013609	Black	Tin	No	3-type	Standard
R3B1S	F013618	Black	Gold	No	3-type	Standard
R3C1S	F013522	Black	Gold	Yes	3-type	Standard
R3B2S	F013619	Green	Gold	No	3-type	Denial
R3C2S	F013523	Green	Gold	Yes	3-type	Denial
S3AR	F013612	Red	Tin	No	3-type	Special
R3B3S	F013620	Red	Gold	No	3-type	Special
R3C3S	F013526	Red	Gold	Yes	3-type	Special
R3B4S	F013621	Yellow	Gold	No	3-type	PBX Battery
R3C4S	F013527	Yellow	Gold	Yes	3-type	PBX Battery

Notes: S3AB modules are RDUP (formerly RUS) accepted in an R99 connector and available for use in connector equivalents.

All modles are UL Listed.

RxxxS modules are designed to meet Telcordia specification GR-974 CORE.

All RDUP (formerly RUS) modules meet the criteria in Govt Publication RDUP TE&CM 823.

REV. B 11/08

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <http://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <http://www.bourns.com/docs/Legal/disclaimer.pdf>