




Features

- Compliant with AEC-Q200 Rev-C- Stress Test Qualification for Passive Components in Automotive Applications
- Fast tripping resettable circuit protection
- Surface mount packaging for automated assembly
- Small footprint size (1210)
- RoHS compliant* and halogen free**
- Agency recognition: 

MF-USMF Series - PTC Resettable Fuses

Electrical Characteristics

| Model | V max. Volts | I max. Amps | I _{hold} | I _{trip} | Resistance | | Max. Time To Trip | | Tripped Power Dissipation |
|-------------|--------------|-------------|-------------------|-------------------|-------------------|--------------------|-------------------|------------------|---------------------------|
| | | | Amperes at 23 °C | | Ohms at 23 °C | | Amperes at 23 °C | Seconds at 23 °C | Watts at 23 °C |
| | | | Hold | Trip | R _{Min.} | R _{1Max.} | | | Typ. |
| MF-USMF005 | 30 | 10 | 0.05 | 0.15 | 2.800 | 50.000 | 0.25 | 1.50 | 0.6 |
| MF-USMF010 | 30 | 10 | 0.10 | 0.30 | 0.800 | 15.000 | 0.50 | 0.60 | 0.6 |
| MF-USMF020 | 30 | 10 | 0.20 | 0.40 | 0.400 | 5.000 | 8.00 | 0.02 | 0.6 |
| MF-USMF035 | 6 | 40 | 0.35 | 0.75 | 0.200 | 1.300 | 8.00 | 0.20 | 0.6 |
| MF-USMF050 | 13.2 | 40 | 0.50 | 1.00 | 0.180 | 0.900 | 8.00 | 0.10 | 0.6 |
| MF-USMF075 | 6 | 40 | 0.75 | 1.50 | 0.070 | 0.450 | 8.00 | 0.10 | 0.6 |
| MF-USMF110 | 6 | 40 | 1.10 | 2.20 | 0.050 | 0.210 | 5.00 | 1.00 | 0.6 |
| MF-USMF150 | 6 | 40 | 1.50 | 3.00 | 0.030 | 0.110 | 5.00 | 5.00 | 0.6 |
| MF-USMF175 | 6 | 40 | 1.75 | 3.50 | 0.020 | 0.090 | 8.00 | 1.00 | 0.7 |
| MF-USMF175X | 6 | 40 | 1.75 | 3.50 | 0.020 | 0.090 | 8.00 | 1.00 | 0.7 |

Environmental Characteristics

| | | |
|----------------------------|-----------------------------------|---------------------------------|
| Operating Temperature..... | -40 °C to +85 °C | |
| Passive Aging..... | +85 °C, 1000 hours..... | ±5 % typical resistance change |
| Humidity Aging..... | +85 °C, 85 % R.H. 1000 hours..... | ±5 % typical resistance change |
| Thermal Shock..... | +85 °C to -40 °C, 20 times..... | ±10 % typical resistance change |
| Solvent Resistance..... | MIL-STD-202, Method 215..... | No change |
| Vibration..... | MIL-STD-883C, Method 2007.1,..... | No change |
| | Condition A | |

Test Procedures And Requirements For Model MF-USMF Series

| Test | Test Conditions | Accept/Reject Criteria |
|-----------------------------|---|--|
| Visual/Mech..... | Verify dimensions and materials..... | Per MF physical description |
| Resistance..... | In still air @ 23 °C..... | R _{min} ≤ R ≤ R _{1max} |
| Time to Trip..... | At specified current, V _{max} , 23 °C..... | T ≤ max. time to trip (seconds) |
| Hold Current..... | 30 min. at I _{hold} | No trip |
| Trip Cycle Life..... | V _{max} , I _{max} , 100 cycles..... | No arcing or burning |
| Trip Endurance..... | V _{max} , 48 hours..... | No arcing or burning |
| Solderability..... | ANSI/J-STD-002..... | 95 % min. coverage |
| UL File Number..... | E174545 http://www.ul.com/ Follow link to Certifications, then UL File No., enter E174545 | |
| TÜV Certificate Number..... | R 02057213 http://www.tuvdotcom.com/ Follow link to "other certificates", enter File No. 2057213 | |

* RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

** Bourns follows the prevailing definition of "halogen free" in the industry. Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less. Specifications are subject to change without notice. The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

Applications

- Game consoles
- PC motherboards
- USB port protection - USB 2.0, 3.0 & OTG
- HDMI 1.4 Source protection
- IEEE 1394 ports
- Mobile phones
- Digital cameras

MF-USMF Series - PTC Resettable Fuses


BOURNS®

Product Dimensions

| Model | A | | B | | C | | D |
|-------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| | Min. | Max. | Min. | Max. | Min. | Max. | Min. |
| MF-USMF005 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.80}{(0.031)}$ | $\frac{1.1}{(0.043)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF010 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.80}{(0.031)}$ | $\frac{1.1}{(0.043)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF020 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.80}{(0.031)}$ | $\frac{1.1}{(0.043)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF035 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.55}{(0.022)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF050 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.55}{(0.022)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF075 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.55}{(0.022)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF110 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.55}{(0.022)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF150 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.40}{(0.016)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF175 | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.40}{(0.016)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |
| MF-USMF175X | $\frac{3.00}{(0.118)}$ | $\frac{3.43}{(0.135)}$ | $\frac{2.35}{(0.093)}$ | $\frac{2.80}{(0.110)}$ | $\frac{0.40}{(0.016)}$ | $\frac{0.85}{(0.033)}$ | $\frac{0.30}{(0.012)}$ |

Packaging: 3000 pcs. per reel.

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$



Terminal material:

Electroless Ni under immersion Au


Termination pad solderability:

Standard Au finish:
Meets ANSI/J-STD-002 Category 2.

Recommended Storage:

40 °C max./70 % RH max.

Solder Reflow Recommendations



Notes:

- MF-USMF models cannot be wave soldered.
- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
- Compatible with Pb and Pb-free solder reflow profiles.
- Excess solder may cause a short circuit, especially during hand soldering. Please refer to the Multifuse® Polymer PTC Soldering Recommendation guidelines.

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.


MF-USMF Series - PTC Resettable Fuses

BOURNS®

Thermal Derating Chart - I_{hold} (Amps)

| Model | Ambient Operating Temperature | | | | | | | | |
|-------------|-------------------------------|--------|------|-------|-------|-------|-------|-------|-------|
| | -40 °C | -20 °C | 0 °C | 23 °C | 40 °C | 50 °C | 60 °C | 70 °C | 85 °C |
| MF-USMF005 | 0.08 | 0.07 | 0.06 | 0.05 | 0.04 | 0.04 | 0.03 | 0.03 | 0.02 |
| MF-USMF010 | 0.15 | 0.13 | 0.12 | 0.10 | 0.09 | 0.08 | 0.07 | 0.06 | 0.05 |
| MF-USMF020 | 0.32 | 0.28 | 0.24 | 0.20 | 0.18 | 0.16 | 0.14 | 0.12 | 0.10 |
| MF-USMF035 | 0.51 | 0.46 | 0.40 | 0.34 | 0.30 | 0.27 | 0.24 | 0.22 | 0.18 |
| MF-USMF050 | 0.76 | 0.66 | 0.58 | 0.48 | 0.42 | 0.38 | 0.35 | 0.29 | 0.23 |
| MF-USMF075 | 1.10 | 0.97 | 0.86 | 0.72 | 0.64 | 0.58 | 0.55 | 0.47 | 0.39 |
| MF-USMF110 | 1.60 | 1.42 | 1.26 | 1.10 | 0.94 | 0.86 | 0.80 | 0.70 | 0.58 |
| MF-USMF150 | 2.30 | 2.02 | 1.76 | 1.43 | 1.24 | 1.11 | 1.00 | 0.85 | 0.65 |
| MF-USMF175 | 2.80 | 2.45 | 2.10 | 1.75 | 1.55 | 1.45 | 1.35 | 1.25 | 1.10 |
| MF-USMF175X | 2.80 | 2.45 | 2.10 | 1.75 | 1.55 | 1.45 | 1.35 | 1.25 | 1.10 |

Typical Time to Trip at 23 °C



The Time to Trip curves represent typical performance of a device in a simulated application environment. Actual performance in specific customer applications may differ from these values due to the influence of other variables.

How to Order

MF - USMF 010 X - 2

Multifuse® Product Designator

Series USMF = 1210 Surface Mount Component


Hold Current, I_{hold} 005-175 (0.05-1.75 Amps)

Multifuse® freeXpansion™ Design

Packaging
Packaged per EIA 481-1
-2 = Tape and Reel

Typical Part Marking

Represents total content. Layout may vary.



MF-USMF SERIES, REV. Q, 07/17

“freeXpansion Design” is a trademark of Bourns, Inc. Specifications are subject to change without notice.


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

MF-USMF Series Tape and Reel Specifications

BOURNS®

| Tape Dimensions | MF-USMF Series per EIA 481-2 |
|------------------------|--|
| W | 8.0 ± 0.3 (0.315 ± 0.012) |
| P ₀ | 4.0 ± 0.1 (0.157 ± 0.004) |
| P ₁ | 4.0 ± 0.1 (0.157 ± 0.004) |
| P ₂ | 2.0 ± 0.05 (0.079 ± 0.002) |
| A ₀ | 2.76 ± 0.10 (0.109 ± 0.004) |
| B ₀ | 3.50 ± 0.10 (0.138 ± 0.004) |
| B ₁ max. | 4.35 (0.171) |
| D ₀ | $1.5 + 0.1/-0.0$ (0.059 + 0.004/-0) |
| F | 3.5 ± 0.05 (0.138 ± 0.002) |
| E ₁ | 1.75 ± 0.10 (0.069 ± 0.004) |
| E ₂ min. | 6.25 (0.246) |
| T max. | 0.6 (0.024) |
| T ₁ max. | 0.1 (0.004) |
| K ₀ | 1.07 ± 0.10 (0.042 ± 0.004) |
| Leader min. | 390 (15.35) |
| Trailer min. | 160 (6.30) |
| Reel Dimensions | |
| A max. | 185 (7.283) |
| N min. | 50 (1.97) |
| W ₁ | $8.4 + 1.5/-0.0$ (0.331 + 0.059/-0) |
| W ₂ max. | 14.4 (0.567) |

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$



Specifications are subject to change without notice.
 The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
 Users should verify actual device performance in their specific applications.