

Test Report

No. : CE/2007/22446G

Date : 2007/09/12

Page : 1 of 5

BOURNS INC.
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114, USA



The following sample(s) was/were submitted and identified by/on behalf of the client as :

Sample Description : SRF SERIES
Style/Item No. : SRF SERIES
Sample Receiving Date : 2007/02/09
Testing Period : 2007/02/09 TO 2007/02/16

=====
Test Requested : In accordance with the RoHS Directive 2002/95/EC, and its amendment directives.

Test Method : With reference to IEC 62321, Ed.1 111/54/CDV
Procedures for the Determination of Levels of Regulated Substances in Electrotechnical Products.

- (1) Determination of Cadmium by ICP-AES.
- (2) Determination of Lead by ICP-AES.
- (3) Determination of Mercury by ICP-AES.
- (4) Determination of Hexavalent Chromium for non-metallic samples by UV/Vis Spectrometry.
- (5) Determination of PBB and PBDE by GC/MS.

Test Result(s) : Please refer to next page(s).



Chenyu Kung / Operation Manager
Signed for and on behalf of
SGS TAIWAN LTD.
Chemical Laboratory – Taipei

Test Report

No. : CE/2007/22446G

Date : 2007/09/12

Page : 2 of 5

BOURNS INC.
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114, USA



Test results by chemical method (Unit: mg/kg)

Test Item (s):	Method (Refer to)	Result	MDL
		No.1	
Cadmium (Cd)	(1)	n.d.	2
Lead (Pb)	(2)	63.3	2
Mercury (Hg)	(3)	n.d.	2
Hexavalent Chromium Cr(VI) by alkaline extraction	(4)	n.d.	2
Sum of PBBs	(5)	n.d.	-
Monobromobiphenyl		n.d.	5
Dibromobiphenyl		n.d.	5
Tribromobiphenyl		n.d.	5
Tetrabromobiphenyl		n.d.	5
Pentabromobiphenyl		n.d.	5
Hexabromobiphenyl		n.d.	5
Heptabromobiphenyl		n.d.	5
Octabromobiphenyl		n.d.	5
Nonabromobiphenyl		n.d.	5
Decabromobiphenyl		n.d.	5
Sum of PBDEs (Mono to Nona) (Note 4)		n.d.	-
Monobromobiphenyl ether		n.d.	5
Dibromobiphenyl ether		n.d.	5
Tribromobiphenyl ether		n.d.	5
Tetrabromobiphenyl ether		n.d.	5
Pentabromobiphenyl ether		n.d.	5
Hexabromobiphenyl ether		n.d.	5
Heptabromobiphenyl ether		n.d.	5
Octabromobiphenyl ether		n.d.	5
Nonabromobiphenyl ether	n.d.	5	
Decabromobiphenyl ether	n.d.	5	
Sum of PBDEs (Mono to Deca)	n.d.	-	

TEST PART DESCRIPTION:

NO.1 : MIXED ALL PARTS

- Note :
1. mg/kg = ppm
 2. n.d. = Not Detected
 3. MDL = Method Detection Limit
 4. According to 2005/717/EC DecaBDE is exempt.
 5. "-" = Not Regulated

Test Report


No. : CE/2007/22446G Date : 2007/09/12

Page : 3 of 5

BOURNS INC.
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114, USA



- 1) These samples were dissolved totally by pre-conditioning method according to below flow chart.
(Cr⁶⁺ test method excluded)
- 2) Name of the person who made measurement: Troy Chang
- 3) Name of the person in charge of measurement: Chenyu Kung




Sample Material	Digestion Acid
Steel, copper, aluminum, solder	Aqua regia, HNO ₃ , HCl, HF, H ₂ O ₂
Glass	HNO ₃ /HF
Gold, platinum, palladium, ceramic	Aqua regia
Silver	HNO ₃
Plastic	H ₂ SO ₄ , H ₂ O ₂ , HNO ₃ , HCl
Others	Any acid to total digestion

BOURNS INC.
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114, USA



PBB/PBDE analytical FLOW CHART



Test Report

No. : CE/2007/22446G

Date : 2007/09/12

Page : 5 of 5

BOURNS INC.

1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114, USA



** End of Report **