

BOURNS®

Bourns Inc.








1200 COLUMBIA AVE.,
RIVERSIDE, CA 92507, U. S. A.

Trimpot RoHS Test Report

MODEL: 3314

MATERIAL DECLARATION SHEET

No.	Construction Element	Report	Note
1	SNAPSTRATE (34880-15502)	 Adobe Acrobat Document CE/2014/40563 2014/4/10	A
2	TERM INK (18200-01359)	 Adobe Acrobat Document CE/2014/40567 2014/4/10	A
3	RESIST INK (18300-01357)	 Adobe Acrobat Document CE/2014/40569 2014/4/10	A
4	RESIST INK (18300-01756)	 Adobe Acrobat Document CE/2014/40570 2014/4/10	A
5	RESIST INK (18300-01775)	 Adobe Acrobat Document CE/2014/40571 2014/4/10	B
6	RESIST INK (18050-00850)	 Adobe Acrobat Document CE/2014/40572 2014/4/10	A
7	RESIST INK (18050-00851)	 Adobe Acrobat Document CE/2014/40573 2014/4/10	A
8	RESIST INK (18050-00852)	 Adobe Acrobat Document CE/2014/40574 2014/4/10	A

9	HOUSING COMPOUND (16553-00506)	 Adobe Acrobat Document CE/2014/40575 2014/4/10	A
10	CONTACT SPRING (34861-63913)	 Adobe Acrobat Document CE/2014/40582 2014/4/10	A
11	LEAD FRAME (34916-25202)	 Adobe Acrobat Document CE/2014/40584 2014/4/10	A
12	SEAL RING (34732-20501)	 Adobe Acrobat Document CE/2014/40586 2014/4/10	A
13	LID (34132-41501)	 Adobe Acrobat Document CE/2014/40588 2014/4/10	A
14	LUBE (18810-00305)	 Adobe Acrobat Document CE/2014/40590 2014/4/10	A
15	LUBE (18810-00421)	 Adobe Acrobat Document CE/2014/40589 2014/4/10	A

- Note A: RoHS compliance.
- Note B: 7(c)-I. Electrical & electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors.

Requirements:

- ❖ Contain Pb · Hg · Cr+6 · PBB and PBDE < 0.1 % (1000 ppm) by weight.
- ❖ Contain Cd < 0.01 % (100 ppm) by weight