

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2006/72269
Date : 2006/07/17
Page : 1 of 4



The following sample(s) was/were submitted and identified by/on behalf of the client as :

Sample Description : MF-R-99, MF-R/72, MF-RX/72, MF-R-6, MF-RHT
Style/Item No : MF-R/72-6, MF-RX/72-6, MF-RX, MF-RG, MF-R/90
Buyer/Order No : BOUMS XIAMEN
Sample Received : 2006/07/10
Testing Period : 2006/07/10 TO 2006/07/17

=====
Test Result(s) : - Please see the next page(s) -


Daniel Yeh, M.R. / Operation Manager
Signed for and on behalf of
SGS TAIWAN LTD.

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
 1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
 SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2006/72269
 Date : 2006/07/17
 Page : 2 of 4



Test Result(s)

PART NAME NO.1 : MIXED ALL PARTS

Test Item (s):	Unit	Method	MDL	Result
				No.1
PBBs (Polybrominated biphenyls)	---	---	---	---
Monobromobiphenyl	%	With reference to USEPA3540C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl	%		0.0005	N.D.
Tribromobiphenyl	%		0.0005	N.D.
Tetrabromobiphenyl	%		0.0005	N.D.
Pentabromobiphenyl	%		0.0005	N.D.
Hexabromobiphenyl	%		0.0005	N.D.
Heptabromobiphenyl	%		0.0005	N.D.
Octabromobiphenyl	%		0.0005	N.D.
Nonabromobiphenyl	%		0.0005	N.D.
Decabromobiphenyl	%		0.0005	N.D.
Total PBBs (Polybrominated biphenyls)/Sum of above	%		-	N.D.
PBBEs(PBDEs) (Polybrominated biphenyl ethers)	---	---	---	---
Monobromobiphenyl ether	%	With reference to USEPA3540C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl ether	%		0.0005	N.D.
Tribromobiphenyl ether	%		0.0005	N.D.
Tetrabromobiphenyl ether	%		0.0005	N.D.
Pentabromobiphenyl ether	%		0.0005	N.D.
Hexabromobiphenyl ether	%		0.0005	N.D.
Heptabromobiphenyl ether	%		0.0005	N.D.
Octabromobiphenyl ether	%		0.0005	N.D.
Nonabromobiphenyl ether	%		0.0005	N.D.
Decabromobiphenyl ether	%		0.0005	N.D.
Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above	%		-	N.D.
Total of Mono to Nonabrominated biphenyl ether. (Note 4)	%	-	N.D.	

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
 1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
 SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2006/72269
 Date : 2006/07/17
 Page : 3 of 4




Test Item (s):	Unit	Method	MDL	Result
				No. 1
Chromium VI (Cr+6)	ppm	UV-VIS(US EPA 7196A) after reference to US EPA 3060A.	2	N.D.
Cadmium (Cd)	ppm	ICP-AES after reference to EN 1122, method B:2001 or other acid digestion.	2	N.D.
Mercury (Hg)	ppm	ICP-AES after reference to US EPA 3052 or other acid digestion.	2	N.D.
Lead (Pb)	ppm	ICP-AES after reference to US EPA 3050B or other acid digestion.	2	29.9

- NOTE: (1) N.D. = Not Detected (<MDL)
 (2) ppm = mg/kg
 (3) MDL = Method Detection Limit
 (4) Decabromobiphenyl ether (DecaBDE) in polymeric applications is exempted by
 Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified
 under document 2005/717/EC.
 (5) PBBEs=PBDEs=Polybrominated Diphenyl Ethers=PBDOs=PBBOs.
 (6) " - " = Not Regulation
 (7) " --- " = Not Applicable

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CE/2006/72269
Date : 2006/07/17
Page : 4 of 4



** End of Report **