

Test Report


BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CV/2006/30251
Date : 2006/04/06
Page : 1 of 4

The following merchandise was (were) submitted and identified by the client as :

Type of Product : BOURNS TRIMPOT
Style/Item No : 3269 (TR:10 OHMS~50K OHMS)
Sample Received : 2006/03/29
Testing Date : 2006/03/29 TO 2006/04/06

=====
Test Result : - Please see the next page -


Daniel Yeh, M.R. / Operation Manager
Signed for and on behalf of
SGS TAIWAN LTD.

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CV/2006/30251
Date : 2006/04/06
Page : 2 of 4

Test Result

PART NAME NO.1 : MIXED ALL PARTS

Test Item (s):	Unit	Method	MDL	Result
				No.1
Monobromobiphenyl	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl	%		0.0005	N.D.
Tribromobiphenyl	%		0.0005	N.D.
Tetrabromobiphenyl	%		0.0005	N.D.
Pentabromobiphenyl	%		0.0005	N.D.
Hexabromobiphenyl	%		0.0005	N.D.
Heptabromobiphenyl	%		0.0005	N.D.
Octabromobiphenyl	%		0.0005	N.D.
Nonabromobiphenyl	%		0.0005	N.D.
Decabromobiphenyl	%		0.0005	N.D.
Total PBBs (Polybrominated biphenyls)/Sum of above	%	-	N.D.	
Monobromobiphenyl ether	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl ether	%		0.0005	N.D.
Tribromobiphenyl ether	%		0.0005	N.D.
Tetrabromobiphenyl ether	%		0.0005	N.D.
Pentabromobiphenyl ether	%		0.0005	N.D.
Hexabromobiphenyl ether	%		0.0005	N.D.
Heptabromobiphenyl ether	%		0.0005	N.D.
Octabromobiphenyl ether	%		0.0005	N.D.
Nonabromobiphenyl ether	%		0.0005	N.D.
Decabromobiphenyl ether	%		0.0005	N.D.
Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above	%	-	N.D.	
Total of Mono to Nonabrominated biphenyl ether. (Note 4)	%	-	N.D.	

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
 1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
 SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CV/2006/30251
 Date : 2006/04/06
 Page : 3 of 4

Test Item (s):	Unit	Method	MDL	Result
				No.1
Chromium VI (Cr+6)	ppm	UV-VIS(US EPA 7196A) after reference to US EPA 3060A.	2	N.D.
Cadmium (Cd)	ppm	ICP-AES after reference to EN 1122, method B:2001 or other acid digestion.	2	N.D.
Mercury (Hg)	ppm	ICP-AES after reference to US EPA 3052 or other acid digestion.	2	N.D.
Lead (Pb)	ppm	ICP-AES after reference to US EPA 3050B or other acid digestion.	2	2551.1

- NOTE: (1) N.D. = Not detected (<MDL)
 (2) ppm = mg/kg
 (3) MDL = Method Detection Limit
 (4) Decabromodiphenyl ether (DecaBDE) in polymeric applications is exempted by
 Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified
 under document 2005/717/EC.
 (5) PBBEs=PBDEs=Polybrominated Diphenyl Ethers=PBDOs=PBBOs.
 (6) " - " = Not Regulation

Test Report

BOURNS ELECTRONICS (TAIWAN) LTD.
1, KUNG 6TH ROAD, INDUSTRIAL ZONE II, LIN-KOU
SHIANG, TAIPEI HSIEN, TAIWAN

Report No. : CV/2006/30251
Date : 2006/04/06
Page : 4 of 4

