




Features

- Complies with IEEE 802.3 standard specifications including 350 μ H with 8 mA DC bias
- Minimum interwinding breakdown voltage of 1500 Vrms
- RoHS compliant
- Four ports connector with enhanced EMI
- Integrated magnetics design provides higher reliability and conserves board space

PT44216M4 - Quad Port 10/100 Base-Tx

Electrical Specifications @ 25 °C

Insertion Loss	
1-100 MHz	-1.0 dB typ.
Return Loss	
1-10 MHz	-20 dB typ.
30-60 MHz	-12 dB typ.
60-80 MHz	-12 dB typ.
Crosstalk	
1-10 MHz	-40 dB typ.
30-60 MHz	-35 dB typ.
60-100 MHz	-30 dB typ.
CMRR	
1-50 MHz	-30 dB typ.
50-100 MHz	-20 dB typ.
Operating Temperature	0 °C to +70 °C
Storage Temperature	-40 °C to +85 °C

Physical Specifications

Metal Shielding	Nickel-plated copper alloy
Contact	Phosphor bronze, 6 u-inch gold-flashed unless otherwise specified
Housing	Thermoplastic PBT UL94V0 rated

Packaging Specifications


160 pcs./tray

How to Order


PT44216M4

Model

Typical Part Marking




Product Dimensions



Recommended PCB Layout

COMPONENT SIDE VIEW



DIMENSIONS: MM (INCHES)


TOLERANCES: .XX 0.25 (.01)

TOLERANCES: .XXX 0.13 (.005)

PT44216M4 - Quad Port 10/100 Base-Tx

BOURNS®

Electrical Schematic



OBsolete



Reliable Electronic Solutions

Asia-Pacific:

Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

Europe:

Tel: +41-41 768 5555 • Fax: +41-41 768 5510

The Americas:

Tel: +1-951 781-5500 • Fax: +1-951 781-5700

www.bourns.com