

# Test Report

BOURNS INC.  
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114,  
U.S.A.

Report No. : CE/2005/73289A  
Date : 2005/07/26  
Page : 1 of 4

**The following merchandise was (were) submitted and identified by the client as :**

Type of Product : SHIELDED SMD POWER INDUCTOR  
Style/Item No : SRR1305 SERIES  
Sample Received : 2005/07/15  
Testing Date : 2005/07/15 TO 2005/07/26

=====  
**Test Result** : - Please see the next page -

  
Daniel Yeh, M.R. / Operation Manager  
Signed for and on behalf of  
SGS TAIWAN LTD.

# Test Report

BOURNS INC.  
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114,  
U.S.A.

Report No. : CE/2005/73289A  
Date : 2005/07/26  
Page : 2 of 4

## Test Result

PART NAME NO.1 : MIXED ALL PARTS

Test Item (s):	Unit	Method	MDL	Result
				No.1
Monobromobiphenyl	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl	%		0.0005	N.D.
Tribromobiphenyl	%		0.0005	N.D.
Tetrabromobiphenyl	%		0.0005	N.D.
Pentabromobiphenyl	%		0.0005	N.D.
Hexabromobiphenyl	%		0.0005	N.D.
Heptabromobiphenyl	%		0.0005	N.D.
Octabromobiphenyl	%		0.0005	N.D.
Nonabromobiphenyl	%		0.0005	N.D.
Decabromobiphenyl	%		0.0005	N.D.
<b>Total PBBs (Polybrominated biphenyls)/Sum of above</b>	%		-	N.D.
Monobromobiphenyl ether	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl ether	%		0.0005	N.D.
Tribromobiphenyl ether	%		0.0005	N.D.
Tetrabromobiphenyl ether	%		0.0005	N.D.
Pentabromobiphenyl ether	%		0.0005	N.D.
Hexabromobiphenyl ether	%		0.0005	N.D.
Heptabromobiphenyl ether	%		0.0005	N.D.
Octabromobiphenyl ether	%		0.0005	N.D.
Nonabromobiphenyl ether	%		0.0005	N.D.
Decabromobiphenyl ether	%		0.0005	N.D.
<b>Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above</b>	%		-	N.D.
<b>Total of Mono to Nona-brominated biphenyl ether. (Note 4)</b>	%		-	N.D.

# Test Report

BOURNS INC.  
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114,  
U.S.A.

Report No. : CE/2005/73289A  
Date : 2005/07/26  
Page : 3 of 4

Test Item (s):	Unit	Method	MDL	Result
				No.1
Chromium VI (Cr+6)	ppm	UV-VIS after reference to US EPA 3060A.	2	N.D.
Cadmium (Cd)	ppm	ICP-AES after reference to EN 1122, method B:2001 or other acid digestion.	2	N.D.
Mercury (Hg)	ppm	ICP-AES after reference to US EPA 3052 or other acid digestion.	2	N.D.
Lead (Pb)	ppm	ICP-AES after reference to US EPA 3050B or other acid digestion.	2	14.4

- NOTE: (1) N.D. = Not detected (<MDL)  
 (2) ppm = mg/kg  
 (3) MDL = Method Detection Limit  
 (4) Decabromodiphenyl ether (DecaBDE) in polymeric applications is exempted by Commission Decision of 13 Oct 2005 amending Directive 2002/95/EC notified under document 2005/717/EC.  
 (5) PBBEs=PBDEs=Polybrominated Diphenyl Ethers=PBDOs=PBBOs.  
 (6) " - " = Not Regulation

## Test Report

BOURNS INC.  
1200 COLUMBIA AVE., RIVERSIDE, CA 92507-2114,  
U.S.A.

Report No. : CE/2005/73289A  
Date : 2005/07/26  
Page : 4 of 4

