








BOURNS®

The Restriction of Hazardous Substances

Part NO.: SRP4020TA, SRP4012TA Series

Date: 1/7/14

No.	Construction Element (subpart)	Homogeneous Material	Report No.	Pb	Cd	Hg	Cr ⁶⁺	PBBs	PBDEs	Br	Cl	File
			Date									
1	Carbonyl body	Carbonyl Powder	CE/2013/A0100	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	
			10/8/13									
2	Circuit-Copper	Copper Wire	Ce/2013/A0653	N.D.	N.D.	N.D.	Negative	N.D.	N.D.	N.D.	N.D.	
			10/11/13									
3	Circuit-Coating	Copper Colored Coating On The Magnet Wire	KA/2013/20904	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	168	
			2/23/13									
4	Terminal-Clip	Copper_C1100	CE/2013/A0101	N.D.	N.D.	N.D.	Negative	N.D.	N.D.	N.D.	N.D.	
			10/8/13									
5	Solder	Lead Free Solder	CE/2013/22766	19	N.D.	N.D.	Negative	N.D.	N.D.	N.D.	N.D.	
			3/1/13									
6	Body-Coating	Environmental epoxy Resin(grey)	CANEC1310552701	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	345	
			7/10/13									
7	Marking	INK-Black	SHAEC1325093702	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	N.D.	173	
			12/27/13									

Remark: 1. Cd<100ppm;
 2. Pb, Hg, Cr6+, PBBs, PBDEs<1000ppm;
 3. Br<900ppm, Cl<900ppm, Br+Cl<1500ppm

RoHS Exemption: None