

BIDIRECTIONAL THYRISTOR OVERVOLTAGE PROTECTORS

TISP4xxxH3BJ Overvoltage Protector Series

TISP4xxxH3BJ Overview

This TISP® device series protects central office, access and customer premise equipment against overvoltages on the telecom line. The TISP4xxxH3BJ is available in a wide range of voltages and has a high current capability, allowing minimal series resistance to be used. These protectors have been specified mindful of the following standards and recommendations: GR-1089-CORE, FCC Part 68, UL1950, EN 60950, IEC 60950, ITU-T K.20, K.21 and K.45. The TISP4350H3BJ meets the FCC Part 68 "B" ringer voltage requirement and survives the Type A and B impulse tests. These devices are housed in a surface mount SMB (DO-214AA) package.

Additional Information

Click these links for more information:









LIBRARY

Agency Recognition

Description					
UL	File Number: <u>E215609</u>				

Summary Electrical Characteristics

Part #	V _{DRM} V	V _(BO) V	V _T @ I _T V	I _{DRM} μΑ	I _(BO) mA	I _T	I _H mA	C _o @ -2 V pF	Functionally Replaces
TISP4070H3	58	70	3	5	600	5	150	120	P0640SC†
TISP4080H3	65	80	3	5	600	5	150	120	P0720SC†
TISP4095H3	75	95	3	5	600	5	150	120	P0900SC†
TISP4115H3	90	115	3	5	600	5	150	120	P1100SC†
TISP4125H3	100	125	3	5	600	5	150	65	
TISP4145H3	120	145	3	5	600	5	150	65	P1300SC†
TISP4165H3	135	165	3	5	600	5	150	65	
TISP4180H3	145	180	3	5	600	5	150	65	P1500SC
TISP4200H3	155	200	3	5	600	5	150	65	
TISP4220H3	160	220	3	5	600	5	150	65	P1800SC
TISP4240H3	180	240	3	5	600	5	150	55	
TISP4250H3	190	250	3	5	600	5	150	55	P2300SC†
TISP4265H3	200	265	3	5	600	5	150	55	
TISP4290H3	220	290	3	5	600	5	150	55	P2600SC†
TISP4300H3	230	300	3	5	600	5	150	55	
TISP4350H3	275	350	3	5	600	5	150	55	P3100SC
TISP4395H3	320	395	3	5	600	5	150	55	P3500SC
TISP4400H3	300	400	3	5	600	5	150	55	

[†] Bourns part has an improved protection voltage

Summary Current Ratings

Parameter		I _{TSP} A					I _{TSM} A	di/dt A/μs
Waveshape	2/10	1.2/50, 8/20	10/160	5/320	10/560	10/1000	1 cycle 60 Hz	2/10 Wavefront
Value	500	300	250	200	160	100	60	400

BOURNS

ITU-T K.20/21 Rating 8 kV 10/700, 200 A 5/310


Ion-Implanted Breakdown Region Precise and Stable Voltage Low Voltage Overshoot under Surge

Device	V_{DRM}	V _(BO)
Device	V	٧
'4070	58	70
'4080	65	80
'4095	75	95
'4115	90	115
'4125	100	125
'4145	120	145
'4165	135	165
'4180	145	180
'4200	155	200
'4220	160	220
'4240	180	240
'4250	190	250
'4265	200	265
'4290	220	290
'4300	230	300
'4350	275	350
'4395	320	395
'4400	300	400

Low Differential Capacitance 67 pF max.



SMBJ Package (Top View)



Device Symbol



Terminals T and R correspond to the alternative line designators of A and B

Rated for International Surge Wave Shapes

Waveshape	Standard	I _{TSP}
wavesnape	Standard	Α
2/10 µs	GR-1089-CORE	500
8/20 µs	IEC 61000-4-5	300
10/160 µs	FCC Part 68	250
10/700 µs	ITU-T K.20/21	200
10/560 µs	FCC Part 68	160
10/1000 μs	GR-1089-CORE	100

Description

These devices are designed to limit overvoltages on the telephone line. Overvoltages are normally caused by a.c. power system or lightning flash disturbances which are induced or conducted on to the telephone line. A single device provides 2-point protection and is typically used for the protection of 2-wire telecommunication equipment (e.g. between the Ring and Tip wires for telephones and modems). Combinations of devices can be used for multi-point protection (e.g. 3-point protection between Ring, Tip and Ground).

The protector consists of a symmetrical voltage-triggered bidirectional thyristor. Overvoltages are initially clipped by breakdown clamping until the voltage rises to the breakover level, which causes the device to crowbar into a low-voltage on state. This low-voltage on state causes the current resulting from the overvoltage to be safely diverted through the device. The high crowbar holding current helps prevent d.c. latchup as the diverted current subsides.

This TISP4xxxH3BJ range consists of eighteen voltage variants to meet various maximum system voltage levels (58 V to 320 V). They are guaranteed to voltage limit and withstand the listed international lightning surges in both polarities. These high (H) current protection devices are in a plastic package SMBJ (JEDEC DO-214AA with J-bend leads) and supplied in embossed carrier reel pack. For alternative voltage and holding current values, consult the factory. For lower rated impulse currents in the SMB package, the 50 A 10/1000 TISP4xxxM3BJ series is available.

How to Order

Device	Package	Package Carrier	
TISP4xxxH3BJ	BI (I Bond DO 214AA/SMB)	Embossed Tape Reeled	TISP4xxxH3BJR-S
	BJ (J-Bend DO-214AA/SMB)	Bulk Pack	TISP4xxxH3BJ-S

Insert xxx value corresponding to protection voltages of 070, 080, 095, 115 etc.

NOVEMBER 1997 - REVISED MARCH 2021

Absolute Maximum Ratings, TA = 25 °C (Unless Otherwise Noted)

Rating		Symbol	Value	Unit
	'4070		± 58	
	'4080		± 65	
	'4095		±75	
	'4115		±90	
	'4125		± 100	
	'4145		± 120	
	'4165		± 135	
	'4180		± 145	
Repetitive peak off-state voltage, (see Note 1)	'4200	V_{DRM}	± 155	V
riepentive peak on state voltage, (see Note 1)	'4220	V DRIM	± 160	V
	'4240		± 180	
	'4250		± 190	
	'4265		±200	
	'4290		±220	
	'4300 '4300		±230	
	'4350 '4350		±275	
	'4395 '4499		± 320	
New years I'll a great and a state of the control (see Nation O. O. and O.	'4400		± 300	
Non-repetitive peak on-state pulse current (see Notes 2, 3 and 4)			500	
2/10 μs (GR-1089-CORE, 2/10 μs voltage wave shape)			500	
8/20 μs (IEC 61000-4-5, 1.2/50 μs voltage, 8/20 current combination wave	e generator)		300	
10/160 μs (FCC Part 68, 10/160 μs voltage wave shape)			250	
5/200 µs (VDE 0433, 10/700 µs voltage wave shape)		I _{TSP}	220	Α
0.2/310 µs (l3124, 0.5/700 µs voltage wave shape)		115P	200	, ,
5/310 µs (ITU-T K.20/21, 10/700 µs voltage wave shape)			200	
5/310 µs (FTZ R12, 10/700 µs voltage wave shape)			200	
10/560 μs (FCC Part 68, 10/560 μs voltage wave shape)			160	
10/1000 μs (GR-1089-CORE, 10/1000 μs voltage wave shape)			100	
Non-repetitive peak on-state current (see Notes 2, 3 and 5)				
20 ms (50 Hz) full sine wave			55	
16.7 ms (60 Hz) full sine wave		I_{TSM}	60	Α
1000 s 50 Hz/60 Hz a.c.			2.1	
Initial rate of rise of on-state current, Exponential current ramp, Maximum ramp va	lue < 200 A	di _T /dt	400	A/µs
Junction temperature		TJ	-40 to +150	°C
Storage temperature range		T _{stg}	-65 to +150	°C

NOTES: 1. See Applications Information and Figure 10 for voltage values at lower temperatures.

- 2. Initially, the TISP4xxxH3BJ must be in thermal equilibrium with T_{.I} = 25 °C
- 3. The surge may be repeated after the TISP4xxxH3BJ returns to its initial conditions.
- 4. See Applications Information and Figure 11 for current ratings at other temperatures.
- 5. EIA/JESD51-2 environment and EIA/JESD51-3 PCB with standard footprint dimensions connected with 5 A rated printed wiring track widths. See Figure 8 for the current ratings at other durations. Derate current values at -0.61 %/°C for ambient temperatures above 25 °C.

Electrical Characteristics, T_A = 25 °C (Unless Otherwise Noted)

	Parameter	Test Conditions		Min.	Тур.	Max.	Unit
l	Repetitive peak off-	$V_D = V_{DRM}$	T _A = 25 °C			±5	μA
IDRM	state current	VD - VDRM	$T_A = 85 ^{\circ}C$			±10	μΛ
			'4070			±70	
			'4080			±80	
			'4095			±95	
			'4115			±115	
			'4125			±125	
			'4145			±145	
			'4165			±165	
			'4180			±180	
V _(BO)	Breakover voltage	$dv/dt = 750 \text{ V/ms}, R_{SOURCE} = 300 \Omega$	'4200			±200	V
· (BO)	2. oanoron ronago	aviati res ville, risource essell	'4220			±220	•
			'4240			±240	
			'4250			±250	
			'4265			±265	
			'4290			±290	
			'4300 '4370			±300	
			'4350			±350	
			'4395 '4499			±395	
			'4400			±400	
			'4070			±78	
			'4080			±88	
			'4095			±103	
			'4115			±124	
			'4125			±134	
			'4145			±154	
		1 / // 4000 // 1 //	'4165 '4169			±174	
		dv/dt ≤ ±1000V/μs, Linear voltage ramp,	'4180 '4180			±189	
V _(BO)	Impulse breakover	Maximum ramp value = ±500 V	'4200 '4200			±210	V
(20)	voltage	di/dt = ±20 A/µs, Linear current ramp,	'4220 '4240			±230	
		Maximum ramp value = ±10 A	'4240 '4250			±250	
			'4250 '4265			±261	
			4200			±276 ±301	
			4290			±301	
			4300			±311	
			4330			±302 ±408	
			4400			±413	
I _(BO)	Breakover current	$dv/dt = \pm 750 V/ms$, $R_{SOURCE} = 300 \Omega$	4400	±0.15		±0.6	А
V _T	On-state voltage	$I_T = \pm 5 \text{ A, t}_W = 100 \text{ µs}$		-		±3	V
I _H	Holding current	$I_T = \pm 5A$, di/dt = -/+30 mA/ms		±0.15		±0.6	Α
dv/dt	Critical rate of rise of off-state voltage	Linear voltage ramp, Maximum ramp value < 0.85V _{DRM}		±5			kV/μs
I _D	Off-state current	V _D = ±50 V	T _A = 85 °C			±10	μA

Electrical Characteristics, T_A = 25 °C (Unless Otherwise Noted) (Continued)

	Parameter		Test Conditions	5	Min.	Тур.	Max.	Unit
		f = 100 kHz,	$V_{d} = 1 \text{ V } \text{ rms}, V_{D} = 0,$	'4070 thru '4115		145	170	
				'4125 thru '4220		80	90	
				'4240 thru '4400		70	84	
		f = 100 kHz,	$V_d = 1 V \text{ rms}, V_D = -1V$	'4070 thru '4115		130	150	
				'4125 thru '4220		71	79	
				'4240 thru '4400		60	67	
C	Off-state capacitance	f = 100 kHz,	$V_{d} = 1 \text{ V ms}, V_{D} = -2 \text{ V}$	'4070 thru '4115		120	140	nΕ
C _{off}	Oir-state capacitance			'4125 thru '4220		65	74	pF
				'4240 thru '4400		55	62	
		f = 100 kHz,	$V_d = 1 V \text{ ms}, V_D = -50 V$	'4070 thru '4115		62	73	
				'4125 thru '4220		30	35	
				'4240 thru '4400		24	28	
		f = 100 kHz,	$V_d = 1 \text{ V } \text{ rms}, V_D = -100 \text{ V}$	'4125 thru '4220		28	33	
		(see Note 6)		'4240 thru '4400		22	26	

NOTE 6: To avoid possible voltage clipping, the '4125 is tested with $V_D = -98 \text{ V}$

Thermal Characteristics

Parameter		Test Conditions		Тур.	Max.	Unit
R _{θJA} Junction to free air thermal resistance	EIA/JESD51-3 PCB, I _T = I _{TSM(1000)} , T _A = 25 °C, (see Note 7)			113	°C/W	
θ	/A	265 mm x 210 mm populated line card, 4-layer PCB, $I_T = I_{TSM(1000)}$, $T_A = 25$ °C		50		O/W

NOTE 7: EIA/JESD51-2 environment and PCB has standard footprint dimensions connected with 5 A rated printed wiring track widths.

Parameter Measurement Information




Figure 1. Voltage-current Characteristic for T and R Terminals

All Mea surements are Referenced to the R Terminal

Typical Characteristics




Figure 2.








Figure 3.






Typical Characteristics





TI4HAE

Rating and Thermal Infomation



§ 100 70 Z_{oJA(t)} - Transient Thermal Impedance -50 40 30 20 15 10 7 5 4 $I_{TSM(t)}$ APPLIED FOR TIME t 3 **EIA/JESD51-2 ENVIRONMENT** 2 EIA/JESD51-3 PCB $T_A = 25 \, ^{\circ}C$ 1.5 0.1 10 100 1000 t - Power Duration - s

THERMAL IMPEDANCE vs
POWER DURATION

150

Figure 8.




Figure 9.




Figure 11.

APPLICATIONS INFORMATION

Deployment

These devices are two terminal overvoltage protectors. They may be used either singly to limit the voltage between two conductors (Figure 12) or in multiples to limit the voltage at several points in a circuit (Figure 13).




Figure 12. Two Point Protection




Figure 13. Multi-point Protection

In Figure 12, protector Th1 limits the maximum voltage between the two conductors to $\pm V_{(BO)}$. This configuration is normally used to protect circuits without a ground reference, such as modems. In Figure 13, protectors Th2 and Th3 limit the maximum voltage between each conductor and ground to the $\pm V_{(BO)}$ of the individual protector. Protector Th1 limits the maximum voltage between the two conductors to its $\pm V_{(BO)}$ value. If the equipment being protected has all its vulnerable components connected between the conductors and ground, then protector Th1 is not required.

Impulse Testing

To verify the withstand capability and safety of the equipment, standards require that the equipment is tested with various impulse wave forms. The table below shows some common values.

Standard	Peak Voltage Setting V	Voltage Waveform µs	Peak Current Value A	Current Waveform µs	TISP4xxxH3 25 °C Rating A	Series Resistance Ω
GR-1089-CORE	2500	2/10	500	2/10	500	0
GK-1007-COKE	1000	10/1000	100	10/1000	100	0
	1500	10/160	200	10/160	250	0
FCC Part 68	800	10/560	100	10/560	160	0
(March 1998)	1500	9/720 †	37.5	5/320 †	200	0
	1000	9/720 †	25	5/320 †	200	0
I3124	1500	0.5/700	37.5	0.2/310	200	0
ITU-T K.20/K.21	1500 4000	10/700	37.5 100	5/310	200	0

[†] FCC Part 68 terminology for the waveforms produced by the ITU-T recommendation K.21 10/700 impulse generator

If the impulse generator current exceeds the protector's current rating, then a series resistance can be used to reduce the current to the protector's rated value to prevent possible failure. The required value of series resistance for a given waveform is given by the following calculations. First, the minimum total circuit impedance is found by dividing the impulse generator's peak voltage by the protector's rated current. The impulse generator's fictive impedance (generators peak voltage divided by peak short circuit current) is then subtracted from the minimum total circuit impedance to give the required value of series resistance. In some cases, the equipment will require verification over a temperature range. By using the rated waveform values from Figure 11, the appropriate series resistor value can be calculated for ambient temperatures in the range of -40 °C to 85 °C.

BOURNS

APPLICATIONS INFORMATION

AC Power Testing

The protector can withstand currents applied for times not exceeding those shown in Figure 8. Currents that exceed these times must be terminated or reduced to avoid protector failure. Fuses, PTC (Positive Temperature Coefficient) resistors and fusible resistors are overcurrent protection devices which can be used to reduce the current flow. Protective fuses may range from a few hundred milliamperes to one ampere. In some cases, it may be necessary to add some extra series resistance to prevent the fuse opening during impulse testing. The current versus time characteristic of the overcurrent protector must be below the line shown in Figure 8. In some cases, there may be a further time limit imposed by the test standard (e.g. UL 1459 wiring simulator failure).

Capacitance

The protector characteristic off-state capacitance values are given for d.c. bias voltage, V_D , values of 0, -1 V, -2 V and -50 V. Where possible, values are also given for -100 V. Values for other voltages may be calculated by multiplying the $V_D = 0$ capacitance value by the factor given in Figure 6. Up to 10 MHz, the capacitance is essentially independent of frequency. Above 10 MHz, the effective capacitance is strongly dependent on connection inductance. In many applications, such as Figure 15 and Figure 17, the typical conductor bias voltages will be about -2 V and -50 V. Figure 7 shows the differential (line unbalance) capacitance caused by biasing one protector at -2 V and the other at -50 V.

Normal System Voltage Levels


The protector should not clip or limit the voltages that occur in normal system operation. For unusual conditions, such as ringing without the line connected, some degree of clipping is permissible. Under this condition, about 10 V of clipping is normally possible without activating the ring trip circuit.

Figure 10 allows the calculation of the protector V_{DRM} value at temperatures below 25 °C. The calculated value should not be less than the maximum normal system voltages. The TISP4265H3BJ, with a V_{DRM} of 200 V, can be used for the protection of ring generators producing 100 V r.m.s. of ring on a battery voltage of -58 V (Th2 and Th3 in Figure 17). The peak ring voltage will be 58 + 1.414*100 = 199.4 V. However, this is the open circuit voltage and the connection of the line, and its equipment will reduce the peak voltage. In the extreme case of an unconnected line, clipping the peak voltage to 190 V should not activate the ring trip. This level of clipping would occur at the temperature when the V_{DRM} has reduced to 190/200 = 0.95 of its 25 °C value. Figure 10 shows that this condition will occur at an ambient temperature of -22 °C. In this example, the TISP4265H3BJ will allow normal equipment operation provided that the minimum expected ambient temperature does not fall below -22 °C.

JESD51 Thermal Measurement Method

To standardize thermal measurements, the EIA (Electronic Industries Alliance) has created the JESD51 standard. Part 2 of the standard (JESD51-2, 1995) describes the test environment. This is a 0.0283 m³ (1 ft³) cube which contains the test PCB (Printed Circuit Board) horizontally mounted at the center. Part 3 of the standard (JESD51-3, 1996) defines two test PCBs for surface mount components; one for packages smaller than 27 mm (1.06 ″) on a side and the other for packages up to 48 mm (1.89 ″). The SMBJ measurements used the smaller 76.2 mm x 114.3 mm (3.0 ″ x 4.5 ″) PCB. The JESD51-3 PCBs are designed to have low effective thermal conductivity (high thermal resistance) and represent a worse case condition. The PCBs used in the majority of applications will achieve lower values of thermal resistance and so can dissipate higher power levels than indicated by the JESD51 values.

Typical Circuits






Figure 14. Modem Inter-wire Protection

Figure 15. Protection Module




Figure 16. ISDN Protection





Figure 17. Line Card Ring/Test Protection

MECHANICAL DATA

Recommended Printed Wiring Footprint



Device Symbolization Code

Devices will be coded as below. As the device parameters are symmetrical, terminal 1 is not identified.

Device	Symbolization
Device	Code
TISP4070H3BJ	4070H3
TISP4080H3BJ	4080H3
TISP4095H3BJ	4095H3
TISP4115H3BJ	4115H3
TISP4125H3BJ	4125H3
TISP4145H3BJ	4145H3
TISP4165H3BJ	4165H3
TISP4180H3BJ	4180H3
TISP4200H3BJ	4200H3
TISP4220H3BJ	4220H3
TISP4240H3BJ	4240H3
TISP4250H3BJ	4250H3
TISP4265H3BJ	4265H3
TISP4290H3BJ	4290H3
TISP4300H3BJ	4300H3
TISP4350H3BJ	4350H3
TISP4395H3BJ	4395H3
TISP4400H3BJ	4400H3

Carrier Information

Devices are shipped in one of the carriers below. Unless a specific method of shipment is specified by the customer, devices will be shipped in the most practical carrier. For production quantities, the carrier will be embossed tape reel pack. Evaluation quantities may be shipped in bulk pack or embossed tape.

Carrier	Order As
Embossed Tape Reeled	TISP4xxxH3BJR-S
Bulk Pack	TISP4xxxH3BJ-S

[&]quot;TISP" is a trademark of Bourns, Ltd., a Bourns Company, and is Registered in the U.S. Patent and Trademark Office. "Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries.

NOVEMBER 1997 - REVISED MARCH 2021

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Legal Disclaimer Notice



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf