

TISP4165H4BJ THRU TISP4200H4BJ, TISP4265H4BJ THRU TISP4350H4BJ

HIGH HOLDING CURRENT **BIDIRECTIONAL THYRISTOR OVERVOLTAGE PROTECTORS**

TISP4xxxH4BJ Overvoltage Protector Series

ITU-T K.20/21 Rating8 kV 10/700, 200 A 5/310


High Holding Current225 mA min.

Ion-Implanted Breakdown Region Precise and Stable Voltage Low Voltage Overshoot under Surge


Device	V _{DRM} V	V _(BO)
'4165	135	165
'4180	145	180
'4200	155	200
'4265	200	265
'4300	230	300
'4350	275	350

Rated for International Surge Wave **Shapes**

Wave Shape	Standard	I _{TSP} A
2/10 μs	GR-1089-CORE	500
8/20 μs	IEC 61000-4-5	300
10/160 μs	FCC Part 68	250
10/700 μs	ITU-T K.20/21	200
10/560 μs	FCC Part 68	160
10/1000 μs	GR-1089-CORE	100



Device Symbol



Terminals T and R correspond to the alternative line designators of A and B

Additional Information

Click these links for more information:











Agency Recognition

LIBRARY

Description		
UL	File Number: E215609	

Low Differential Capacitance.. 67 pF max.



Description

These devices are designed to limit overvoltages on the telephone line. Overvoltages are normally caused by a.c. power system or lightning flash disturbances which are induced or conducted on to the telephone line. A single device provides 2-point protection and is typically used for the protection of 2-wire telecommunication equipment (e.g., between the Ring and Tip wires for telephones and modems). Combinations of devices can be used for multi-point protection (e.g., 3-point protection between Ring, Tip and Ground).

The protector consists of a symmetrical voltage-triggered bidirectional thyristor. Overvoltages are initially clipped by breakdown clamping until the voltage rises to the breakover level, which causes the device to crowbar into a low-voltage on state. This low-voltage on state causes the current resulting from the overvoltage to be safely diverted through the device. The high crowbar holding current helps prevent d.c. latchup as the diverted current subsides.

How to Order

Device	Package	Carrier	Order As
TISP4xxxH4BJ	BJ (J-Bend DO-214AA/SMB)	Embossed Tape Reeled	TISP4xxxH4BJR-S
TISF 4XXXII4BS	D3 (3-Delia DO-214AA/3IVID)	Bulk Pack	TISP4xxxH4BJ-S

Insert xxx value corresponding to protection voltages of 165 through to 350.



WARNING Cancer and Reproductive Harm www.P65Warnings.ca.gov

NOVEMBER 1997 - REVISED JULY 2019 *RoHS Directive 2015/863, Mar 31, 2015 and Annex. Specifications are subject to change without notice.

TISP4xxxH4BJ Overvoltage Protector Series

BOURNS

Description

This TISP4xxxH4BJ range consists of six voltage variants to meet various maximum system voltage levels (135 V to 275 V). They are guaranteed to voltage limit and withstand the listed international lightning surges in both polarities. These high (H) current protection devices are in a plastic package SMBJ (JEDEC DO-214AA with J-bend leads) and supplied in embossed carrier reel pack. For alternative voltage and holding current values, consult the factory. For lower rated impulse currents in the SMB package, the 50 A 10/1000 TISP4xxxM3BJ series is available.

Absolute Maximum Ratings, TA = 25 °C (Unless Otherwise Noted)

Rating			Value	Unit
Repetitive peak off-state voltage, (see Note 1)	'4165 '4180 '4200 '4265 '4300 '4350	$V_{ m DRM}$	±135 ±145 ±155 ±200 ±230 ±275	٧
Non-repetitive peak on-state pulse current (see Notes 2, 3 and 4)				
2/10 μs (GR-1089-CORE, 2/10 μs voltage wave shape)			500	
8/20 μs (IEC 61000-4-5, 1.2/50 μs voltage, 8/20 current combination wave gene	rator)		300	
10/160 μs (FCC Part 68, 10/160 μs voltage wave shape)			250	
5/200 µs (VDE 0433, 10/700 µs voltage wave shape)	I _{TSP}	220	Α	
0.2/310 µs (l3124, 0.5/700 µs voltage wave shape)		200	A	
5/310 μs (ITU-T K.20/21, 10/700 μs voltage wave shape)			200	
5/310 µs (FTZ R12, 10/700 µs voltage wave shape)	İ	200		
10/560 μs (FCC Part 68, 10/560 μs voltage wave shape)			160	
10/1000 μs (GR-1089-CORE, 10/1000 μs voltage wave shape)			100	
Non-repetitive peak on-state current (see Notes 2, 3 and 5)				
20 ms (50 Hz) full sine wave			55	
16.7 ms (60 Hz) full sine wave		I_{TSM}	60	Α
1000 s 50 Hz/60 Hz a.c.			2.1	
Initial rate of rise of on-state current, Exponential current ramp, Maximum ramp value < 2	200 A	di _T /dt	400	A/µs
Junction temperature		TJ	-40 to +150	°C
Storage temperature range		T _{stg}	-65 to +150	°C

NOTES: 1. See Applications Information and Figure 10 for voltage values at lower temperatures.

- 2. Initially, the TISP4xxxH4BJ must be in thermal equilibrium with $T_J = 25$ °C.
- 3. The surge may be repeated after the TISP4xxxH4BJ returns to its initial conditions.
- 4. See Applications Information and Figure 11 for current ratings at other temperatures.
- 5. EIA/JESD51-2 environment and EIA/JESD51-3 PCB with standard footprint dimensions connected with 5 A rated printed wiring track widths. See Figure 8 for the current ratings at other durations. Derate current values at -0.61 %/°C for ambient temperatures above 25 °C.

Electrical Characteristics, T_A = 25 °C (Unless Otherwise Noted)

	Parameter	Test Conditions			Max.	Unit
I _{DRM}	Repetitive peak off- state current	$V_{D} = V_{DRM}$ $T_{A} = 25 ^{\circ}\text{C}$ $T_{A} = 85 ^{\circ}\text{C}$			±5 ±10	μΑ
V _(BO)	Breakover voltage	$dv/dt = \pm 750V/ms, R_{SOURCE} = 300 \ \Omega$			±165 ±180 ±200 ±265 ±300 ±350	V
V _(BO)	Impulse breakover voltage	dv/dt ≤ ±1000V/µs, Linear voltage ramp, 4180 Maximum ramp value = ±500 V 4200 di/dt = ±20 A/µs, Linear current ramp, 4265 Maximum ramp value = ±10 A 4300 4350			±174 ±189 ±210 ±276 ±311 ±363	V
I _(BO)	Breakover current	$dv/dt = \pm 750V/ms$, $R_{SOURCE} = 300 \Omega$			±0.8	Α
V _T	On-state voltage	$I_T = \pm 5 \text{ A}, t_W = 100 \mu\text{s}$			±3	V
I _H	Holding current	$I_T = \pm 5 \text{ A}, \text{ di/dt} = -/+30 \text{ mA/ms}$			±0.8	Α
dv/dt	Critical rate of rise of off-state voltage	Linear voltage ramp, Maximum ramp value < 0.85V _{DRM}				kV/μs
I _D	Off-state current	$V_D = \pm 50 \text{ V}$ $T_A = 85$	С		±10	μA
C _{off}	Off-state capacitance	$ \begin{aligned} & \text{f} = 100 \text{ kHz}, & \text{V}_{\text{d}} = 1 \text{ V ms}, \text{V}_{\text{D}} = 0 & \text{'4165 thru '42} \\ & \text{'4265 thru '43} \\ & \text{f} = 100 \text{ kHz}, & \text{V}_{\text{d}} = 1 \text{ V ms}, \text{V}_{\text{D}} = -1 \text{ V} & \text{'4165 thru '42} \\ & \text{'4265 thru '43} \\ & \text{f} = 100 \text{ kHz}, & \text{V}_{\text{d}} = 1 \text{ V ms}, \text{V}_{\text{D}} = -2 \text{ V} & \text{'4165 thru '42} \\ & \text{'4265 thru '43} \\ & \text{f} = 100 \text{ kHz}, & \text{V}_{\text{d}} = 1 \text{ V ms}, \text{V}_{\text{D}} = -50 \text{ V} & \text{'4165 thru '42} \\ & \text{'4265 thru '43} \\ & \text{f} = 100 \text{ kHz}, & \text{V}_{\text{d}} = 1 \text{ V ms}, \text{V}_{\text{D}} = -100 \text{ V} & \text{'4165 thru '42} \\ & \text{(see Note 6)} & \text{'4265 thru '43} \end{aligned} $	50 50 50 50 50 50 50 50	80 70 71 60 65 55 30 24 28 22	90 84 79 67 74 62 35 28 33 26	pF

NOTE 6: To avoid possible voltage clipping, the '4125 is tested with $V_D = -98 \text{ V}$

Thermal Characteristics

	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
		EIA/JESD51-3 PCB, I _T = I _{TSM(1000)} , T _A = 25 °C, (see Note 7)			113	°C /W
ТθЈА		265 mm x 210 mm populated line card, 4-layer PCB, $I_T = I_{TSM(1000)}$, $T_A = 25$ °C		50		0 / 11

NOTE 7: EIA/JESD51-2 environment and PCB has standard footprint dimensions connected with 5 A rated printed wiring track widths.

Parameter Measurement Information








Figure 1. Voltage-current Characteristic for T and R Terminals All Measurements are Referenced to the R Terminal

Typical Characteristics












NOVEMBER 1997 - REVISED JULY 2019


Typical Characteristics





Typical Characteristics






IMPULSE RATING

AMBIENT TEMPERATURE

TC4HAA

V_{DRM} DERATING FACTOR vs



500 400 IEC 1.2/50, 8/20 Impulse Current - A 300 FCC 10/160 250 ITU-T 10/700 200 FCC 10/560 150 120 **BELLCORE 10/1000** 100 90 -40 -30 -20 -10 0 10 20 30 40 50 60 70 80

BELLCORE 2/10

Figure 11.

T_A - Ambient Temperature - °C

NOVEMBER 1997 - REVISED JULY 2019

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

Figure 10.

700 600

APPLICATIONS INFORMATION

Deployment

These devices are two terminal overvoltage protectors. They may be used either singly to limit the voltage between two conductors (Figure 12) or in multiples to limit the voltage at several points in a circuit (Figure 13).




Figure 12. Two Point Protection




Figure 13. Multi-point Protection

In Figure 12, protector Th1 limits the maximum voltage between the two conductors to $\pm V_{(BO)}$. This configuration is normally used to protect circuits without a ground reference, such as modems. In Figure 13, protectors Th2 and Th3 limit the maximum voltage between each conductor and ground to the $\pm V_{(BO)}$ of the individual protector. Protector Th1 limits the maximum voltage between the two conductors to its $\pm V_{(BO)}$ value. If the equipment being protected has all its vulnerable components connected between the conductors and ground, then protector Th1 is not required.

Impulse Testing

To verify the withstand capability and safety of the equipment, standards require that the equipment is tested with various impulse wave forms. The table below shows some common values.

Standard	Peak Voltage Setting V	Voltage Waveform µs	Peak Current Value A	Current Waveform µs	TISP4xxxH4 25 C Rating A	Series Resistance Ω
GR-1089-CORE	2500	2/10	500	2/10	500	0
GK-1009-COKE	1000	10/1000	100	10/1000	100	O
	1500	10/160	200	10/160	250	0
FCC Part 68	800	10/560	100	10/560	160	0
(March 1998)	1500	9/720 †	37.5	5/320 †	200	0
	1000	9/720 †	25	5/320 †	200	0
I3124	1500	0.5/700	37.5	0.2/310	200	0
ITU-T K.20/K.21	1500 4000	10/700	37.5 100	5/310	200	0

[†] FCC Part 68 terminology for the waveforms produced by the ITU-T recommendation K.21 10/700 impulse generator

If the impulse generator current exceeds the protector's current rating, then a series resistance can be used to reduce the current to the protector's rated value to prevent possible failure. The required value of series resistance for a given waveform is given by the following calculations. First, the minimum total circuit impedance is found by dividing the impulse generator's peak voltage by the protector's rated current. The impulse generator's fictive impedance (generator's peak voltage divided by peak short circuit current) is then subtracted from the minimum total circuit impedance to give the required value of series resistance. In some cases, the equipment will require verification over a temperature range. By using the rated waveform values from Figure 11, the appropriate series resistor value can be calculated for ambient temperatures in the range of -40 °C to 85 °C.

TISP4xxxH4BJ Overvoltage Protector Series

BOURNS

APPLICATIONS INFORMATION

AC Power Testing

The protector can withstand currents applied for times not exceeding those shown in Figure 8. Currents that exceed these times must be terminated or reduced to avoid protector failure. Fuses, PTC (Positive Temperature Coefficient) resistors and fusible resistors are overcurrent protection devices which can be used to reduce the current flow. Protective fuses may range from a few hundred milliamperes to one ampere. In some cases, it may be necessary to add some extra series resistance to prevent the fuse opening during impulse testing. The current versus time characteristic of the overcurrent protector must be below the line shown in Figure 8. In some cases, there may be a further time limit imposed by the test standard (e.g. UL 1459 wiring simulator failure).

Capacitance

The protector characteristic off-state capacitance values are given for d.c. bias voltage, V_D , values of 0, -1 V, -2 V and -50 V. Where possible, values are also given for -100 V. Values for other voltages may be calculated by multiplying the $V_D = 0$ capacitance value by the factor given in Figure 6. Up to 10 MHz, the capacitance is essentially independent of frequency. Above 10 MHz, the effective capacitance is strongly dependent on connection inductance. In many applications, such as Figure 15 and Figure 17, the typical conductor bias voltages will be about -2 V and -50 V. Figure 7 shows the differential (line unbalance) capacitance caused by biasing one protector at -2 V and the other at -50 V.

Normal System Voltage Levels


The protector should not clip or limit the voltages that occur in normal system operation. For unusual conditions, such as ringing without the line connected, some degree of clipping is permissible. Under this condition, about 10 V of clipping is normally possible without activating the ring trip circuit. Figure 10 allows the calculation of the protector V_{DRM} value at temperatures below 25 °C. The calculated value should not be less than the maximum normal system voltages. The TISP4265H4BJ, with a V_{DRM} of 200 V, can be used for the protection of ring generators producing 100 V r.m.s. of ring on a battery voltage of -58 V (Th2 and Th3 in Figure 17). The peak ring voltage will be 58 + 1.414*100 = 199.4 V. However, this is the open circuit voltage and the connection of the line and its equipment will reduce the peak voltage. In the extreme case of an unconnected line, clipping the peak voltage to 190 V should not activate the ring trip. This level of clipping would occur at the temperature when the V_{DRM} has reduced to 190/200 = 0.95 of its 25 °C value. Figure 10 shows that this condition will occur at an ambient temperature does not fall below -22 °C. In this example, the TISP4265H4BJ will allow normal equipment operation provided that the minimum expected ambient temperature does not fall below -22 °C.

JESD51 Thermal Measurement Method

To standardize thermal measurements, the EIA (Electronic Industries Alliance) has created the JESD51 standard. Part 2 of the standard (JESD51-2, 1995) describes the test environment. This is a 0.0283 m³ (1 ft³) cube which contains the test PCB (Printed Circuit Board) horizontally mounted at the center. Part 3 of the standard (JESD51-3, 1996) defines two test PCBs for surface mount components; one for packages smaller than 27 mm on a side and the other for packages up to 48 mm. The SMBJ measurements used the smaller 76.2 mm x 114.3 mm (3.0 " x 4.5 ") PCB. The JESD51-3 PCBs are designed to have low effective thermal conductivity (high thermal resistance) and represent a worse case condition. The PCBs used in the majority of applications will achieve lower values of thermal resistance and so can dissipate higher power levels than indicated by the JESD51 values.

APPLICATIONS INFORMATION

Typical Circuits






Figure 14. Modem Inter-wire Protection

Figure 15. Protection Module




Figure 16. ISDN Protection





Figure 17. Line Card Ring/Test Protection

TISP4xxxH4BJ Overvoltage Protector Series

BOURNS®

MECHANICAL DATA

Recommended Printed Wiring Footprint



MDXXBI

Device Symbolization Code

Devices will be coded as below. As the device parameters are symmetrical, terminal 1 is not identified.

Device	Symbolization Code
TISP4165H4BJ	4165H4
TISP4180H4BJ	4180H4
TISP4200H4BJ	4200H4
TISP4265H4BJ	4265H4
TISP4300H4BJ	4300H4
TISP4350H4BJ	4350H4

Carrier Information

Devices are shipped in one of the carriers below. Unless a specific method of shipment is specified by the customer, devices will be shipped in the most practical carrier. For production quantities, the carrier will be embossed tape reel pack. Evaluation quantities may be shipped in bulk pack or embossed tape.

Carrier	Order As
Embossed Tape Reel Pack	TISP4xxxH4BJR-S
Bulk Pack	TISP4xxxH4BJ-S

BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 885 877 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

"TISP" is a trademark of Bourns, Ltd., a Bourns Company, and is Registered in the U.S. Patent and Trademark Office.

"Bourns" is a registered trademark of Bourns, Inc. in the U.S. and other countries.

NOVEMBER 1997 - REVISED JULY 2019

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Legal Disclaimer Notice



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf