


# MATERIAL DECLARATION SHEET



Material Number	3339 ( 250Ω to 25KΩ) LF			
Product Line	Trimmer			
Compliance Date	2/17/2005			
RoHS Compliant	Yes DC 509	MSL		

No.	Construction Element (subpart)	Homogeneous Material	Material weight [g]	Homogeneous Material	CASRN	Materials Mass %	Material Mass % of total unit wt.	Subpart mass of total wt. (%)
				Substances	if applicable			
1	Contact Spring	Ni/Ag	0.0056	Copper	7440-50-8	59	0.6106	1.03
				Nickel	7440-02-0	12	0.1242	
				Zinc	7440-66-6	29	0.3001	
2	Shaft	PBT	0.0168	Polybutylene terephthalate	30965-26-5	55	1.7076	3.10
				Glass fiber	65997-17-3	30	0.9314	
				Antimony trioxide	1309-64-4	4	0.1242	
				Brominated FR (TBBPA polycarbonate polymer)	trade secret	11	0.3415	
3	Rotor	Nylon	0.0265	Polyamide 66	32131-17-2	60	2.9385	4.90
				Glass fiber	65997-17-3	30	1.4692	
				Tetrafluoroethylene polymer	9002-84-0	8	0.3918	
4	Seal Ring	Rubber	0.0031	Silicon rubber	63394-02-5	100	0.5729	0.57
5	Cover	PBT	0.139	Polybutylene terephthalate	30965-26-5	49	12.5873	25.69
				Glass fiber	65997-17-3	35	8.9909	
				Brominated flame retardant	Trade secret	10	2.5688	
				Antimony trioxide	1309-64-4	6	1.5413	
6	Substrate	Ceramic	0.2017	Aluminum oxide	1344-28-1	96	35.7849	37.28
				Silicon dioxide	7631-86-9	2	0.7455	
				Magnesium oxide	1309-48-4	1	0.3728	
				Calcium oxide	1305-78-8	1	0.3728	

# MATERIAL DECLARATION SHEET



7	Drive Wheel	Rubber	0.0022	Silicon Rubber	63394-02-5	100	0.4066	0.41
8	Insert	Nylon	0.0223	Polyamide 66	32131-17-2	60	2.4727	4.12
				Glass fiber	65997-17-3	30	1.2364	
				Carbon black	7440-44-0	2	0.0824	
				Tetrafluoroethylene polymer	9002-84-0	8	0.3297	
9	Potting	Epoxy	0.0625	Cycloaliphatic epoxide	trade secret	40	4.6202	11.55
				Polyetherpolyol resins	39072-02-1	15	1.7326	
				Silicon dioxide	67762-90-7	25	2.8876	
				Hydrated alumina	21645-51-2	20	2.3101	
10	Termination Ink	Ink	0.002	Silver	7440-22-4	59	0.2181	0.37
				Palladium	7440-05-3	24	0.0887	
				Lead oxide glass	1317-36-8	9	0.0333	
				Bismuth trioxide	1304-76-3	6	0.0222	
				Silicon dioxide	7631-86-9	1	0.0037	
				Barium oxide	1304-28-5	1	0.0037	
11	Resistive Ink	Ink	0.0043	Ruthenium Dioxide	12036-10-1	35	0.2781	0.79
				Calcium Silicate borate glass	59794-15-9	46	0.3656	
				Silver	7440-22-4	7	0.0556	
				Titanium dioxide	13463-67-7	5	0.0397	
				Manganese dioxide	1313-13-9	6	0.0477	
				Cuprous oxide	1317-39-1	1	0.0079	
12	Terminals	Copper	0.0517	Copper	7440-50-8	100	9.5546	10.18
		Plating	0.0034	Tin	7440-31-5	100	0.6283	
		Total Weight	0.5411					

# MATERIAL DECLARATION SHEET



13*	Adaptor	PBT	0.318	Polybutylene terephthalate	30965-26-5	49	18.1376	37.02
				Glass fiber	65997-17-3	35	12.9554	
				Brominated flame retardant	Trade secret	10	3.7015	
				Antimony trioxide	1309-64-4	6	2.2209	
		Total Weight	0.8591					

**This Document was updated on: 8-11-2011**

**Important remarks:**

1. It is the responsibility of the user to verify they are accessing the latest version.
2. No. 13\* included for terminal style S and W only.
3. Non RoHS Compliant versions available without the LF suffix
4. RoHS exemption – 7(c)-I – Electrical and electronic components containing lead in a glass or ceramic...