

## Moisture / Reflow Sensitivity Classification

Moisture/Reflow Sensitivity Classification (MSL), as defined in IPC/JEDEC Standard J-STD-020, is not offered as part of Bourns® Multifuse® Polymer PTC standard product ratings or packaging labels as the baking process involved is not applicable to heat sensitive components such as PPTC resettable fuses. However, as a courtesy to address frequent customer requests, Bourns recommends that Multifuse® Polymer PTC passive components be handled according to the Floor Life and MSL Classification tables below.

Bourns has determined that if IPC/JEDEC Standard J-STD-020 were to be applied to Bourns® Multifuse® Polymer PTC products:

1. The Bourns® Multifuse® model series with an MSL Classification level 1 would have a moisture sensitivity rating equivalent to IPC/JEDEC Standard J-STD-020 MSL 1, specifying an unlimited floor life under the conditions 30 °C / 85 % RH; and
2. The Bourns® Multifuse® model series with an MSL Classification level 2a would have a moisture sensitivity rating equivalent to IPC/JEDEC Standard J-STD-020 MSL 2a.

An IPC/JEDEC Standard J-STD-020 MSL 2a rating means:

1. These components are sensitive to moisture.
2. Once these components are removed from the moisture barrier bag packaging at factory ambient temperature of  $\leq 30$  °C/60 % RH, they must be assembled within 4 weeks from the date the bag was opened.
3. If the above conditions are exceeded, a rebake may be necessary prior to assembly to ensure component compliance with stated performance specifications. Recommended re-bake condition: 40 °C / 5 % RH for 29 days; or contact Bourns.

Floor Life		
MSL Classification	Time	Condition
1	Unlimited	$\leq 30$ °C / 85 % RH
2	1 year	$\leq 30$ °C / 60 % RH
2a	4 weeks	
3	168 hours	
4	72 hours	
5	48 hours	
5a	24 hours	
6	Time on Label (TOL)	

MSL Classification									
Structure	Model Series	1	2	2a	3	4	5	5a	6
Surface Mount	MF-ASML/X			•					
	MF-FSMF	•							
	MF-FSML/X			•					
	MF-FSHT	•							
	MF-PSMF	•							
	MF-PSML			•					
	MF-PSML/X			•					
	MF-PSHT	•							
	MF-NSMF	•							
	MF-NSML			•					
	MF-NSML/X			•					
	MF-NSHT	•							
	MF-USMF	•							
	MF-USML			•					
	MF-USML/X			•					
	MF-USHT	•							
	MF-MSMF	•							
	MF-MSHT	•							
	MF-SMDF	•							
	MF-LSMF	•							
	MF-GSMF	•							
	MF-SM	•							
	MF-SMHT	•							
	MF-SM/250	•							
	MF-SM/250V	•							
	MF-SD/250	•							

MSL Classification									
Structure	Model Series	1	2	2a	3	4	5	5a	6
Radial Leaded Through-Hole	MF-R	•							
	MF-RG	•							
	MF-RHS	•							
	MF-RHT	•							
	MF-RM	•							
	MF-RX/72	•							
	MF-RX/250	•							
Battery Strap	MF-LR	•							
	MF-LS	•							
	MF-S	•							
	MF-SVS	•							
	MF-VS	•							
	MF-VS Narrow Body	•							

**BOURNS®**

Asia-Pacific: Tel: +886-2 2562-4117 • Email: [asiacus@bourns.com](mailto:asiacus@bourns.com)

Europe: Tel: +36 88 885 877 • Email: [eurocus@bourns.com](mailto:eurocus@bourns.com)

Mexico: Tel: +52 614 478 0400 • Email: [mexicus@bourns.com](mailto:mexicus@bourns.com)

The Americas: Tel: +1-951 781-5500 • Email: [americus@bourns.com](mailto:americus@bourns.com)  
[www.bourns.com](http://www.bourns.com)