



# Test Report


BOURNS INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, U. S. A.

Report No. : CE/2005/42628B  
Date : 2005/04/15  
Page : 1 of 4

**The following merchandise was (were) submitted and identified by the client as :**

<u>Type of Product</u>	:	CDNBS08-SRDA3. 3-4
<u>Sample Received</u>	:	2005/04/13
<u>Testing Date</u>	:	2005/04/13 TO 2005/04/15

**Test Result** : - Please see the next page -



**Daniel Yeh, M.R. / Operation Manager**  
Signed for and on behalf of  
**SGS TAIWAN LTD.**

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification, and Jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company. 此報告是遵循本公司訂定之通用服務條款所製作發放。請注意此條款列印於背面。將本公司之義務、免責、管轄權皆明確規範之。此報告結果除非另有說明僅對檢驗之樣品負責。本報告未經本公司書面許可，不可部份複製。

TW 1748064

1001



# Test Report

BOURNS INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, U. S. A.

Report No. : CE/2005/42628B  
Date : 2005/04/15  
Page : 2 of 4

## Test Result

PART NAME NO.1 : MIXED ALL PARTS (PLEASE REFER TO THE PHOTO ATTACHED)

Test Item (s):	Unit	Method	MDL	Result
				No.1
Monobromobiphenyl	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl	%		0.0005	N.D.
Tribromobiphenyl	%		0.0005	N.D.
Tetrabromobiphenyl	%		0.0005	N.D.
Pentabromobiphenyl	%		0.0005	N.D.
Hexabromobiphenyl	%		0.0005	N.D.
Heptabromobiphenyl	%		0.0005	N.D.
Octabromobiphenyl	%		0.0005	N.D.
Nonabromobiphenyl	%		0.0005	N.D.
Decabromobiphenyl	%		0.0005	N.D.
<b>Total PBBs (Polybrominated biphenyls)/Sum of above</b>	%	-	N.D.	
Monobromobiphenyl ether	%	With reference to USEPA3540C or USEPA3550C. Analysis was performed by HPLC/DAD, LC/MS or GC/MS. (prohibited by 2002/95/EC (RoHS), 83/264/EEC, and 76/769/EEC)	0.0005	N.D.
Dibromobiphenyl ether	%		0.0005	N.D.
Tribromobiphenyl ether	%		0.0005	N.D.
Tetrabromobiphenyl ether	%		0.0005	N.D.
Pentabromobiphenyl ether	%		0.0005	N.D.
Hexabromobiphenyl ether	%		0.0005	N.D.
Heptabromobiphenyl ether	%		0.0005	N.D.
Octabromobiphenyl ether	%		0.0005	N.D.
Nonabromobiphenyl ether	%		0.0005	N.D.
Decabromobiphenyl ether	%		0.0005	N.D.
<b>Total PBBEs(PBDEs) (Polybrominated biphenyl ethers)/Sum of above</b>	%	-	N.D.	

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification, and Jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company. 此報告是遵循本公司訂定之通用服務條款所製作發放。請注意此條款列印於背面，將本公司之義務，免責，管轄權皆明確規範之。此報告結果除非另有說明僅對檢驗之樣品負責。本報告未經本公司書面許可，不可部份複製。

TW 1748065



## Test Report

BOURNS INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, U. S. A.

Report No. : CE/2005/42628B  
Date : 2005/04/15  
Page : 3 of 4

Test Item (s):	Unit	Method	MDL	Result
				No. 1
Chromium VI (Cr+6)	ppm	UV-VIS after reference to US EPA 3060A.	2	N.D.
Cadmium (Cd)	ppm	ICP-AES after reference to EN 1122, method B:2001 or other acid digestion.	2	N.D.
Mercury (Hg)	ppm	ICP-AES after reference to US EPA 3052 or other acid digestion.	2	N.D.
Lead (Pb)	ppm	ICP-AES after reference to US EPA 3050B or other acid digestion.	2	N.D.

- NOTE: (1) N.D. = Not detected (<MDL)  
(2) ppm = mg/kg  
(3) MDL = Method Detection Limit  
(4) " - " = No Regulation

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification, and Jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company. 此報告是遵循本公司訂定之通用服務條款所製作發給。請注意此條款列印於背面，將本公司之義務、免責、管轄權皆明確規範之。此報告結果除非另有說明僅對檢驗之樣品負責。本報告未經本公司書面許可，不可部份複製。

TW 1748066

SGS Taiwan Ltd.  
台灣檢驗科技股份有限公司

No. 33 Wu Chyuan Road, Wuku Industrial Zone, Taipei County, Taiwan. / 台北縣五股工業區五權路33號  
t (886-2) 2299-3939 f (886-2) 2299-3237 www.tw.sgs.com

Member of SGS Group



## Test Report

BOURNS INC.  
1200 COLUMBIA AVE. RIVERSIDE, CA 92507, U. S. A.

Report No. : CE/2005/42628B  
Date : 2005/04/15  
Page : 4 of 4

**CE/2005/  
42628B**



This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification, and Jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company. 此報告是遵循本公司訂定之通用服務條款所製作發放。請注意此條款列印於背面，將本公司之義務、免責、管轄權皆明確規範之。此報告結果除非另有說明僅對檢驗之樣品負責。本報告未經本公司書面許可，不可部份複製。

TW 1748067

SGS Taiwan Ltd.  
台灣檢驗科技股份有限公司

No. 33 Wu Chyuan Road, Wuku Industrial Zone, Taipei County, Taiwan. /台北縣五股工業區五權路33號

t (886-2) 2299-3939

f (886-2) 2299-3237

www.tw.sgs.com

Member of SGS Group