



BOURNS®

Features

- Available in E12 series
- Unit height of 3 mm
- Current up to 3 A
- RoHS compliant*

Applications

- Input/output of DC-DC converters
- Power supplies for:
 - Portable communication equipment
 - Camcorders
 - LCD TVs
 - Radios

SRR6603 Series - Shielded Power Inductors

Electrical Specifications @ 25 °C

Bourns Part No.	Inductance 100 KHz		Q Min.	Test Frequency (Hz) Q		SRF Nom. (MHz)	RDC Max. (Ω)	I rms (A) Max.	I sat (A) Typ.
	μH	Tol. %		L/0.1 V	Q				
SRR6603-1R0ML	1.0	±20	10	100K	500K	70	0.040	3.00	1.200
SRR6603-1R5ML	1.5	±20	20	100K	500K	70	0.045	2.80	0.920
SRR6603-2R2ML	2.2	±20	25	100K	500K	70	0.050	1.80	0.800
SRR6603-3R3ML	3.3	±20	40	100K	200K	60	0.055	1.60	0.620
SRR6603-4R7ML	4.7	±20	40	100K	200K	60	0.060	1.40	0.500
SRR6603-6R8ML	6.8	±20	40	100K	200K	50	0.065	1.20	0.400
SRR6603-100ML	10.0	±20	40	100K	200K	38	0.075	1.00	0.320
SRR6603-150ML	15.0	±20	40	100K	100K	33	0.090	0.80	0.260
SRR6603-220ML	22.0	±20	40	100K	100K	25	0.110	0.70	0.240
SRR6603-330ML	33.0	±20	40	100K	100K	20	0.190	0.60	0.160
SRR6603-470ML	47.0	±20	40	100K	100K	20	0.230	0.50	0.140
SRR6603-680ML	68.0	±20	40	100K	100K	15	0.290	0.40	0.120
SRR6603-101ML	100.0	±20	40	100K	100K	10	0.480	0.30	0.100
SRR6603-151ML	150.0	±20	40	100K	100K	9	0.590	0.26	0.080
SRR6603-221ML	220.0	±20	40	100K	100K	6	0.770	0.22	0.070
SRR6603-331ML	330.0	±20	40	100K	100K	5	1.400	0.20	0.050
SRR6603-471ML	470.0	±20	40	100K	100K	4	1.800	0.19	0.045
SRR6603-561ML	560.0	±20	40	100K	100K	3.5	2.000	0.185	0.043
SRR6603-681ML	680.0	±20	40	100K	100K	3	2.200	0.18	0.040
SRR6603-102ML	1000.0	±20	40	100K	100K	2	3.400	0.15	0.028
SRR6603-152ML	1500.0	±20	50	100K	100K	2	4.200	0.12	0.024
SRR6603-222ML	2200.0	±20	50	100K	100K	2	8.500	0.10	0.020
SRR6603-332ML	3300.0	±20	50	100K	100K	1	11.00	0.08	0.018
SRR6603-472ML	4700.0	±20	50	100K	100K	1	13.90	0.06	0.014
SRR6603-682ML	6800.0	±20	50	100K	100K	1	25.00	0.04	0.012
SRR6603-103ML	10000.0	±20	50	100K	100K	0.8	32.80	0.02	0.010

Additional Information

Click these links for more information:



PRODUCT
SELECTOR


TECHNICAL
LIBRARY

INVENTORY

SAMPLES


CONTACT

Recommended Layout



DIMENSIONS: MM
(INCHES)

Schematic



CALIFORNIA WARNING: Can expose you to lead, a carcinogen and reproductive toxicant.
See www.P65Warnings.ca.gov

*RoHS Directive 2015/863, Mar 31, 2015 and Annex.

Specifications are subject to change without notice.


Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

SRR6603 Series - Shielded Power Inductors

BOURNS®


Soldering Profile



Profile Feature	Pb-Free Assembly
Preheat / Soak:	
Temperature Min. (T_{smin})	150 °C
Temperature Max. (T_{smax})	200 °C
Time (t_s) from (T_{smin} to T_{smax})	60~120 seconds
Ramp Up Rate (T_L to T_p)	3 °C / second max.
Liquidous Temperature (T_L)	217 °C
Time (t_L) maintained above T_L	60~150 seconds
Classification Temperature (T_c)	250 °C
Time (t_p) within 5 °C of the specified classification temperature (T_c)	< 30 seconds
Ramp Down Rate (T_p to T_L)	6 °C / second max.
Time 25 °C to Peak Temperature	8 minutes max.

NOTE: The product has been tested under this reflow condition. Deviations from this, especially higher temperatures or longer durations, could impact performance.

Packaging Specifications



REV. 02/26

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., IATF 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <http://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <http://www.bourns.com/docs/Legal/disclaimer.pdf>