

Features

- Low thermal resistant ceramic core
- E24 resistance values
- RoHS compliant*
- Wide power range (1~10 W)
- Coating material meets UL 94V-0 requirements

Applications

- Smart meters
- Renewable energy
- Industrial
- Power supplies/chargers
- Lighting
- Instruments/gauges
- White goods

W Series Wirewound Power Resistor

| Electrical Characteristics | |
|---|-------------|
| Resistance Range Tolerance | • |
| Operating Temperature Temperature Coefficient Maximum Voltage | ±300 ppm/°C |

Non-inductive version is available upon request.

Popular Resistance Values

| Code | R Value |
|------|---------|
| 15R0 | 15 Ω |
| 22R0 | 22 Ω |
| 33R0 | 33 Ω |
| 39R0 | 39 Ω |
| 47R0 | 47 Ω |

| Code | R Value |
|------|---------|
| 56R0 | 56 Ω |
| 82R0 | 82 Ω |
| 1000 | 100 Ω |
| 1200 | 120 Ω |
| 1500 | 150 Ω |

Other E24 resistance values available upon request.

Physical Characteristics

| Resistor | Low thermal resistant ceramic core |
|------------------|---|
| Lead Wire | Tin-plated copper wire |
| Coating Material | • |

Environmental Characteristics

| Test | Conditions | Specification | |
|---|---|-----------------------|--|
| Short Time Overload | 2.5 times rated voltage for 5 seconds. | ΔR/R≤±(2 % ± 0.05 Ω) | |
| Solderability | 245 ±3 °C for 2.5 ±0.5 seconds. | Over 95 % coverage | |
| Resistance to Solder Heat | 260 ±5 °C for 10 ± 1 seconds. | ΔR/R≤±(1 % + 0.05 Ω) | |
| Dielectric Strength | electric Strength Test voltage >500 Vrms for >1 minute. | | |
| Insulation Resistance Test voltage >500 Vrms for 1 minute. | | >10 ⁹ Ω | |
| 40 ±2 °C, 90 to 95 %. Load Life Humidity 1.5 hours ON, 0.5 hours OFF for 1000 hours at rated power. | | ΔR/R≤ ±(5 % + 0.05 Ω) | |
| 70 ±2 °C. Load Life 1.5 hours ON, 0.5 hours OFF 1000 hours at rated power. | | ΔR/R≤±(5 % + 0.05 Ω) | |

How to Order

W 3 M 22R0 J Product Series -W = Wirewound Power Rating —

1 = 1 Watt

2 = 2 Watts

3 = 3 Watts

5 = 5 Watts

7 = 7 Watts 9 = 9 Watts 10 = 10 Watts Pin Style -M = Axial Miniaturized Version Resistance Code • R<100 ohms:

"R" represents decimal point

(examples: 56R0 = 56 ohms)

• R≥100 ohms:

First three digits are significant, fourth digit represents number of zeros to follow

(example: 1500 = 150 ohms)

Resistance Tolerance - $J = \pm 5 \%$

Packaging Specifications

| Model | Style | Qty. per Box (Pcs.) | Min. Order Quantity (Pcs.) | |
|-------|--------------|---------------------------|-------------------------------------|--|
| W1M | | | | |
| W2M | Ammo Pack | 1,000 | 5,000 | |
| W3M | | | | |
| W5M | Ammo | 500 | 2 000 | |
| W7M | Pack | 500 | 2,000 | |
| W9M | Bulk in | 25 / 200 | 2,000 | |
| W10M | Box | 25 / 200 | 2,000 | |



WARNING Cancer and Reproductive Harm - www.P65Warnings.ca.gov

W Series Wirewound Power Resistor

Product Dimensions


DIMENSIONS: (INCHES)

| Madal | Dimensions | | | | |
|-------|---|---------------------------------------|---|---|--|
| Model | L* | D | w | Т | |
| W1M | $\frac{9.5 \pm 1.0}{(.374 \pm .004)}$ | | | $\frac{0.60 \pm 0.05}{(.024 \pm .002)}$ | |
| W2M | $\frac{11.5 \pm 1.0}{(.453 \pm .004)}$ | $\frac{4.5 \pm 1.0}{(.177 \pm .004)}$ | $\frac{28.0 \pm 3.0}{(1.102 \pm .118)}$ | $\frac{0.65 \pm 0.05}{(.026 \pm .002)}$ | |
| W3M | $\frac{15.5 \pm 1.0}{(.610 \pm .004)}$ | $\frac{5.5 \pm 1.0}{(.217 \pm .004)}$ | $\frac{28.0 \pm 3.0}{(1.102 \pm .118)}$ | $\frac{0.70 \pm 0.05}{(.028 \pm .002)}$ | |
| W5M | $\frac{17.5 \pm 1.0}{(.689 \pm .004)} \qquad \frac{6.5 \pm 1.0}{(.256 \pm .004)}$ | | $\frac{28.0 \pm 3.0}{(1.102 \pm .118)}$ | $\frac{0.75 \pm 0.05}{(.030 \pm .002)}$ | |
| W7M | $\frac{24.5 \pm 1.0}{(.965 \pm .004)}$ | $\frac{8.5 \pm 1.0}{(.335 \pm .004)}$ | $\frac{38.0 \pm 3.0}{(1.496 \pm .118)}$ | $\frac{0.75 \pm 0.05}{(.030 \pm .002)}$ | |
| W9M | $\frac{39.5 \pm 1.0}{(1.555 \pm .004)}$ | $\frac{8.5 \pm 1.0}{(.335 \pm .004)}$ | $\frac{38.0 \pm 3.0}{(1.496 \pm .118)}$ | $\frac{0.75 \pm 0.05}{(.030 \pm .002)}$ | |
| W10M | $\frac{52.5 \pm 1.0}{(2.067 \pm .004)}$ | $\frac{8.5 \pm 1.0}{(.335 \pm .004)}$ | $\frac{38.0 \pm 3.0}{(1.496 \pm .118)}$ | $\frac{0.75 \pm 0.05}{(.030 \pm .002)}$ | |


^{*} Larger body size available upon request.

Typical Part Marking

Resistors shall be marked with color coding. Colors shall be in accordance with JIS C 0802.




| Color | 1st Band | 2nd Band | Multi- plier | Tol. | |
|--------|-------------|-------------|-----------------|---------|--|
| Black | 0 | 0 | 1 Ω | | |
| Brown | 1 | 1 | 10 Ω | ±1 % | |
| Red | 2 | 2 | 100 Ω | ±2 % | |
| Orange | 3 | 3 | 1K Ω | | |
| Yellow | 4 | 4 | 10K Ω | | |
| Green | 5 | 5 | 100K Ω | ±0.5 % | |
| Blue | 6 | 6 | 1Μ Ω | ±0.25 % | |
| Violet | 7 | 7 | 10M Ω | ±0.10 % | |
| Grey | 8 | 8 | | ±0.05 % | |
| White | 9 | 9 | | | |
| Gold | | | 0.1 Ω | ±5 % | |
| Silver | | | 0.01 Ω | ±10 % | |



W Series Wirewound Power Resistor

Packaging Specifications



| Model | 0 | Р | Α | В | С | Qty./Box |
|-------|-------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|------------|
| W1M | $\frac{58 \pm 1}{(2.283 \pm .039)}$ | $\frac{5 \pm 0.3}{(.197 \pm .012)}$ | $\frac{75 \pm 5}{(2.953 \pm .197)}$ | $\frac{70 \pm 5}{(2.756 \pm .197)}$ | $\frac{255 \pm 5}{(10.039 \pm .197)}$ | 1,000 pcs. |
| W2M | $\frac{58 \pm 1}{(2.283 \pm .039)}$ | $\frac{10 \pm 0.5}{(.394 \pm .020)}$ | $\frac{80 \pm 5}{(3.150 \pm .197)}$ | $\frac{82 \pm 5}{(3.228 \pm .197)}$ | $\frac{255 \pm 5}{(10.039 \pm .197)}$ | 1,000 pcs. |
| W3M | $\frac{65 \pm 5}{(2.559 \pm .197)}$ | $\frac{10 \pm 0.5}{(.394 \pm .020)}$ | $\frac{90 \pm 5}{(3.543 \pm .197)}$ | $\frac{119 \pm 5}{(4.685 \pm .197)}$ | $\frac{255 \pm 5}{(10.039 \pm .197)}$ | 1,000 pcs. |
| W5M | $\frac{65 \pm 5}{(2.559 \pm .197)}$ | $\frac{10 \pm 0.5}{(.394 \pm .020)}$ | $\frac{90 \pm 5}{(3.543 \pm .197)}$ | $\frac{88 \pm 5}{(3.465 \pm .197)}$ | $\frac{255 \pm 5}{(10.039 \pm .197)}$ | 500 pcs. |
| W7M | $\frac{90 \pm 5}{(3.543 \pm .197)}$ | $\frac{10 \pm 0.5}{(.394 \pm .020)}$ | $\frac{115 \pm 5}{(4.528 \pm .197)}$ | $\frac{124 \pm 5}{(4.882 \pm .197)}$ | $\frac{500 \pm 5}{(19.685 \pm .197)}$ | 500 pcs. |

For W9M and W10M packaging specifications, please contact factory.

BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 885 877 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

09/19

Legal Disclaimer Notice



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf