

Features

- Formerly a **KEKO**VARICON product
- Four model sizes available 0603, 0805, 1206 and 1210
- Characterized for inductance and capacitance
- Short response time
- Non-sensitive to mildly activated fluxes

ZVE Series - Suppression Varistors

- Operating voltage range up to 18 V
- Non-plastic coating for better flammability rating
- RoHS compliant*

General Information

ZVE varistors are designed to suppress ESD events, including those specified in IEC 1000-4-2 or other standards used for Electromagnetic Compliance testing. The ZVE series is typically applied to protect integrated circuits and other components at the circuit board level operating at 18 VDC or less.

The fabrication method, design and materials of these devices result in capacitance characteristics typically suitable for high frequency attenuation/low-pass filter circuit functions, providing suppression and filtering in a single device.

Absolute Maximum Ratings

Parameter	Value	Units
Continuous:		
Steady State Applied Voltage		
DC Voltage Range (V _{dc})	≤ 18	V
AC Voltage Range (V _{rms})	2 to 30	V
Transient:		
Peak Single Pulse Surge Current, 8/20 µs Waveform (Imax)	20, 30	A
Single Pulse Surge Energy, 10/1000 µs Waveform (Wmax)	0.05 to 0.1	J
Operating Ambient Temperature	-55 to +125	°C
Storage Temperature Range	-55 to +150	°C
Threshold Voltage Temperature Coefficient	< +0.05	%/°C
Response Time	< 1	ns
Climatic Category	55 / 125 / 56	

Additional Information

Click these links for more information:




Agency Recognition

Standard	UL 1449
File Number	E326499**

**Not all rated voltages are UL recognized; check the file for details.

Multilayered Varistor Symbol



Index

Features1
General Information 1
Agency Recognition <u>1</u>
MOV Symbol 1
Absolute Maximum Ratings1
Applications2
Device Ratings2
Product Dimensions2
Capacitance – Frequency Characteristics 2
How to Order <u>3</u>
Typical Part Marking3
Soldering Pad Configuration3
Packaging Specifications 4
Soldering Recommendations for
SMD Components <u>5-7</u>
Reliability – Lifetime
Terminology <u>11</u>
Legal Disclaimer <u>12</u>

BOURNS

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com EMEA: Tel: +36 88 885 877 • Email: eurocus@bourns.com The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com www.bourns.com



*RoHS Directive 2015/863, Mar 31, 2015 and Annex. Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

Applications

- Protection of components and circuits sensitive to ESD transients occurring on power supply, control and signal lines
- Suppression of ESD events as specified in IEEEC 1000-4-2, MIL-STD 883C, method 3015.7 or AEC-Q200-002 for Electromagnetic Compliance (EMC)
- Used in mobile communication, computer/EDP products, medical products* handheld/portable devices, industrial equipment, including diagnostic port protection and I/O interfaces

ZVE Series – Suppression Varistors


BOURNS®

Device Ratings


Model	V _{rms}	V _{dc}	V _n @ 1 mA	V _c 8/20 μs	Ι _c 8/20 μs	W _{max} 10/1000 µs	P max.	C _{max} @ 1 MHz	l _{typ} 100 mA/ns
	V	V	V	V	А	J	W	pF	nH
ZVE 14 S 0603	14	18	22 - 28	50	2	0.05	0.003	75	< 1.0
ZVE 14 S 0805	14	18	22 - 28	50	2	0.10	0.004	100	< 1.5
ZVE 14 S 1206	14	18	22 - 28	50	2	0.10	0.004	200	< 1.8
ZVE 14 S 1210	14	18	22 - 28	50	2	0.10	0.004	400	< 3.5

Product Dimensions

Model	Dimension					
model	L	W	t (Max.)			
ZVE 14 S 0603	$\frac{1.6 \pm 0.20}{(.063 \pm .008)}$	$\frac{0.80 \pm 0.10}{(.031 \pm .004)}$	<u>0.95</u> (.037)			
ZVE 14 S 0805	$\frac{2.0 \pm 0.25}{(.079 \pm .010)}$	$\frac{1.25 \pm 0.20}{(.049 \pm .008)}$	<u>0.95</u> (.037)			
ZVE 14 S 1206	$\frac{3.2 \pm 0.30}{(.126 \pm .012)}$	$\frac{1.60 \pm 0.20}{(.063 \pm .008)}$	<u>1.20</u> (.047)			
ZVE 14 S 1210	$\frac{3.2 \pm 0.30}{(.126 \pm .012)}$	$\frac{2.50 \pm 0.25}{(.098 \pm .010)}$	<u>1.30</u> (.051)			



Capacitance - Frequency Characteristics



Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.


How to Order ZVE14S1206NIR1yy Series Designator ZVE = ZVE Series Maximum Continuous Working Voltage (V_{rms}) V_n Tolerance S = Special (See Device Ratings Table for Details) Model Size • 0603 • 0805 • 1206 • 1210 End Terminations • (Blank) = AgPd end terminations suitable for Pb reflow soldering (Available upon Request) • N = Barrier type end terminations suitable for Pb-free reflow soldering • NI = NiSn barrier type end terminations suitable for Pb and Pb-free reflow soldering (Standard) Packaging R1 = 4000 pcs. per 180 mm (7-inch) reel Special Requirements -• уу

Instructions for Creating Orderable Part Number:

1) Start with base part number in characteristics table (example: ZVE14S1206).

- 2) Add End Terminations: NI (example part number becomes ZVE14S1206NI).
- 3) Add Packaging: R1 (example part number becomes ZVE14S1206NIR1).
- 4) Part number can have no spaces or lower case letters.

Soldering Pad Configuration



Size	Dimension									
0120	L	w	t (Max.)	A	В	С	D			
0603	$\frac{1.6 \pm 0.20}{(.063 \pm .008)}$	$\frac{0.80 \pm 0.10}{(.315 \pm .004)}$	<u>1.0</u> (.039)	<u>1.0</u> (.039)	<u>1.0</u> (.039)	<u>0.6</u> (.024)	<u>2.6</u> (.102)			
0805	2.0 ± 0.25 (.079 ± .010)	$\frac{1.25 \pm 0.20}{(.049 \pm .008)}$	<u>1.1</u> (.043)	<u>1.4</u> (.055)	<u>1.2</u> (.047)	<u>1.0</u> (.039)	$\frac{3.4}{(.134)}$			
1206	$\frac{3.2 \pm 0.30}{(.126 \pm .012)}$	$\frac{1.60 \pm 0.20}{(.063 \pm .008)}$	<u>1.6</u> (.063)	<u>1.8</u> (.071)	<u>1.2</u> (.047)	<u>2.1</u> (.083)	4.5 (.177)			
1210	$\frac{3.2 \pm 0.30}{(.126 \pm .012)}$	$\frac{2.50 \pm 0.20}{(.098 \pm .008)}$	<u>1.8</u> (.071)	<u>2.8</u> (.110)	<u>1.2</u> (.047)	<u>2.1</u> (.083)	$\frac{4.5}{(.177)}$			

BOURNS

Typical Part Marking

No marking.

Specifications are subject to change without notice.


```
Users should verify actual device performance in their specific applications.
```


BOURNS

Packaging Specifications

Conforms to IEC Publication 286-3 Ed. 4: 2007-06







Dimension	Model Size					
Dimension	0603	0805	1206	1210		
A ₀	<u>1.2</u> (.047)	<u>1.6</u> (.063)	<u>1.9</u> (.075)	<u>2.9</u> (.114)		
B ₀	<u>1.9</u> (.075)	<u>2.4</u> (.094)	$\frac{3.75}{(.148)}$	3.7 (.146)		
K ₀ MAX.	<u>1.1</u> (.043)		<u>1.8</u> (.071)	<u>2.0</u> (.079)		
B ₁ MAX.		$\frac{4.35}{(.171)}$				
D ₁ DIA. MIN.	0.3 (.012)					
E ₂ MIN.	<u>6.25</u> (.246)					
P ₁	<u>4</u> (.157)					

Dimension	Model Size						
Dimension	0603	1206	1210				
F		<u>3</u> (.1)	. <u>5</u> 38)				
W		<u>8.0</u> (.315)					
T ₂ MAX.	3.5 (.138)						
W ₁	<u>8.4 + 1.5</u> (.331 + .059)						
W ₂ MAX.	<u>14.4</u> (.567)						
W ₃	$\frac{7.9}{(.311)}$ to $\frac{10.9}{(.429)}$						
A DIA.		<u>18</u> (7.0	<u>30</u>)87)				

DIMENSIONS:

MM (INCHES)

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.

BOURNS

Soldering Recommendations for SMD Components

Popular soldering techniques used for surface mounted components are Wave and Infrared Reflow processes. Both processes can be performed with Pb-containing or Pb-free solders.

End Termination	Designation	Recommended and Suitable for	RoHS Compliant
NiSn End Termination	ZVE SeriesNi R1	Pb-containing and Pb-free soldering	Yes

Wave Soldering

This process is generally associated with discrete components mounted on the underside of printed circuit boards, or for large top-side components with bottom-side mounting tabs to be attached, such as the frames of transformers, relays, connectors, etc. SMD varistors to be wave soldered are first glued to the circuit board, usually with an epoxy adhesive. When all components on the PCB have been positioned and an appropriate amount of time is allowed for adhesive curing, the completed assembly is then placed on a conveyor and run through a single, double wave process.

Infrared Reflow Soldering

These reflow processes are typically associated with top-side component placement. This technique utilizes a mixture of adhesive and solder compounds (and sometimes fluxes) that are blended into a paste. The paste is then screened onto PCB soldering pads specifically designed to accept a particular sized SMD component. The recommended solder paste wet layer thickness is 100 to 300 μ m. Once the circuit board is fully populated with SMD components, it is placed in a reflow environment, where the paste is heated to slightly above its eutectic temperature. When the solder paste reflows, the SMD components are attached to the solder pads.

Solder Fluxes

Solder fluxes are generally applied to populated circuit boards to keep oxides from forming during the heating process and to facilitate the flowing of the solder. Solder fluxes can be either a part of the solder paste compound or separate materials, usually fluids. Recommended fluxes are:

- · non-activated (R) fluxes, whenever possible
- mildly activated (RMA) fluxes of class L3CN
- class ORLO

Activated (RA), water soluble or strong acidic fluxes with a chlorine content > 0.2 wt. % are NOT RECOMMENDED. The use of such fluxes could create high leakage current paths along the body of the varistor components.

When a flux is applied prior to wave soldering, it is important to completely dry any residual flux solvents prior to the soldering process.

Thermal Shock

To avoid the possibility of generating stresses in the varistor chip due to thermal shock, a preheat stage to within 100 °C of the peak soldering process temperature is recommended. Additionally, SMD varistors should not be subjected to a temperature gradient greater than 4 °C/sec., with an ideal gradient being 2 °C/sec. Peak temperatures should be controlled. Wave and Reflow soldering conditions for SMD varistors with Pb-containing solders are shown on the next page in Fig. 1 and 2 respectively, while Wave and Reflow soldering conditions for SMD varistors with Pb-free solders are shown in Fig. 1 and 3.


Whenever several different types of SMD components are being soldered, each having a specific soldering profile, the soldering profile with the least heat and the minimum amount of heating time is recommended. Once soldering has been completed, it is necessary to minimize the possibility of thermal shock by allowing the hot PCB to cool to less than 50 °C before cleaning.

Specifications are subject to change without notice.

```
Users should verify actual device performance in their specific applications.
```

BOURNS

Soldering Recommendations for SMD Components (Continued)



Inspection Criteria

When Wave or Infrared Reflow processes are used, the inspection criteria to determine acceptable solder joints will depend on several key variables, principally termination material process profiles.

Pb-containing Wave and IR Reflow Soldering

Solder forms a metallurgical junction with the thin tin-alloy (over the barrier layer), and due to its small volume "climbs" the outer surface of the terminations, so the meniscus will be slightly lower. This optical appearance difference should be taken into consideration when programming visual inspection of the PCB after soldering.




Fig. 4 Soldering Criteria for Wave and IR Reflow Pb-containing Soldering



Fig. 5 Soldering Criteria for Wave and IR Reflow Pb-free Soldering

NiSn End Terminations

Before

soldering

After

soldering

w

90 % (

Barrier

Solderable

metal

Metal

Solder paste

Pb-free Wave and IR Reflow Soldering

Solder forms a metallurgical junction with the entire volume of the end termination, i.e., it diffuses from pad to end termination across the inner side, forming a "mirror" or "negative meniscus. The height of the solder penetration can be clearly seen on the end termination and is always 30 % higher than the chip height.

Since barrier type terminations on Bourns[®] chips do not require the use of sometimes problematic nickel and tin-alloy electroplating processes, these variators are truly considered environmentally friendly.

Solder Test and Retained Samples

Reflow soldering test based on J-STD-020D.1 and soldering test by dipping based on IEC 60068- 2 for Pb-free solders are performed on each production lot as shown in the following chart. Test results and accompanying samples are retained for a minimum of two (2) years. The solderability of a specific lot can be checked at any time within this period, should a customer require this information.

Specifications are subject to change without notice.

```
Users should verify actual device performance in their specific applications.
```

BOURNS

Soldering Recommendations for SMD Components (Continued)

Test	Resistance to Flux	Solderability	Static Leaching (Simula- tion of Reflow Soldering)	Dynamic Leaching (Simu- lation of Wave Soldering)
Soldering method	Dipping	Dipping	Dipping	Dipping with Agitation
Flux	L3CN, ORL0	L3CN, ORL0, R	L3CN, ORL0, R	L3CN, ORL0, R
Pb Solder	62Sn / 36Pb / 2Ag			
Pb Soldering Temperature (°C)	235 ± 5	235 ± 5	260 ± 5	235 ± 5
Pb-Free Solder	Sn96 / Cu0,4-0,8 / 3-4Ag			
Pb-Free Soldering Temperature (°C)	250 ± 5	250 ± 5	280 ± 5	250 ± 5
Soldering Time (sec.)	2	210	10	> 15
Burn-in Conditions	V _{dcmax} , 48 hours	-	-	-
Acceptance Criterion	dVn < 5 %, i _{dc} must stay unchanged	> 95 % of end termination must be covered by solder	> 95 % of end termination must be intact and covered by solder	> 95 % of end termination must be intact and covered by solder

Rework Criteria - Soldering Iron

Unless absolutely necessary, the use of soldering irons is NOT recommended for reworking variator chips. If no other means of rework is available, the following criteria must be strictly followed:

- Do not allow the tip of the iron to directly contact the top of the chip
- Do not exceed the following soldering iron specifications:

Storage Conditions

SMD varistors should be used within 1 year of purchase to avoid possible soldering problems caused by oxidized terminals. The storage environment should be controlled, with humidity less than 40 % and temperature between -25 and +45 °C. Varistor chips should always be stored in their original packaged unit.

When varistor chips have been in storage for more than 1 year, and when there is evidence of solderability difficulties, Bourns can "refresh" the terminations to eliminate these problems.

Specifications are subject to change without notice.

```
Users should verify actual device performance in their specific applications.
```

BOURNS

Reliability - Lifetime

Pb-free Wave and IR Reflow Soldering

In general, **reliability** is the ability of a component to perform and maintain its functions in routine circumstances, as well as in hostile or unexpected circumstances.

The Mean life of the ZVX series is a function of:

- · Factor of Applied Voltage
- Ambient Temperature

Mean life is closely related to Failure rate (formula).

Mean life (ML) is the arithmetic mean (average) time to failure of a component.

Failure rate is the frequency with which an engineered system or component fails, expressed, for example, in failures per hour. Failure rate is usually time dependent, and an intuitive corollary is that the rate changes over time versus the expected life cycle of a system.

Failure rate formula - calculation


 $\Lambda = \frac{10^9}{\text{ML [h]}} \text{ [fit]}$

FAV - Factor of Applied Voltage

 $\mathsf{FAV} = \frac{\mathsf{V}_{\mathsf{apl}}}{\mathsf{V}_{\mathsf{max}}}$

Vapl.....applied voltage

Vmaxmaxiimum operating voltage



Specifications are subject to change without notice.

```
Users should verify actual device performance in their specific applications.
```

BOURNS

Reliability Testing Procedures

Varistor test procedures comply with CECC 42200, IEC 1051-1/2 (and AEC-Q200, if applicable). Test results are available upon customer request. Special tests can be performed upon customer request.

Reliability Parameter	Test	Tested According to	Condition to be Satisfied after Testing
AC/DC Bias Reliability	AC/DC Life Test	CECC 42200, Test 4.20 or IEC 1051-1, Test 4.20, AEC-Q200 Test 8 - 1000 h at UCT	lδV _n (1 mA)l < 10 %
Pulse Current Capability I _{max} 8/20 µs		CECC 42200, Test C 2.1 or IEC 1051-1, Test 4.5 10 pulses in the same direction at 2 pulses per minute at maximum peak current for 10 pulses	lδV _n (1 mA)l < 10 % no visible damage
Pulse Energy Capability	W _{max} 10/1000 μs	CECC 42200, Test C 2.1 or IEC 1051-1, Test 4.5 10 pulses in the same direction at 1 pulse every 2 minutes at maximum peak current for 10 pulses	lδV _n (1 mA)l < 10 % no visible damage
WLD Capability	WLD x 10	ISO 7637, Test pulse 5, 10 pulses at rate of 1 per minute	lδV _n (1 mA)l < 15 % no visible damage
V _{jump} Capability	V _{jump} 5 min.	Increase of supply voltage to $V \ge V_{jump}$ for 1 minute	lδV _n (1 mA)l < 15 % no visible damage
Environmental and Storage Reliability	Climatic Sequence	 CECC 42200, Test 4.16 or IEC 1051-1, Test 4.17 a) Dry heat, 16h, UCT, Test Ba, IEC 68-2-2 b) Damp heat, cyclic, the first cycle: 55 °C, 93 % RH, 24 h, Test Db 68-2-4 c) Cold, LCT, 2 h, Test Aa, IEC 68-2-1 d) Damp heat cyclic, remaining 5 cycles: 55 °C, 93 % RH, 24 h/cycle, Test Bd, IEC 68-2-30 	lδV _n (1 mA)l < 10 %
• •	Thermal Shock	CECC 42200, Test 4.12, Test Na, IEC 68-2-14, AEC-Q200 Test 16, 5	$ \delta V_{\rm H} (1 \text{ mA}) < 10 \%$ no visible damage
	Steady State Damp Heat	CECC 42200, Test 4.17, Test Ca, IEC 68-2-3, AEC-Q200 Test 6, 56 days, 40 °C, 93 % RH, AEC-Q200 Test 7: Bias, Rh, T all at 85.	lδV _n (1 mA)l < 10 %
	Storage Test	IEC 68-2-2, Test Ba, AEC-Q200 Test 3, 1000 h at maximum storage temperature	lδV _n (1 mA)l < 5 %

Continued on Next Page

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.

BOURNS

Reliability Testing Procedures (Continued)

Reliability Parameter	Test	Tested According to	Condition to be Satisfied after Testing
	Solderability	CECC 42200, Test 4.10.1, Test Ta, IEC 68-2-20 solder bath and reflow method	Solderable at shipment and after 2 years of storage, criteria: >95% must be covered by solder for reflow meniscus
	Resistance to Soldering Heat	CECC 42200, Test 4.10.2, Test Tb, IEC 68-2-20 solder bath nad reflow method	lδV _n (1 mA)l < 5 %
	Terminal Strength	JIS-C-6429, App. 1, 18N for 60 sec same for AEC-Q200 Test 22	No visual damage
Mechanical Reliability	Board Flex	JIS-C-6429, App. 2, 2 mm min. AEC-Q200 test 21 - Board flex: 2 mm flex min.	lδV _n (1 mA)l < 2 % No visible damage
	Vibration	CECC 42200, Test 4.15, Test Fc, IEC 68-2-6, AEC-Q200 Test 14 Frequency range 10 to 55 Hz (AEC: 10-2000 Hz) Amplitude 0.75 m/s ² or 98 m/s ² (AEC: 5 g for 20 minutes) To- tal duration 6 h (3x2 h) (AEC: 12 cycles each of 3 directions) Waveshape - half sine	lδV _n (1 mA)l < 2 % No visible damage
	Mechanical Shock	CECC 42200, Test 4.14, Test Ea, IEC 68-2-27, AEC-Q200 Test 13. Acceleration = 490 m/s ² (AEC: MIL-STD-202-Method 213), Pulse duration = 11 ms, Waveshape - half sine; Number of shocks = $3x6$	lδV _n (1 mA)l < 10 % No visible damage
Electrical Transient Conduction	ISO-7637-1 Pulses	AEC-Q200 Test 30: Test pulses 1 to 3. Also other pulses - freestyle.	lδV _n (1 mA)l < 10 % No visible damage

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.

Terminology

BOURNS

Symbol Definition Term applied to the component under continuous operation conditions at +25 °C Rated DC Voltage......VdcVdcMaximum continuous DC voltage (<5 % ripple) which may be applied to the component under continuous operating conditions at +25 °C characteristics of the system are referred; V_{rms} = 1.1 x V temperature Varistor VoltageVn vn......Voltage across the varistor measured at a given reference current (In) Protection Level when passing an 8/20 µs class current pulse per minute for the 8/20 µs pulse V_c/V_{app} , where $(V_{app} = V_{rms} \text{ or } V_{dc})$ of the rated battery voltage. The circuit power supply may be subjected to a temporary overvoltage condition due to the voltage regulation failing or it may be deliberately generated when it becomes necessary to boost start the car. Transient Energy current, with rated AC voltage or rated DC voltage also applied, without causing device failure Load Dump TransientWLDLoad Dump is a transient which occurs in automotive environments. It is an exponentially decaying positive voltage which occurs in the event of a battery disconnect while the alternator is still generating charging current with other loads remaining on the alternator circuit at the time of battery disconnect. Rated Peak Single Pulse......ImaxMaximum peak current which may be applied for a single 8/20 µs pulse, with rated line Transient Current voltage also applied, without causing device failure within a specified isolated time period, without causing device failure at 25 °C Power Dissipation Capacitance......Capacitance between two terminals of the varistor measured @ 1 kHz described by I = k V exp(a), where: k is a device constant, - $I_1 < I < I_n$ and - $a \log (I_1/I_n)/\log(V_1/V_n) = 1/\log (V_1/V_n)$, where: - Ir is reference current (1 mA) and Vn is varistor voltage - $I_1 = 10 I_n$, V₁ is the voltage measured at I₁ Coefficient Insulation ResistanceIR......IR.......Minimum resistance between shorted terminals and varistor surface between the varistor terminations and any conducting mounting surface as defined by the temperature limits of its climatic category Climatic CategoryLCT/UCT/DHD ..LCT & UCT = Lower and Upper Category Temperature - the minimum and maximum ambient temperatures for which a varistor has been designed to operate continuously. DHD = Dump Heat Test Duration Current/Energy Derating......Derating of maximum values when operated above UCT

REV. A 01/20

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

Legal Disclaimer Notice

This legal disclaimer applies to purchasers and users of Bourns[®] products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns[®] products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns[®] products.

The characteristics and parameters of a Bourns[®] product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns[®] product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns[®] product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns[®] product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns[®] product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns[®] product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns[®] product to meet the requirements of such industry standard or particular qualification. Users of Bourns[®] products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns[®] products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns[®] products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns[®] standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns[®] standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications, it should only be used in such sub-category of automotive applications product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns[®] standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns[®] standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns[®] standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns[®] custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns[®] custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns[®] standard products shall also apply to such Bourns[®] custom products.

Users shall not sell, transfer, export or re-export any Bourns[®] products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns[®] products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns[®] products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns[®] products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <u>http://www.bourns.com/legal/disclaimers-terms-and-policies</u> PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf