

MATERIAL DECLARATION SHEET



Material Number	3549S-1XD-XXXX			
Product Line	Sensors & Controls			
Compliance Date	January 31, 2007			
RoHS Compliant	Yes	MSL	N/A	

No.	Construction Element(subpart)	Homogeneous Material	Material weight [g]	Homogeneous Material Substances	CASRN if applicable	Materials Mass %	Material Mass % of total unit wt	Subpart mass of total wt. . (%)
1	Hex Nut	Brass C260	1.25	Copper	7440-50-8	70	3.9830	5.6900
				Zinc	7440-66-6	30	1.7070	
		Plating	0.0900	Nickel	7440-02-0	100	0.4097	0.4097
2	Lock Washer	C1050 Carbon Steel	0.17	Carbon	7440-44-0	0.5	0.0038	0.7693
				Iron	7439-89-6	98.7	0.7593	
				Manganese	7439-96-5	0.75	0.0058	
				Phosphorus	7723-14-0	0.02	0.0002	
				Sulphur	7704-34-9	0.03	0.0002	
		Plating	0.0010	Nickel	10101-97-0	100	0.0046	0.0046
3	Lid Molded	Bushing Brass 360	3.53	Copper	7440-50-8	61.5	9.8821	16.0685
				Iron	7439-89-6	0.2	0.0321	
				Lead	7439-92-1	3.0	0.4821	
				Zinc	7440-66-6	35	5.6240	
				Misc, not to Declare	N/A	0.3	0.0482	
		Shinkong	0.836	PBT	26062-94-2	54.25	2.0645	3.8055
				GF-Fibre ISO 1043-2	65997-17-3	30	1.1416	

MATERIAL DECLARATION SHEET



				Halogenated Compound ISO 1043-4, not Declarable	N/A	9	0.3425	
				Antimonytrioxide	1309-64-4	3.5	0.1332	
				Carbon Black	1333-86-4	1.25	0.0476	
				Additives, not to Declare	N/A	2	0.0761	
4	Housing	ShinKong	3.032	PBT	26062-94-2	54.25	7.4874	13.80
				GF-Fibre ISO 1043-2	65997-17-3	30	4.1405	
				Halogenated Compound ISO 1043-4, not Declarable	N/A	9	1.2421	
				Antimonytrioxide	1309-64-4	3.5	0.4831	
				Carbon Black	1333-86-4	1.25	0.1725	
				Additives, not to Declare	N/A	2	0.2760	
5	Element Assy	Mandrel Wire Annealed Copper Wire	2.03	Copper	7440-50-8	100	9.24	9.24
		Coating	0.000083	Polyamide	63428-83-1	100	0.0004	0.0004
		Resist Wire Nickel- Chromium Alloy	0.523	Nickel	7440-02-0	74	1.76	2.38
				Copper	7440-50-8	1	0.0238	
				Chromium	7440-47-3	21	0.4999	
				Aluminum	7429-90-5	1	0.0238	
				Silicon	7440-21-3	1	0.0238	
				Cobalt	7440-48-4	1	0.0238	
				Manganese	7439-96-5	1	0.0238	
6	Varnish	Hi-Thermo	0.094	Alkyd Resin	63148-69-6	99.5	0.43	0.43
				Misc, Not to Declare	N/A	0.5	0.0021	

MATERIAL DECLARATION SHEET



		Pigment	0.006	Basic Violet 11.1	73398-89-7	99.5	0.0272	0.03
				Misc. Not to Declare	N/A	0.5	0.0001	
7	Terminal Cover	Nylatron	0.109	Nylon 6.6 (Polyhexamethylene Adipamide)	32131-17-2	66	0.33	0.50
				Glass Fiber	65997-17-3	32	0.16	
				Molybdenum Disulfide	1317-33-5	2	0.01	
8	T.R. Terminal x2	Nickel/Silver C752	0.0905	Copper	7440-50-8	65.00	0.268	0.41
				Nickel	7440-02-0	18.00	0.074	
				Zinc	7440-66-6	17.00	0.070	
		Silver Alloy A56T	0.0001	Silver	7440-22-4	56.00	0.0003	0.0005
				Copper	7440-50-8	22.00	0.0001	
				Zinc	7440-66-6	17.00	0.00008	
				Tin	7440-31-5	5.00	0.00002	
		Plating	0.0003	Gold	7440-57-5	100.00	0.0014	0.0014
9	Shaft	Brass 360	7.432	Copper	7440-50-8	61.5	20.806	33.83
				Iron	7439-89-6	0.2	0.068	
				Lead	7439-92-1	3.0	1.015	
				Zinc	7440-66-6	35	11.841	
				Misc, not to Declare	N/A	0.3	0.101	
		Plating	0.001	Nickel	7440-02-0	100	0.005	0.0046
10	Rotor Molded	Nylatron	1.154	Nylon 6.6 Polyhexamethylene Adipamide)	32131-17-2	66	3.47	5.25
				Glass Fiber	65997-17-3	32	1.68	
				Molybdenum Disulfide	1317-33-5	2	0.105	
11	Slider Molded	Nylatron	0.205	Nylon 6.6 (Polyhexamethylene Adipamide)	32131-17-2	66	0.62	0.93

MATERIAL DECLARATION SHEET



				Glass Fiber	65997-17-3	32	0.30	
				Molybdenum Disulfide	1317-33-5	2	0.02	
12	Contact Spring	Paliney #6	0.003	Palladium	7440-05-3	44	0.01	0.01
				Silver	7440-22-4	38	0.01	
				Copper	7440-50-8	16	0.002	
				Platinum	7440-06-4	1	0.0001	
				Nickel	7440-02-0	1	0.000	
		Pfinodal 7 C72900	0.01	Copper	7440-50-8	72.875	0.033173	0.05
				Lead	7439-92-1	0.025	0.000011	
				Iron	7439-89-6	0.3	0.000137	
				Nickel	7440-02-0	21	0.009559	
				Cobalt	7440-48-4	0.25	0.000114	
				Tin	7440-31-5	5.1	0.002322	
				Manganese	7439-96-5	0.3	0.000137	
				Misc	Not to declare	0.15	0.000068	
13	Collector Bar	Nickel/Silver C770	0.074	Copper	7440-50-8	59	0.199	0.34
				Nickel	7440-02-0	12	0.04	
				Zinc	7440-66-6	29	0.0977	
		Plating	0.0009	Gold	7440-57-5	100	0.004	0.004
14	Terminal Wiper	Brass C260	0.3810	Copper	7440-50-8	70	1.214	1.73
				Zinc	7440-66-6	30	0.52	
		Under Plating	0.0120	Nickel	7440-02-0	100	0.05	0.05
		Finish Plating	0.0026	Gold	7440-57-5	100	0.01	0.01
15	Cover	Nylatron	0.812	Nylon 6.6 (Polyhexamethylene Adipamide)	32131-17-2	66.00	2.439	3.70
				Glass Fiber	65997-17-3	32.00	1.183	
				Molybdenum Disulfide	1317-33-5	2.00	0.074	

MATERIAL DECLARATION SHEET



16	C-Ring	Stainless Steel 420	0.014	Carbon	7440-44-0	0.31	0.00020	0.06
				Silicon	7440-21-3	0.44	0.0003	
				Manganese	7439-96-5	0.45	0.0003	
				Phosphorus	7723-14-0	0.02	0.00001	
				Sulfur	7704-34-9	0.01	0.00000	
				Nickel	7440-02-0	0.23	0.00015	
				Chromium	7440-47-3	13.15	0.008	
				Iron	7439-89-6	85.40	0.054	
17	Washer S.S.	Stainless Steel 301	0.001	Carbon	7440-44-0	0.15	0.00001	0.00
				Manganese	7439-96-5	2	0.0001	
				Phosphorus	7723-14-0	0.045	0.000002	
				Sulfur	7704-34-9	0.03	0.000001	
				Silicon	7440-21-3	1	0.0000	
				Chromium	7440-47-3	17	0.001	
				Nickel	7440-02-0	7	0.000	
				Iron	7439-89-6	72.775	0.003	
18	Washer S. S	Stainless Steel 301	0.001	Carbon	7440-44-0	0.15	0.00001	0.00
				Manganese	7439-96-5	2	0.0001	
				Phosphorus	7723-14-0	0.045	0.000002	
				Sulfur	7704-34-9	0.03	0.000001	
				Silicon	7440-21-3	1	0.0000	
				Chromium	7440-47-3	17	0.001	
				Nickel	7440-02-0	7	0.0003	
				Iron	7439-89-6	72.775	0.003	
19	Lube	Lube	0.009	1-Decene, Tetramer, Mixed with 1-Decene Trimer, Hydorgenated	68649-12-7	58.8	0.0241	0.04
				1-Propene, Polymer with	9010-79-1	30.8	0.0126	

MATERIAL DECLARATION SHEET



				Ethene				
				Silica, Amorphous Fumed	112945-52-5	5.4	0.0022	
				Polytetrafluoroethylene	9002-84-0	5	0.0020	
20	Lube	Lube	0.09	Decanoic Acid, Mixed Esters with Heptanoic Acid, Octanoic Acid, Trimethylolpropane	68130-53-0	54.4	0.22	0.41
				Lithium 12-Hydroxystearate	7620-77-1	5.7	0.023	
				Isohexadecyl-Isooctadecanoate	52006-45-8	33.7	0.14	
				Polyisobutylene	9003-27-4	6.2	0.025	
21	Epoxy	Epoxy	0.005	Bisphenol A Diglycidyl Ether Resin	25068-38-6	44	0.01001	0.02276
				Alumina Trihydrate	21645-51-2	11	0.00250	
				Antimony Trioxide	1309-64-4	11	0.00250	
				Diglycidyl Ether of Polypropylene Glycol	9072-62-2	10.2	0.00232	
				Titanium Dioxide	13463-67-7	0.9	0.00020	
				Kaolin Clay	1332-58-7	6	0.00137	
				Epoxy Resin	67924-34-9	6.1	0.00139	
				Magnesium Aluminum Silicate	1302-88-1	9.5	0.002162	
				Phthalocyanine Blue	147-14-8	1.3	0.000296	
Total weight		21.9685						

MATERIAL DECLARATION SHEET



This Document was updated on: **07/24/2025**

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.