



Features

- Provides a maximum 16x32 pin array
- Terminal field rotates 180 ° and locks into place for convenient front access to equipment terminations
- Bifurcated wire-wrap terminals for convenient connection of up to four wires
- Universal hole pattern is compatible with most standard frames
- Cover safeguards personnel and cross-connections
- Inside surface provides ample space for circuit and pair designations
- Both front and rear fanning strips have snap-through slots
- Slotted front-to-rear fanning strip

Versablock® Rotating Terminal Block (139 Series)

No matter what the application – termination of line drawers, trunk modules, tie pairs, transmission channel banks, etc. – the versatile Versablock® Rotating Terminal Block (139 Series) adapts easily to your communications equipment termination needs. In addition, the Versablock® Rotating Terminal Block offers the following benefits:

Versatile

- Suitable for vertical or horizontal installation
- Connectorized or non-connectorized cable terminations
- Multiple pin patterns and wiring configurations available
- Choice of terminals: bifurcated wire-wrap, single wire-wrap, bifurcated quick-clip insulation displacement connector (IDC)

Easy to use

- Blocks snap securely into place and remove easily without tools
- Floating terminal pins are easily replaceable
- Hinged protective front cover latches securely and opens easily
- Slotted front-to-rear fanning strip
- Equipment terminals are easily accessible
- Terminates 22 to 26 AWG conductors
- UL94V-0 material

Specifications

Plastic Materials	Polycarbonate
Metal Parts	
Wire-wrap Terminals	Brass
IDC Terminals	Phosphor bronze
Plating	Hard, bright tin
Non-Connectorized Cable Connections	
Terminations	Wire-wrap
Cross-Connect (Jumper) Connections	
Terminations	Wire-wrap or IDC; contact resistance <1 milliohm change over product life
Dielectric Strength	2000 VDC
Insulation Resistance	>500 megohms
Environmental Conditions	For indoor use
Temperature Characteristics	-20 °C to +45 °C (-4 °F to +113 °F)
Practices	SRP 203-242

Packaging Specifications

Standard Package	10 modules
Dimensions (H x W x D)	350 x 590 x 260 mm (13.5 x 23 x 10 in.)
Weight	11.8 kg (26.5 lbs.)

Accessories

A full range of accessories and replacement parts are available for the Versablock® Rotating Terminal Block (139 Series).

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Versablock® Rotating Terminal Block (139 Series)

BOURNS®

How to Order

Part Number	Description	Typical Application
Connectorized Blocks		
139-D4100R019W	Versablock® Rotating Terminal Block (139 Series), 100 pair, 8x25, single wire-wrap cross-connect, four 50-pin male connectors, white label	Tie pairs
Non-Connectorized Blocks		
139-M0256R058B	Versablock® Rotating Terminal Block (139 Series), 256 pair, 16x32, single wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services
139-M0156R067B	Versablock® Rotating Terminal Block (139 Series), 156 pair, 12x26, single wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll and special services (replacement for 132 series terminal block)
139-N0128R001B	Versablock® Rotating Terminal Block (139 Series), 128 pair, 8x32, single wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services
139-N0128T001B	Versablock® Rotating Terminal Block (139 Series), 128 pair, 8x32, bifurcated wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services
139-N0128T001D	Versablock® Rotating Terminal Block (139-Series), 128 pair, 8x32, bifurcated wire-wrap cross-connect, single wire-wrap equipment, yellow label	1ESS / 1AESS line equipment (4:1)
139-M0104R066B	Versablock® Rotating Terminal Block (139-Series), 104 pair, 8x26, single wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services (replacement for 132 series terminal block)
139-N0100R012B	Versablock® Rotating Terminal Block (139-Series), 100 pair, 8x25, single wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services
139-N0100R012W	Versablock® Rotating Terminal Block (139-Series), 100 pair, 8x25, single wire-wrap cross-connect, single wire-wrap equipment, white label	Tie pairs
139-N0100T012B	Versablock® Rotating Terminal Block (139-Series), 100 pair, 8x25, bifurcated wire-wrap cross-connect, single wire-wrap equipment, beige label	Miscellaneous trunk, toll, and special services
Special Application Blocks		
139-R6144Q062B	Versablock® Rotating Terminal Block (139-Series), 144 pair, 8x40, bifurcated quick-clip cross-connect, six 64-pin male connectors, metal housing, beige label	Special
139-R0011W063B	Versablock® Rotating Terminal Block (139-Series), 11 pair bunching block, 8x22, single wire-wrap cross-connect, bifurcated wire-wrap equipment, beige label	Bunching block - 1:8 ratio
139-R004	Versablock® Rotating Terminal Block (139-Series), 32 pair diode alarm matrix block, 8x32, single wire-wrap cross-connect, single wire-wrap equipment, diode circuits installed	Diode alarm matrix, 1:3 ratio (max. 32 alarm inputs, max. 96 alarm outputs)

Note: Order by Part Number.

REV. A 10/19

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, “Bourns”).

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns’ knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user’s application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user’s sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products’ data sheets in the section entitled “Applications.” Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user’s sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or “automotive grade” does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products’ data sheets in the section entitled “Applications.” Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user’s sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: <http://www.bourns.com/legal/disclaimers-terms-and-policies>

PDF: <http://www.bourns.com/docs/Legal/disclaimer.pdf>