

MATERIAL DECLARATION SHEET



Material Number	1250A-3S series			
Product Line	SPD			
Compliance Date	2025/9/30			
RoHS Compliant	Yes	MSL	1	

NO	Construction Element (subpart)	Homogeneous Materials	Material weight [g]	Homogeneous Material	CASRN	Materials Mass %	Material Mass % of total unit wt.	Subpart mass of total wt • (%)
				Substances	if applicable			
1	Varistor	Ceramic	71.5	Zinc oxide	1314-13-2	99.00%	19.40%	19.60%
				Manganese oxide	1344-43-0	0.25%	0.05%	
				Nickel oxide	1313-99-1	0.25%	0.05%	
				Cobalt oxide	1307-96-6	0.25%	0.05%	
				Bismuth trioxide	1304-76-3	0.25%	0.05%	
	Termination		3	Silver	7440-22-4	100.00%	0.82%	0.82%
2	Plastic shell	PBT	159.9	Polybutylene terephthalate	63440-93-7	80.00%	35.06%	43.83%
				Glass fiber	65997-17-3	20.00%	8.77%	
3	Spring	Spring	1	Iron	7439-89-6	98.00%	0.27%	0.27%
				Manganese	7439-96-5	0.65%	0.00%	
				Carbon	7440-44-0	0.65%	0.00%	
				Silicon	7440-21-3	0.20%	0.00%	
				Misc not to declare	---	0.50%	0.00%	

MATERIAL DECLARATION SHEET



4	Switch	Brass H62(C2800)	2.4	Copper	7440-50-8	65.00%	0.43%	0.66%
				Lead	7439-92-1	0.02%	0.00%	
				Zinc	7440-66-6	34.95%	0.23%	
				Iron	7439-89-6	0.03%	0.00%	
		Plastic shell	2.66	PPA	24938 - 64 - 5	50.00%	0.36%	0.73%
				Glass fiber.	65997-17-3	30.00%	0.22%	
				Flame retardant (C18H16Br4O3) n	68928-70-1	12.00%	0.09%	
				Flame retardant Sb2O3	1309-64-4	8.00%	0.06%	
		Phosphorous copper	0.9	Copper	7440-50-8	95.20%	0.23%	0.25%
				Tin	7440-31-5	4.80%	0.01%	
		Cold rolled steel	0.12	Iron	7440-22-4	90.00%	0.03%	0.03%
				Carbon	7440-02-0	10.00%	0.00%	
5	Electrode	Copper part	89.1	Iron	7439-89-6	73.00%	0.34%	0.46%
				Chromium	7440-47-3	18.00%	0.08%	
				Nickel	7440-02-0	9.00%	0.04%	
6	Low-temperature alloys	Alloys Solder	1.5	Copper	7440-50-8	91.55%	22.36%	24.42%
				Tin	7440-31-5	8.00%	1.95%	
				Zinc	31396-84-6	0.30%	0.07%	
				Phosphorus	7723-14-0	0.15%	0.04%	
6	Low-temperature alloys	Alloys Solder	1.5	Tin	7440-31-5	42.00%	0.17%	0.41%
				Bismuth	7440-69-9	58.00%	0.24%	

MATERIAL DECLARATION SHEET



7	Potting adhesive	Potting adhesive	15.5	Polydimethylsiloxane	68083-19-2	60.00%	2.55%	4.25%
				Polymethylhydrosiloxane	63148-57-2	5.00%	0.21%	
				Alumina	1344-28-1	24.00%	1.02%	
				Aluminum hydroxide	21645-51-2	10.00%	0.42%	
				Platinum	68478-92-2	0.20%	0.01%	
				Carbon black	1333-86-4	0.80%	0.03%	
8	Screw	SUS304	15.4	Carbon	7440-44-0	0.19%	0.01%	4.22%
				Manganese	7439-96-5	0.78%	0.03%	
				Phosphorus	7723-14-0	0.02%	0.00%	
				Sulfur	7704-34-9	0.01%	0.00%	
				Silicon	7440-21-3	0.04%	0.00%	
				Aluminum	7429-90-5	0.04%	0.00%	
				Iron	7439-89-6	98.91%	4.18%	
9	Ink Printing	Ink	0.15	Epoxy Resins	61788-97-4	60.00%	0.02%	0.04%
				Titanium dioxide powder, color powder	1333-86-4	35.00%	0.01%	
				Other additives	67763-03-5	5.00%	0.00%	

Total 364.81

This Document was updated:Sept. 2025

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.