

# Model 3520 %" Diameter 5-Turn Bushing Mount WIREWOUND ELEMENT



#### **FEATURES**

- SILVERWELD® termination eliminates vulnerable single wire termination
- High temperature performance + 125°C
- Outstanding resistance to humidity. Exceeds humidity cycling requirements of MIL-R-12934
- Housing: high temperature, moisture resistant, thermosetting plastic
- 100% contact pressure control assures low noise and long rotational life
- Performance of the Model 3520 is guaranteed by Bourns Reliability Assurance Program which includes individual inspection to published electrical and physical characteristics
- Custom design capability is available to satisfy your most demanding and difficult special requirements

Actual Size



# STANDARD RESISTANCES

Resistance (ohms)	Part Number*	Resolution (percent)	Resistance (ohms)	Part Number*	Resolution (percent)
25	3520S-1-250	0.077	5,000	3520S-1-502	0.032
50	3520S-1-500	0.072	10,000	3520S-1-103	0.027
100	3520S-1-101	0.072	20,000	3520S-1-203	0.023
200	3520S-1-201	0.063	50,000	3520S-1-503	0.018
500	35208-1-501	0.045	75,000	3520S-1-753	0.014
1,000	3520S-1-102	0.036	100,000	3520S-1-104	0.014
2.000	3520S-1-202	0.028	250,000	3520S-1-254	0.012

 $<sup>\</sup>ensuremath{^{\circ}}$  The last three digits of the part number represent the resistance in standard code.

## Model 3520 Wirewound Potentiometer

### **SPECIFICATIONS**

THE SPECIFICATIONS LISTED BELOW ARE FOR THE STANDARD MODEL. MODIFICATIONS OF ALL TYPES (MECHANICAL, ELECTRICAL AND ENVIRONMENTAL) CAN BE CUSTOM ENGINEERED TO YOUR SPECIFIC REQUIREMENTS.

ELECTRICAL CHARACTERISTICS	
Resistance Range	25Ω to 250K ohms
Resistance Tolerance*	±3.0%
Linearity (Independent)*	±0.3%
Resolution	See Standard Resistance Table
Effective Electrical Angle*	1800° (+10°,0°)
Absolute Minimum Resistance*	$1\Omega$ or 0.1%, whichever is greater
Noise*	100Ω maximum
Power Rating: 70°C 125°C	
Dielectric Strength Sea Level 80,000	1500 volts AC minimum
Insulation Resistance, 500 Volts DC*	1000 megohms minimum
ENVIRONMENTAL CHARACTERISTICS	
Operating Temperature Range	—65°C to +125°C
Temperature Coefficient of Wire**	20 PPM/°C maximum
Humidity	MIL-R-12934, Humidity Cycling
Vibration Wiper Bounce Wiper Shift	0.1 millisecond maximum
Shock Wiper Bounce and Wiper Shift	,
Load Life	,


Sand and Dust	MIL-E-5272
Fungus	MIL-E-5272
Salt Spray	MIL-STD-202, Method 101A
MECHANICAL AND PHYSICA	AL CHARACTERISTICS
Mechanical Angle*	1800° (+10°,0°)
Shaft Runout*	
Shaft Radial Play*	.002 in. T.I.R.
	1,000,000 shaft revolutions
Stop Strength	48 ozin. minimum
Torque*	
Ganging	2 cups maximum
Weight	Approximately 0.7 oz.
Terminals	
Marking*	

#### NOTE


- \*100% or statistical sampling inspection performed to insure highest quality.
- \*\*Consult manufacturer for complete specifications for resistances below 2000 and above 75K  $\!\Omega.$


Specifications are subject to change without notice.

3520



LOCKWASHER AND MOUNTING NUT SUPPLIED WITH EACH UNIT





TOLERANCES: EXCEPT WHERE NOTED DECIMALS: XX  $\pm$  .010, XXX  $\pm$  .005 FRACTIONS:  $\pm\frac{1}{16}$ 

