


- Designed for Complementary Use with BDW63, BDW63A, BDW63B, BDW63C and BDW63D
- 60 W at 25°C Case Temperature
- 6 A Continuous Collector Current
- Minimum h_{FE} of 750 at 3V, 2 A



Pin 2 is in electrical contact with the mounting base.

MDTRACA

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING			VALUE	UNIT
	BDW64		-45	
	BDW64A		-60	
Collector-base voltage (I _E = 0)	BDW64B	V _{CBO}	-80	V
	BDW64C		-100	
	BDW64D		-120	
	BDW64		-45	
Collector-emitter voltage (I _B = 0) (see Note 1)	BDW64A		-60	
	BDW64B	V_{CEO}	-80	V
	BDW64C		-100	
	BDW64D		-120	
Emitter-base voltage		V _{EBO}	-5	V
Continuous collector current		I _C	-6	Α
Continuous base current		Ι _Β	-0.1	Α
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)			60	W
Continuous device dissipation at (or below) 25°C free air temperature (see Note 3)			2	W
Unclamped inductive load energy (see Note 4)		½Ll _C ²	50	mJ
Operating junction temperature range		Tj	-65 to +150	°C
Operating temperature range		T _{stg}	-65 to +150	°C
Operating free-air temperature range	T _A	-65 to +150	°C	

- NOTES: 1. These values apply when the base-emitter diode is open circuited.
 - 2. Derate linearly to 150°C case temperature at the rate of 0.48 W/°C.
 - 3. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.
 - 4. This rating is based on the capability of the transistor to operate safely in a circuit of: L = 20 mH, $I_{B(on)}$ = -5 mA, R_{BE} = 100 Ω , $V_{BE(off)}$ = 0, R_S = 0.1 Ω , V_{CC} = -20 V.



electrical characteristics at 25°C case temperature (unless otherwise noted)

	PARAMETER		TES	T CONDITIONS		MIN	TYP	MAX	UNIT
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C = -30 mA	I _B = 0	(see Note 5)	BDW64 BDW64A BDW64B BDW64C BDW64D	-45 -60 -80 -100 -120			V
I _{CEO}	Collector-emitter cut-off current		$I_{B} = 0$		BDW64 BDW64A BDW64B BDW64C BDW64D			-0.5 -0.5 -0.5 -0.5 -0.5	mA
I _{CBO}	Collector cut-off current	$\begin{split} V_{CB} &= -45 \text{ V} \\ V_{CB} &= -60 \text{ V} \\ V_{CB} &= -80 \text{ V} \\ V_{CB} &= -100 \text{ V} \\ V_{CB} &= -120 \text{ V} \\ V_{CB} &= -45 \text{ V} \\ V_{CB} &= -60 \text{ V} \\ V_{CB} &= -80 \text{ V} \\ V_{CB} &= -100 \text{ V} \\ V_{CB} &= -120 \text{ V} \end{split}$	_	T _C = 150°C	BDW64 BDW64A BDW64C BDW64D BDW64 BDW64A BDW64B BDW64C BDW64D			-0.2 -0.2 -0.2 -0.2 -0.2 -5 -5 -5 -5	mA
I _{EBO}	Emitter cut-off current	V _{EB} = -5 V	I _C = 0					-2	mA
h _{FE}	Forward current transfer ratio	$V_{CE} = -3 V$ $V_{CE} = -3 V$	$I_C = -2 A$ $I_C = -6 A$	(see Notes 5 and 6)		750 100		20000	
V _{BE(on)}	Base-emitter voltage	V _{CE} = -3 V	I _C = -2 A	(see Notes 5 and 6)				-2.5	V
V _{CE(sat)}	Collector-emitter saturation voltage	$I_B = -12 \text{ mA}$ $I_B = -60 \text{ mA}$	$I_C = -2 A$ $I_C = -6 A$	(see Notes 5 and 6)				-2.5 -4	V
V _{EC}	Parallel diode forward voltage	I _E = -6 A	I _B = 0					-3.5	V

NOTES: 5. These parameters must be measured using pulse techniques, $t_0 = 300 \mu s$, duty cycle $\leq 2\%$.

thermal characteristics

	PARAMETER			MAX	UNIT
$R_{\theta JC}$	Junction to case thermal resistance			2.08	°C/W
$R_{\theta JA}$	Junction to free air thermal resistance			62.5	°C/W

resistive-load-switching characteristics at 25°C case temperature

	PARAMETER	TEST CONDITIONS †			MIN	TYP	MAX	UNIT
t _{on}	Turn-on time	I _C = -3 A	$I_{B(on)} = -12 \text{ mA}$	$I_{B(off)} = 12 \text{ mA}$		1		μs
t _{off}	Turn-off time	$V_{BE(off)} = 4.5 \text{ V}$	$R_L = 10 \Omega$	$t_p = 20 \ \mu s, \ dc \le 2\%$		5		μs

[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

^{6.} These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

TYPICAL CHARACTERISTICS

TYPICAL DC CURRENT GAIN vs **COLLECTOR CURRENT** TCS125AD 40000 $T_c = -40^{\circ}C$ 25°C $T_c = 100$ °C h_{FE} - Typical DC Current Gain 10000 1000 -3 V = 300 μs, duty cycle < 2% 100 -0.5 -1.0 -10 Ic - Collector Current - A

COLLECTOR-EMITTER SATURATION VOLTAGE




Figure 1.

Figure 2.

COLLECTOR CURRENT TCS125AF -3.0 $T_c = -40^{\circ}C$ V_{BE(sat)} - Base-Emitter Saturation Voltage -25°C 100°C -2.0 -2.5 -1.0 -1.5 $= I_{c} / 100$ = 300 μs, duty cycle < 2% -0.5 -0.5 -1.0 -10


I_c - Collector Current - A

Figure 3.

BASE-EMITTER SATURATION VOLTAGE

PRODUCT INFORMATION

MAXIMUM SAFE OPERATING REGIONS



THERMAL INFORMATION

