

Features

- RoHS compliant*
- IEEE802.3af/ANSI X3.263



Model SM51108EL is obsolete and not recommended for new designs. Model **SM51108PEL** is the preferred alternative.

Applications


- VoIP
- PoE

SM51108L 10/100 Base Tx VoIP Modules (Power over Ethernet - PoE)

Electrical Specifications

Inductance - Open Circuit 350 μ H min.
 ... (100 KHz, 0.1 V with 8 mA DC bias)
 Turns Ratio 1CT: 1CT
 Insertion Loss
 1-100 MHz, -1.2 dB max.
 Return Loss (@ 100 ohms)
 1-30 MHz.....-16 dB min.
 40 MHz.....-14 dB min.
 50 MHz.....-13 dB min.
 60-80 MHz.....-12 dB min.
 Cross Talk
 60 MHz.....-40 dB min.
 100 MHz.....-35 dB min.
 DCMRR
 30 MHz.....-43 dB min.
 60 MHz.....-37 dB min.
 100 MHz.....-33 dB min.
 PoE Current..... Up to 320 mA DC
 Isolation 1500 VAC
 Operating Temperature
-40 °C to +85 °C

Electrical Schematic




Packaging Specifications

..... 700 pcs./reel


How To Order

Model **SM51108E L**
 Termination _____
 L = Tin only (RoHS Compliant)

Product Dimensions



Recommended Layout



DIMENSIONS: $\frac{\text{MM}}{\text{INCHES}}$