


MATERIAL DECLARATION SHEET



Material Number	PWR263S-35			
Product Line	Fixed Resistor			
Compliance Date	10/31/2025			
RoHS Compliant		MSL	1	

PWR263S > 4 Ω

No.	Construction Element (Subpart)	Homogeneous Material	Material Weight (g)	Homogeneous Material Substance	CASRN	Material Mass %	Material Mass % of total unit wt.	Subpart mass of total wt. (%)
1	Housing	Epoxy Molding Compound	0.5000	Silica, vitreous	60676-86-0	75.0000%	26.9862%	35.9816%
				Epoxy cresol novolac resin	29690-82-2	14.0000%	5.0374%	
				Phenol formaldehyde resin	9003-35-4	7.0000%	2.5187%	
				3,5,3',5'-Tetrabromobisphenol A, epichlorohydrin polymer	40039-93-8	2.0000%	0.7196%	
				Carbon black	1333-86-4	1.0000%	0.3598%	
				Antimony trioxide	1309-64-4	1.0000%	0.3598%	
2	Back Plate	Copper C102	0.6606	Copper	7440-50-8	99.9990%	47.5384%	47.5389%
				Oxygen	7782-44-7	0.0010%	0.0005%	
		Plating	0.0083	Tin	7440-31-5	100.0000%	0.5973%	0.5973%
		Plating	0.0019	Nickel	7440-02-0	100.0000%	0.1367%	0.1367%
3	Terminals	Copper C102	0.1100	Copper	7440-50-8	99.9990%	7.9159%	7.9159%
				Oxygen	7782-44-7	0.0010%	0.0001%	
		Plating	0.0075	Tin	7440-31-5	100.0000%	0.5397%	0.5397%
4	Solder Paste	Solder	0.0200	Tin	7440-31-5	95.0000%	1.3673%	1.4393%
				Silver	7440-22-4	3.0000%	0.0432%	
				Copper	7440-50-8	0.5000%	0.0072%	
				Misc, not to declare	N/A	1.5000%	0.0216%	
5	Substrate	Alumina	0.0780	Aluminum oxide	1344-28-1	96.0000%	5.3886%	5.6131%
				Silicon dioxide	7631-86-9	2.0000%	0.1123%	
				Magnesium oxide	1309-48-4	1.0000%	0.0561%	

MATERIAL DECLARATION



6	Termination Pad	Ink	0.0020	Calcium oxide	1305-78-8	1.0000%	0.0561%	0.1439%
				Silver	7440-22-4	95.6000%	0.1376%	
				Platinum	7440-06-4	2.0000%	0.0029%	
				Dibismuth-trioxide	1304-76-3	1.0000%	0.0014%	
				Lead	7439-92-1	1.0000%	0.0014%	
7	Resistive Ink	Ink	0.0008	Copper	7440-50-8	0.4000%	0.0006%	0.0576%
				Aluminum oxide	1344-28-1	3.0000%	0.0017%	
				Quartz	14808-60-7	1.0000%	0.0006%	
				Ceramic w/o Declarable	66402-68-4	11.0000%	0.0063%	
				Titanium-dioxide	13463-67-7	1.0000%	0.0006%	
				Zinc oxide	1314-13-2	0.5000%	0.0003%	
				Silicon dioxide	7631-86-9	14.5000%	0.0083%	
				Palladium	7440-05-3	11.0000%	0.0063%	
				Silver	7440-22-4	8.0000%	0.0046%	
				Copper	7440-50-8	1.0000%	0.0006%	
				Glass w/o Declarable	65997-17-3	19.0000%	0.0109%	
8	Encapsulant Glaze Ink	Ink	0.0005	Lead in Glass	7439-92-1	19.0000%	0.0109%	0.0360%
				Ruthenium (IV) oxide	12036-10-1	11.0000%	0.0063%	
				Glass without declarable substances	65997-17-3	98.0000%	0.0353%	
				Pigment Green 17 (C.I.)	1308-38-9	2.0000%	0.0007%	

Total Weight 1.3896

This Document was updated on: 11/11/2025

Important remarks:

1. It is the responsibility of the user to verify they are accessing the latest version.
2. Resistive material weight will be different based on the resistance value and some Homogeneous material might not be present.