



Features

- 0.1 % tolerance from 100 ohms to 360K ohms
- Lead free
- RoHS compliant*
- Three layer contacting process with nickel barrier helps prevent leaching and provides excellent solderability

- Suitable for most types of soldering processes
- Paper tape on reel for automatic placement

CRP0603 Series - Precision Chip Resistors


Electrical Characteristics

Characteristic	Model CRP0603
Power Rating @ 70 °C	1/10 W
Operating Temperature Range	-55 °C to +125 °C
Derated to Zero Load at	+125 °C
Maximum Working Voltage	50 V, not to exceed power rating
Maximum Overload Voltage	100 V
Resistance Range: (E-96 + E-24 Values)	100 ohms to 360K ohms
Temperature Coefficient	±50 PPM/°C, 100 ohms to 35.7K ohms ±100 PPM/°C, 36K ohms to 360K ohms


Characteristic Data

Tests per IEC115-1	ΔR Max.
Load Life (1000 Hours)	±(0.5 % + 0.05 ohms)
Load Life Humidity (1000 Hours)	±(0.5 % + 0.05 ohms)
Short Time Overload	±(0.5 % + 0.05 ohms)


Derating Curve



Dimensional Drawing



Construction



Reliable Electronic Solutions

Asia-Pacific:

TEL +886-2 25624117
FAX +886-2 25624116

Europe:

TEL +41-41 7685555
FAX +41-41 7685510

North America:

TEL +1-951 781-5500
FAX +1-951 781-5700

www.bourns.com

*RoHS Directive 2002/95/EC Jan 27 2003 including Annex


Specifications are subject to change without notice.

Customers should verify actual device performance in their specific applications.


CRP0603 Series - Precision Chip Resistors

BOURNS®

Soldering Profile for Lead Free Chip Resistors and Arrays



Packaging Dimensions (Conforms to EIA RS-481A)



Marking on reel: Part number, quantity, resistance value and tolerance, date code.

CRP0603 Series - Precision Chip Resistors

BOURNS®

Resistor Markings

CRP0603
EIA-96 Marking



0.1 % marking
Value = 12.4K ohms

Marking Explanation

E-24: 3 digits; first two digits are significant, third digit is number of zeros to follow.

E-96: EIA-96 marking (see table below).

EIA-96 Marking for CRP0603, 0.1 %

Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value	Code	R Value
01	100	13	133	25	178	37	237	49	316	61	422	73	562	85	750
02	102	14	137	26	182	38	243	50	324	62	432	74	576	86	768
03	105	15	140	27	187	39	249	51	332	63	442	75	590	87	787
04	107	16	143	28	191	40	255	52	340	64	453	76	604	88	806
05	110	17	147	29	196	41	261	53	348	65	464	77	619	89	825
06	113	18	150	30	200	42	267	54	357	66	475	78	634	90	845
07	115	19	154	31	205	43	274	55	365	67	487	79	649	91	866
08	118	20	158	32	210	44	280	56	374	68	499	80	665	92	887
09	121	21	162	33	215	45	287	57	383	69	511	81	681	93	909
10	124	22	165	34	221	46	294	58	392	70	523	82	698	94	931
11	127	23	169	35	226	47	301	59	402	71	536	83	715	95	953
12	130	24	174	36	232	48	309	60	412	72	549	84	732	96	976

This table shows the first two digits for the three-digit EIA-96 part marking scheme. The third character is a letter multiplier:

Y=10⁻² X=10⁻¹ A=10⁰ B=10¹ C=10² D=10³ E=10⁴ F=10⁵

How To Order

CRP 0603 - B Z - 7871 E LF

Model _____
(CRP = Precision Chip Resistor)

Size _____
0603 = 0603 Size

Resistance Tolerance _____
B = ±0.1 %

TCR (ppm/°C) _____
Z = ±50 PPM/°C, 100 ohms through 35.7K ohms
X = ±100 PPM/°C, 36K ohms through 360K ohms

Resistance Value _____
First three digits are significant, fourth digit represents number of zeros to follow (example: 7871 = 7.87K ohms)

Packaging _____
E = 5,000 pieces on 180 mm (7 inch) reel

Termination _____
LF = Tin-plated (lead free)