

NEW PRODUCT RELEASE

SINGLFUSE™ SMD FUSES







Bourns SinglFuse Product Line Announces New AEC-Q200 Compliant Automotive Grade SMD Fuse Families

Model SF-1206SA-W, SF-2410FPA-W and SF-2410FA-W Series

Riverside, California – February 6, 2020 – Bourns is pleased to announce the introduction of new families of AEC-Q200 compliant, automotive grade SMD fuses to complement its already successful line of SinglFuse™ SMD Fuse products.

The new Model <u>SF-1206SA-W</u>, <u>SF-2410FPA-W</u> and <u>SF-2410FA-W</u> series are UL 248-14 listed, RoHS compliant* and halogen free**. All three series meet Bourns' internal AEC-Q200 equivalent test plan with more severe test conditions and larger sample sizes to ensure performance robustness in certain harsh environments. These new model families are intended for use in a variety of industrial, medical*** (low to medium risk), telecom and Battery Management Systems applications.

Series	Size (EIA)	Fuse Type	Rated Current	Rated Voltage	UL Listed	RoHS Compliant*	Halogen Free**	AEC-Q200 Compliant****
SF-1206SA-W	1206	Slow Blow	1.5 A – 15 A	32 – 65 Vdc	Yes	Yes	Yes	Yes
SF-2410FPA-W	2410	Fast Acting Precision	1 A – 10 A	125 Vdc	Yes	Yes	Yes	Yes
SF-2410FA-W	2410	Fast Acting	12 A – 20 A	65 Vdc	Yes	Yes	Yes	Yes

For additional information on Bourns® SinglFuse™ products, please visit the Bourns website at www.bourns.com/products/circuit-protection/singlfuse-smd-fuses. Should you have any questions, please feel free to contact Bourns Customer Service/Inside Sales.

Features

- Fast acting & slow blow fusing speeds
- EIA1206 & 2410 footprints
- AEC-Q200 compliant****
- UL 248-14 listed
- RoHS compliant* and halogen free**

Applications

- Industrial
- Medical (low to medium risk)***
- Telecom
- Battery Management Systems

SF1933

^{*} RoHS Directive 2015/863, Mar 31, 2015 and Annex.

^{**} Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

^{***} Bourns® products have not been designed for and are not intended for use in "lifesaving," "life-critical" or "life-sustaining" applications nor any other applications where failure or malfunction of the Bourns® product may result in personal injury or death. See Legal Disclaimer Notice http://www.bourns.com/docs/legal/disclaimer.pdf.

^{****} Meets Bourns internal AEC-Q200 equivalent test plan.