


- Designed for Complementary Use with BDW74, BDW74A, BDW74B, BDW74C and BDW74D
- 80 W at 25°C Case Temperature
- 8 A Continuous Collector Current
- Minimum h_{FE} of 750 at 3V, 3 A



TO-220 PACKAGE (TOP VIEW) B 1 C E 3

Pin 2 is in electrical contact with the mounting base.

MDTRACA

1

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING	SYMBOL	VALUE	UNIT	
	BDW73		45	
	BDW73A		60	
Collector-base voltage (I _E = 0)	BDW73B	V _{CBO}	80	V
	BDW73C		100	
	BDW73D		120	
	BDW73		45	
	BDW73A		60	
Collector-emitter voltage (I _B = 0) (see Note 1)	BDW73B	V_{CEO}	80	V
	BDW73C		100	
	BDW73D		120	
Emitter-base voltage		V _{EBO}	5	V
Continuous collector current		I _C	8	Α
Continuous base current		I _B	0.3	Α
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)	P _{tot}	80	W	
Continuous device dissipation at (or below) 25°C free air temperature (see Note 3)			2	W
Unclamped inductive load energy (see Note 4)		½Ll _C ²	75	mJ
Operating junction temperature range		Tj	-65 to +150	°C
Operating temperature range		T _{stg}	-65 to +150	°C
Operating free-air temperature range		T _A	-65 to +150	°C

- NOTES: 1. These values apply when the base-emitter diode is open circuited.
 - 2. Derate linearly to 150°C case temperature at the rate of 0.64 W/°C.
 - 3. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.
 - 4. This rating is based on the capability of the transistor to operate safely in a circuit of: L = 20 mH, $I_{B(on)}$ = 5 mA, R_{BE} = 100 Ω , $V_{BE(off)}$ = 0, R_S = 0.1 Ω , V_{CC} = 20 V.



electrical characteristics at 25°C case temperature (unless otherwise noted)

	PARAMETER		TES	T CONDITIONS		MIN	TYP	MAX	UNIT
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C = 30 mA	I _B = 0	(see Note 5)	BDW73 BDW73A BDW73B BDW73C BDW73D	45 60 80 100 120			V
I _{CEO}	Collector-emitter cut-off current	V _{CE} = 30 V V _{CE} = 30 V V _{CE} = 40 V V _{CE} = 50 V V _{CE} = 60 V	$I_{B} = 0$		BDW73 BDW73A BDW73B BDW73C BDW73D			0.5 0.5 0.5 0.5 0.5	mA
I _{CBO}	Collector cut-off current	~-	E = 0 E = 0	$T_{C} = 150^{\circ}C$	BDW73 BDW73A BDW73C BDW73D BDW73 BDW73A BDW73A BDW73C BDW73C BDW73C			0.2 0.2 0.2 0.2 0.2 5 5 5 5	mA
I _{EBO}	Emitter cut-off current	V _{EB} = 5 V	I _C = 0					2	mA
h _{FE}	Forward current transfer ratio	$V_{CE} = 3 V$ $V_{CE} = 3 V$	$I_C = 3 A$ C = 8 A	(see Notes 5 and 6)		750 100		20000	
V _{BE(on)}	Base-emitter voltage	V _{CE} = 3 V	$I_C = 3 A$	(see Notes 5 and 6)				2.5	V
V _{CE(sat)}	Collector-emitter saturation voltage	$I_B = 12 \text{ mA}$ $I_B = 80 \text{ mA}$	$I_C = 3 \text{ A}$ $I_C = 8 \text{ A}$	(see Notes 5 and 6)				2.5 4	V
V _{EC}	Parallel diode forward voltage	I _E = 8 A	I _B = 0					3.5	V

NOTES: 5. These parameters must be measured using pulse techniques, $t_0 = 300 \mu s$, duty cycle $\leq 2\%$.

thermal characteristics

	PARAMETER			MAX	UNIT
$R_{\theta JC}$	Junction to case thermal resistance			1.56	°C/W
$R_{\theta JA}$	Junction to free air thermal resistance			62.5	°C/W

resistive-load-switching characteristics at 25°C case temperature

Ī		PARAMETER	TEST CONDITIONS †			MIN	TYP	MAX	UNIT
ĺ	t _{on}	Turn-on time	I _C = 3 A	I _{B(on)} = 12 mA	$I_{B(off)} = -12 \text{ mA}$		1		μs
ĺ	t _{off}	Turn-off time	$V_{BE(off)} = -3.5 \text{ V}$	$R_L = 10 \Omega$	$t_p = 20 \ \mu s, \ dc \le 2\%$		5		μs

[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

^{6.} These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

TYPICAL CHARACTERISTICS

TYPICAL DC CURRENT GAIN COLLECTOR CURRENT TCS130AD 50000 $T_c = -40^{\circ}C$ 25°C = 100°C h_{FE} - Typical DC Current Gain 10000 1000 3 V = 300 μ s, duty cycle < 2% 100 10 0.5 1.0 I_c - Collector Current - A

Figure 1.

COLLECTOR-EMITTER SATURATION VOLTAGE




Figure 2.

BASE-EMITTER SATURATION VOLTAGE




Figure 3.

MAXIMUM SAFE OPERATING REGIONS





Figure 4.

THERMAL INFORMATION

MAXIMUM POWER DISSIPATION



PRODUCT INFORMATION