

## Features

- RoHS compliant\*
- Bifilar or sector windings
- Wide frequency range over 1000MHz
- Rated current 0.2 to 0.5A
- Model DR331 recommended for new designs

## DR332 Series Surface Mount Data Line Chokes


### Electrical Characteristics (@ 25 °C)

Bourns Part Number	L (1-4) @ 100 kHz, 0.1 Vrms (μH)	LL (1-4) @ 100 kHz, 0.1 Vrms (Typ.) (2-3 Short)	RDC (Ω) (Winding) Max. (Ω)	Rated Current Max.	Winding
DR332-113AE	11.0 +25 %	0.05 μH	0.12	0.5 A	Bifilar
DR332-253AE	25.0 +25 %	1.50 μH	0.20	0.5 A	Sector
DR332-513AE	51.0 +25 %	2.00 μH	0.30	0.5 A	Sector
DR332-474AE	470.0 +25 %	0.28 μH	0.28	0.5 A	Bifilar
DR332-105AE	1000.0 +25 %	0.29 μH	0.40	0.5 A	Bifilar
DR332-475AE	4700.0 +25 %	0.30 μH	0.70	0.2 A	Bifilar


Note: For tape and reel packaging, add "E" at the end of part number.

Rated Voltage .....80 Vdc/42 Vac  
 Hipot (1 sec.).....250 Vac/60 Hz, 3 mA  
 \*Operating Temperature ..-40 to +135 °C  
 \*Storage Temperature .....-40 to +135 °C  
 Temperature Rise  
 .....30 °C max. at rated current  
 Resistance to Solder Heat  
 .....260 °C 10 sec.  
 Core .....Ferrite  
 Wire .....Enameled copper wire (Class F)  
 Base .....PPHS (UL 94V-0)  
 Terminal .....Cu/Ni/Sn  
 Adhesive.....Epoxy resin  
 Packaging .....1500 pcs. per reel

### Product Dimensions



### Recommended PCB Layout




\*Model DR443-475:  
 Operating Temperature .....-40 to +100 °C  
 Storage Temperature .....-40 to +100 °C


### How to Order

Model DR332 - 513 AE  
 Value Code \_\_\_\_\_  
 See Model-Value Table  
 Termination \_\_\_\_\_  
 AE = Cu/Ni/Sn (Lead Free)

### Schematic



### Typical Part Marking




\*RoHS Directive 2002/95/EC Jan 27, 2003 including Annex.  
 Specifications are subject to change without notice.  
 Customers should verify actual device performance in their specific applications.

## Applications


- For the suppression of EMI in data and signal lines, e.g. CAN Bus

# DR332 Series Surface Mount Data Line Chokes




## Solder Profile



## Impedance vs. Frequency



## Insertion Loss vs. Frequency



Specifications are subject to change without notice.  
Customers should verify actual device performance in their specific applications.

# DR332 Series Surface Mount Data Line Chokes

## Packaging Specifications

