
BD249, BD249A, BD249B, BD249C NPN SILICON POWER TRANSISTORS

BOURNS®

- Designed for Complementary Use with the BD250 Series
- 125 W at 25°C Case Temperature
- 25 A Continuous Collector Current
- 40 A Peak Collector Current
- Customer-Specified Selections Available



Pin 2 is in electrical contact with the mounting base.

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING	SYMBOL	VALUE	UNIT		
	BD249		55		
Collector-emitter voltage ($R_{BE} = 100 \Omega$)	BD249A	N	70	v	
$Collector-entitler voltage (R_{BE} = 100 \Omega)$	BD249B	VCER	90	v	
	BD249C		115		
	BD249		45		
Collector-emitter voltage ($I_C = 30 \text{ mA}$)	BD249A	v	60	V	
	BD249B	V _{CEO}	80		
	BD249C		100		
Emitter-base voltage		V _{EBO}	5	V	
Continuous collector current		۱ _C	25	A	
Peak collector current (see Note 1)		I _{CM}	40	A	
Continuous base current		I _B	5	A	
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)	P _{tot}	125	W		
Continuous device dissipation at (or below) 25°C free air temperature (see Note	P _{tot}	3	W		
Unclamped inductive load energy (see Note 4)		½LI _C ²	90	mJ	
Operating junction temperature range		Тj	-65 to +150	°C	
Storage temperature range		T _{stg}	-65 to +150	°C	
Lead temperature 3.2 mm from case for 10 seconds		TL	250	°C	

NOTES: 1. This value applies for $t_p \leq 0.3$ ms, duty cycle $\leq 10\%.$

2. Derate linearly to 150°C case temperature at the rate of 1 W/°C.

3. Derate linearly to 150°C free air temperature at the rate of 24 mW/°C.

4. This rating is based on the capability of the transistor to operate safely in a circuit of: L = 20 mH, $I_{B(on)}$ = 0.4 A, R_{BE} = 100 Ω , $V_{BE(off)}$ = 0, R_S = 0.1 Ω , V_{CC} = 20 V.

PRODUCT INFORMATION

BD249, BD249A, BD249B, BD249C NPN SILICON POWER TRANSISTORS



electrical characteristics at 25°C case temperature

PARAMETER			TEST CONDITION	S	MIN			UNIT
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C = 30 mA (see Note 5)	I _B = 0	BD249 BD249A BD249B BD249C	45 60 80 100			v
I _{CES}	Collector-emitter cut-off current	$V_{CE} = 55 V$ $V_{CE} = 70 V$ $V_{CE} = 90 V$ $V_{CE} = 115 V$	$V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$ $V_{BE} = 0$	BD249 BD249A BD249B BD249C			0.7 0.7 0.7 0.7	mA
I _{CEO}	Collector cut-off current	$V_{CE} = 30 V$ $V_{CE} = 60 V$	I _B = 0 I _B = 0	BD249/249A BD249B/249C			1 1	mA
I _{EBO}	Emitter cut-off current	V _{EB} = 5 V	I _C = 0				1	mA
h _{FE}	Forward current transfer ratio	$V_{CE} = 4 V$ $V_{CE} = 4 V$ $V_{CE} = 4 V$	$I_{C} = 1.5 \text{ A}$ $I_{C} = 15 \text{ A}$ $I_{C} = 25 \text{ A}$	(see Notes 5 and 6)	25 10 5			
V _{CE(sat)}	Collector-emitter saturation voltage	$I_B = 1.5 A$ $I_B = 5 A$	I _C = 15 A I _C = 25 A	(see Notes 5 and 6)			1.8 4	V
V _{BE}	Base-emitter voltage	$V_{CE} = 4 V$ $V_{CE} = 4 V$	I _C = 15 A I _C = 25 A	(see Notes 5 and 6)			2 4	V
h _{fe}	Small signal forward current transfer ratio	V _{CE} = 10 V	I _C = 1 A	f = 1 kHz	25			
h _{fe}	Small signal forward current transfer ratio	V _{CE} = 10 V	I _C = 1 A	f = 1 MHz	3			

NOTES: 5. These parameters must be measured using pulse techniques, $t_p = 300 \ \mu s$, duty cycle $\leq 2\%$.

6. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

thermal characteristics

PARAMETER	MIN	ТҮР	MAX	UNIT
R _{0JC} Junction to case thermal resistance			1	°C/W
R _{eJA} Junction to free air thermal resistance			42	°C/W

resistive-load-switching characteristics at 25°C case temperature

	PARAMETER	TEST CONDITIONS [†]			MIN	ТҮР	MAX	UNIT
t _{on}	Turn-on time	I _C = 5 A	$I_{B(on)} = 0.5 A$	$I_{B(off)} = -0.5 A$		0.3		μs
t _{off}	Turn-off time	$V_{BE(off)} = -5 V$	$R_L = 5 \Omega$	t_p = 20 µs, dc \leq 2%		0.9		μs


[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.






BD249, BD249A, BD249B, BD249C NPN SILICON POWER TRANSISTORS

TYPICAL CHARACTERISTICS






PRODUCT INFORMATION

JUNE 1973 - REVISED SEPTEMBER 2002 Specifications are subject to change without notice.

MAXIMUM SAFE OPERATING REGIONS



MAXIMUM POWER DISSIPATION VS **CASE TEMPERATURE** TIS635AA 140 P_{rot} - Maximum Power Dissipation - W 0 09 08 00 07 20 0 0 25 50 75 100 125 150 T_c - Case Temperature - °C

