

BOURNS®

- RoHS compliant*
- Designed for Complementary Use with BD646, BD648, BD650 and BD652
- 62.5 W at 25°C Case Temperature
- 8 A Continuous Collector Current
- Minimum h_{FE} of 750 at 3V, 3 A





MDTRACA



absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING			VALUE	UNIT	
	BD645		80		
Collector-base voltage ($I_{\scriptscriptstyle E}=0$)	BD647	N.	100	V	
Collector-base voltage (I _E = 0)	BD649	V _{СВО}	120		
	BD651		140		
	BD645		60		
Collector-emitter voltage (I _B = 0)	BD647	V	80	V	
	BD649	V_{CEO}	100		
	BD651		120		
Emitter-base voltage		V _{EBO}	5	V	
Continuous collector current		I _C	8	Α	
Peak collector current (see Note 1)		I _{CM}	12	Α	
Continuous base current		Ι _Β	0.3	Α	
Continuous device dissipation at (or below) 25°C case temperature (see Note 2)		P _{tot}	62.5	W	
Continuous device dissipation at (or below) 25°C free air temperature (see Note 3)			2	W	
Unclamped inductive load energy (see Note 4)	½Ll _C ²	50	mJ		
Operating junction temperature range		T _j	-65 to +150	°C	
Storage temperature range	T _{stg}	-65 to +150	°C		
Lead temperature 3.2 mm from case for 10 seconds			260	°C	

- NOTES: 1. This value applies for $t_p \le 0.3$ ms, duty cycle $\le 10\%$.
 - 2. Derate linearly to 150°C case temperature at the rate of 0.4 W/°C.
 - 3. Derate linearly to 150°C free air temperature at the rate of 16 mW/°C.
 - 4. This rating is based on the capability of the transistor to operate safely in a circuit of: L = 20 mH, $I_{B(on)}$ = 5 mA, R_{BE} = 100 Ω , $V_{BE(off)}$ = 0, R_S = 0.1 Ω , V_{CC} = 20 V.

How to Order

Device	Package	Carrier	Order As		
BDxxx	TO-220	Tube	BDxxx-S		

Insert xxx transistor type number 645, 647, 649, etc.

PRODUCT INFORMATION

MAY 1993 - REVISED JUNE 2013

^{*}RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011. Specifications are subject to change without notice.



electrical characteristics at 25°C case temperature (unless otherwise noted)

	PARAMETER	TEST CONDITIONS			MIN	TYP	MAX	UNIT	
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C = 30 mA	I _B = 0	(see Note 5)	BD645 BD647 BD649 BD651	60 80 100 120			V
I _{CEO}	Collector-emitter cut-off current	$V_{CE} = 30 \text{ V}$ $V_{CE} = 40 \text{ V}$ $V_{CE} = 50 \text{ V}$ $V_{CE} = 60 \text{ V}$	$I_{B} = 0$ $I_{B} = 0$ $I_{B} = 0$ $I_{B} = 0$		BD645 BD647 BD649 BD651			0.5 0.5 0.5 0.5	mA
Ісво	Collector cut-off current	$V_{CB} = 40 \text{ V}$ $V_{CB} = 50 \text{ V}$ $V_{CB} = 60 \text{ V}$	$I_{E} = 0$	$T_{C} = 150^{\circ}\text{C}$ $T_{C} = 150^{\circ}\text{C}$ $T_{C} = 150^{\circ}\text{C}$ $T_{C} = 150^{\circ}\text{C}$	BD645 BD647 BD649 BD651 BD645 BD647 BD649 BD651			0.2 0.2 0.2 0.2 2.0 2.0 2.0 2.0	mA
I _{EBO}	Emitter cut-off current	V _{EB} = 5 V	I _C = 0	(see Notes 5 and	6)			5	mA
h _{FE}	Forward current transfer ratio	V _{CE} = 3 V	I _C = 3 A	(see Notes 5 and	6)	750			
V _{CE(sat)}	Collector-emitter saturation voltage	$I_B = 12 \text{ mA}$ $I_B = 50 \text{ mA}$	$I_C = 3 A$ $I_C = 5 A$	(see Notes 5 and	6)			2 2.5	V
V _{BE(sat)}	Base-emitter saturation voltage	I _B = 50 mA	I _C = 5 A	(see Notes 5 and	6)			3	V
V _{BE(on)}	Base-emitter voltage	V _{CE} = 3 V	I _C = 3 A	(see Notes 5 and	6)			2.5	٧

NOTES: 5. These parameters must be measured using pulse techniques, $t_p = 300 \ \mu s$, duty cycle $\leq 2\%$.

thermal characteristics

	PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta JC}$	R _{0JC} Junction to case thermal resistance			2.0	°C/W
$R_{\theta JA}$	Junction to free air thermal resistance			62.5	°C/W

Users should verify actual device performance in their specific applications.

^{6.} These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

TYPICAL CHARACTERISTICS

TYPICAL DC CURRENT GAIN COLLECTOR CURRENT TCS130AD 50000 -40°C 25°C $T_c =$ $T_c = 100$ °C h_{FE} - Typical DC Current Gain 10000 1000 3 V = 300 μ s, duty cycle < 2% 100 1.0 10 0.5

Figure 1.

I_c - Collector Current - A

COLLECTOR-EMITTER SATURATION VOLTAGE




Figure 2.

BASE-EMITTER SATURATION VOLTAGE





Figure 3.


PRODUCT INFORMATION

MAXIMUM SAFE OPERATING REGIONS



THERMAL INFORMATION

MAXIMUM POWER DISSIPATION



PRODUCT INFORMATION