## BOURNS

## **Product Change Notification**

MAGNETICS



Revised March 12, 2014

## Changes to Bourns® Model 1140 High Current Choke Series

Bourns is announcing changes to the Model 1140 High Current Choke Series including manufacturing location, the core slot radius, marking method, winding polarity mark, Minimum Order Quantity (MOQ), Multiples Quantity (Mult), rated current and the center mounting hole diameter. The complete list of affected part numbers are listed in Table 1 on the following page.

The <u>manufacturing location</u> is being transferred from Guangdong, China to Xiamen, China to help streamline the production process. To improve core production yield and reduce core chipping, the <u>core slot radius</u> has been increased (Figure 1). The <u>marking methods</u> have also been changed from an ink-marking to a more durable laser-marking (Figure 2). Another change is the addition of a <u>winding polarity mark</u>, which indicates the start lead of winding (Figure 2). The <u>Minimum Order Quantity (MOQ) / Multiples Quantity (Mult)</u> has changed from 240/24 to 140/70. <u>Rated current</u>, Idc, is redefined with Irms and Isat (Table 1). Lastly, the <u>center mounting hole diameter</u> has been modified (Figure 3).

Qualification tests include drop and humidity, resistance to soldering heat, solderability, temperature rise, terminal strength and thermal shock. The tests were performed with satisfactory results. Evaluation samples are available upon request.

The appearance (i.e., the form) of component is slightly different due to the changed marking method and core slot modification. There is no impact to the fit, function, quality or reliability of the component.

Implementation dates are as follows:

We will begin phasing in this process: June 16, 2014

Date that manufacturing of existing products will cease: June 13, 2014

First date code using the above changes: 1425

## Table 1

Part Number	Before Change	After Change	
	ldc (A)	Irms (A)	Isat(A)
1140-1R8M-RC	27	34.5	80.0
1140-2R2M-RC	27	34.5	80.0
1140-2R7M-RC	27	28.1	80.0
1140-3R3M-RC	27	28.1	80.0
1140-3R9M-RC	27	28.1	80.0
1140-4R7M-RC	27	28.1	80.0
1140-5R6M-RC	27	24.4	80.0
1140-6R8M-RC	27	24.4	73.5
1140-8R2M-RC	27	24.4	70.3
1140-100K-RC	27	21.8	65.3
1140-120K-RC	27	21.8	59.6
1140-150K-RC	27	19.9	53.9
1140-180K-RC	27	17.2	49.2
1140-220K-RC	21	16.2	43.7
1140-270K-RC	21	16.0	39.0
1140-330K-RC	21	15.8	36.5
1140-390K-RC	21	15.1	32.3
1140-470K-RC	14.4	12.3	30.6
1140-560K-RC	14.4	12.0	27.6
1140-680K-RC	14.4	11.4	25.2
1140-820K-RC	14.4	10.9	23.1
1140-101K-RC	14.4	10.5	20.6
1140-121K-RC	14.4	9.9	18.6
1140-151K-RC	11.4	8.3	16.9

Part Number	Before After Change Change		
	Idc (A)	Irms (A)	Isat(A)
1140-181K-RC	11.4	7.8	15.5
1140-221K-RC	11.4	7.4	14.0
1140-271K-RC	11.4	7.0	12.4
1140-331K-RC	11.4	6.1	11.2
1140-391K-RC	9	5.8	10.4
1140-471K-RC	7.2	4.9	9.5
1140-561K-RC	7.2	4.7	8.6
1140-681K-RC	7.2	4.4	7.9
1140-821K-RC	7.2	4.2	7.2
1140-102K-RC	5.5	3.6	6.5
1140-122K-RC	5.5	3.4	5.9
1140-152K-RC	4.5	2.9	5.3
1140-182K-RC	4.5	2.8	4.9
1140-222K-RC	4	2.4	4.4
1140-272K-RC	4	2.2	3.9
1140-332K-RC	2.8	1.9	3.6
1140-392K-RC	2.8	1.8	3.3
1140-472K-RC	2	1.6	3.0
1140-562K-RC	2	1.3	2.8
1140-682K-RC	1.6	1.2	2.5
1140-822K-RC	1.6	1.2	2.3
1140-103K-RC	1.3	1.0	2.1
1140-123K-RC	1.3	0.9	1.9
1140-153K-RC	1.3	0.9	1.7

Figure 1



Before Change - Small Radius



After Change - Larger Radius


Figure 2



Before Change - with Ink Marking



After Change - with Laser Marking and Polarity Mark



If you have any questions or need additional information, please feel free to contact Customer Service/Inside Sales.