























BOURNS® TRIMPOT® POTENTIOMETERS




MULTITURN THROUGH-HOLE SEALED

| | | | | | | | | | |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 3005 | 3006 | 3009 | 3057 | 3059 | 3082 | 3292 | 3296 | 3299 | 3339 |
|  |  |  |  |  |  |  |  |  |  |
| 3/4" Wirewound | 3/4" Cermet | 3/4" Cermet | 1-1/4" Wirewound | 1-1/4" Cermet | 1/2" Cermet | 3/8" Cermet | 3/8" Cermet | 3/8" Cermet | 5/16" Cermet |
| 20-Turns | 15-Turns | 15-Turns | 22-Turns | 22-Turns | 10-Turns | 25-Turns | 25-Turns | 25-Turns | 4-Turns |
| 3250 | 3252 | 3260 | 3262 | 3266 | 3290 | PV12 | PV36 | PV37 | |
|  |  |  |  |  |  |  |  |  | |
| 1/2" Wirewound | 1/2" Cermet | 1/4" Wirewound | 1/4" Cermet | 1/4" Cermet | 3/8" Wirewound | 5/16" Cermet | 3/8" Cermet | 3/8" Cermet | |
| 25-Turns | 25-Turns | 11-Turns | 12-Turns | 12-Turns | 25-Turns | 4-Turns | 25-Turns | 12-Turns | |

*All multiturn through-hole sealed trimmers require an LF suffix at the end of the part number in order to be RoHS compliant. The exception is for wirewound and PV models as they are already RoHS compliant and hence, do not require the LF suffix.



SINGLE-TURN THROUGH-HOLE SEALED

| | | |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 3329 | 3362 | 3345 |
|  |  |  |
| 1/4" Cermet | 1/4" Cermet | 1/2" Wirewound |
| .5 Watt | .5 Watt | 1 Watt |




| | | |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 3360 | PV32 | 3386 |
|  |  |  |
| 6 mm Conductive Plastic | 1/4" Cermet | 3/8" Cermet |
| .25 Watt | .5 Watt | .5 Watt |



SINGLE-TURN SMD SEALED

| | | |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 3312 | 3313 | PVG3 |
|  |  |  |
| 2 mm Cermet | 3 mm Cermet | 3 mm Cermet |
| .1 Watt | .125 Watt | .25 Watt |

| | |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
| 3314 | 3361 |
|  |  |
| 4 mm Cermet | 1/4" Cermet |
| .25 Watt | .5 Watt |

MULTITURN SMD SEALED










| | | |
|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 3214 | 3223 | PVG5 |
|  |  |  |
| 4 mm Cermet | 3 mm Cermet | 5 mm Cermet |
| 5-Turns | 11-Turns | 12-Turns |

| | |
|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 3224 | 3269 |
|  |  |
| 4 mm Cermet | 1/4" Cermet |
| 12-Turns | 12-Turns |

*All SMD multiturn & single-turn sealed trimmers are RoHS compliant, except for Models 3269 & 3361. Models 3269 & 3361 require an LF suffix at the end of the part number in order to be RoHS compliant.






BOURNS® TRIMPOT® POTENTIOMETERS

MILITARY SPECIFICATION MODELS

| MIL-PRF-27208 | | | | MIL-PRF-22097 | | | | |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| RT12 | RT22 | RT24 | RT26 | RJ12 | RJ22 | RJ24 | RJ26 | RJ50 |
|  |  |  |  |  |  |  |  |  |
| 1-1/4" Wirewound | 1/2" Wirewound | 3/8" Wirewound | 1/4" Wirewound | 1-1/4" Cermet | 1/2" Cermet | 3/8" Cermet | 1/4" Cermet | 1/4" Cermet |
| 22-Turns | 25-Turns | 25-Turns | 11-Turns | 22-Turns | 25-Turns | 25-Turns | 12-Turns | Single-Turn |

*Military trimmers are NOT RoHS compliant. They meet MIL-STD specifications.

HI-RELIABILITY MIL-SPEC

| MIL-PRF-39015 | | MIL-PRF-39035 | | |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| RTR22 | RTR24 | RJR24 | RJR26 | RJR50 |
|  |  |  |  |  |
| 1/2" Wirewound | 3/8" Wirewound | 3/8" Cermet | 1/4" Cermet | 1/4" Cermet |
| 25-Turns | 25-Turns | 25-Turns | 12-Turns | Single-Turn |

*Military trimmers are NOT RoHS compliant. They meet MIL-STD specifications.

OPEN-FRAME THROUGH-HOLE SINGLE-TURN

| 3306 | 3352 |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |
| 6 mm Cermet | 3/8" Cermet |
| .2 Watt | .5 Watt |

*All open-frame trimmers are RoHS compliant, except for Model 3352. Model 3352 requires an LF suffix at the end of the part number in order to be RoHS compliant.

OPEN-FRAME SMD SINGLE-TURN

| TC33 | TC42 |
|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |
| 3 mm Cermet | 2 mm Cermet |
| .1 Watt | .1 Watt |

BOURNS®

Americas: Tel: +1-951 781-5500
Email: americus@bourns.com

EMEA: Tel: +36 88 885 887
Email: eurocus@bourns.com

Asia-Pacific: Tel: +886-2 256 241 17
Email: asiacus@bourns.com

www.bourns.com

COPYRIGHT© 2022 • BOURNS, INC. • 11/22 • e/T1903
"Bourns" and "Trimpot" are registered trademarks of Bourns, Inc. in the U.S. and other countries.

RoHS Directive 2015/863 Mar. 31, 2015 and Annex